

DT-215P-A1

21.5" PCAP Touch Monitor



Stand sold separately
Part #SS-215-A1

Description

The ultra-modern, unique zero bezel and modular design of the DT-215P-A1 makes it a one-stop-shop solution with optional peripherals for added functionality. This 10-point touch, projected capacitive, Full HD 1920 x 1080 solution is great for retail point-of-sale or point-of-service with add-on features like 3 track MSR and a 2MP camera – one mounting location, the top. The seamless bezel, advanced PCAP technology and rounded aesthetic bridges the gap between daily consumer devices and commercial devices, a step towards commonality and memorable end-user experience.

Featured Specifications

- Size: 21.5" TFT LCD
- Maximum Resolution: 1920 x 1080
- Contrast Ratio: 1000:1
- Aspect Ratio: 16:9
- Brightness: 250 nits (No Touch), 225 nits (P-CAP)
- View Angle: H: 178°, V: 178°
- Video Port: 1 x VGA, 1 x DP, 1 x HDMI
- Warranty: 3 year

Specifications

Touch LCD Display

Touch Screen	Projected Capacitive
Touch Points	10
Touch Screen Interface	USB-C

I/O Ports

Serial Port	1 x RJ11 (for Remote Key)
USB Port	1 x USB Type C (Alt Mode for DP video support)
Video Port	1 x VGA, 1 x DP, 1 x HDMI (up to 1920 x 1080 @60Hz)
Audio Port	1 x Audio-Input (3.5 mm Mini-Jack)
Power Input	1 x DC In 12V Jack Power Input

Physical Properties

Power Supply	Max. 60W (12V, 5A) External Power Adaptor
Speaker	2 x 2W
Housing Color	Black
Construction	Glass, Plastic (ABS), SECC Metal
Compliance	–
Dimensions (W x H x D) mm	510.96 x 308.01 x 37.9 mm (monitor only)
Net Weight (kg)	4.05 kg (monitor only)
Gross Weight (kg)	8.8 kg (monitor only)
Carton (W x H x D) mm	615 x 405 x 160 mm (monitor only)
VESA	100 x 100 mm
Ball Drop	–

Safety

Certifications	CE, FCC, LVD, RoHS
----------------	--------------------

Environment

Operating Temperature	0°C ~ 40°C, 20% ~ 80% RH. Non-Condensing
Storage Temperature	-20°C ~ 60°C, 10% ~ 90% RH. Non-Condensing

Optional Peripheral

MSR	MSR-215-A1 (Sold Separately)
Camera	CAM-000-A1 (Sold Separately)
21.5" Slim Stand	SS-215-A1 (Sold Separately)



www.MicroTouch.com | us.orders@microtouch.com
TES America, LLC | 215 Central Avenue, Holland, MI 49423 | (616) 786-5353

The information presented in this specification sheet is intended as general information about MicroTouch products and is subject to change. Product specifications and warranties will be governed by TES America, LLC. standard terms and conditions of sale. Products are subject to availability. Copyright © 2021 TES America, LLC. All rights reserved. MT21-1028