



Pulse 17

PULSE 17 B13VGK-888US

Specification

Manufacturer Part #	PULSE1713888
os	Windows 11 Home
	(MSI recommends Windows 11 Pro for business)
СРИ	Intel® Core™ i7-13620H
CPU Speed	2.4-4.9 GHz
Chipset	•
Color	Black
Screen Size	17.3" Thin Bezel FHD, IPS-Level 144Hz, 45% NTSC
Resolution	1920x1080
	16:9
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
	Up to 2175MHz Boost Clock 140W Maximum Graphics Power with Dynamic Boost.
	*May vary by scenario *Full-Power GPU Design
Video Memory	8G GDDR6
Keyboard	4 zone RGB keyboard with Anti-Ghost key (99 Key)
Speaker	2x Speakers 2W
Memory	16GB (8GB*2)
	DDR5 5200MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.2
Card Reader	•
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen1
	1x USB 2.0
Type-C Port	1x USB 3.2 Gen1 w/DP 1.4
Video Port	HDMI v 2.1 8K@60Hz
	4K@120Hz
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240 W
Battery Pack	4 cell , 90Whr Li-Polymer
Dimension	15.67"x10.75"x0.99"
Weight	5.95 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)