HL-L6210dwt

Business Laser Printer with Dual Paper Trays, Wireless Networking, and Duplex Printing

Specifications:

-	
Print	
Print Technology	Electrophotographic Laser
Print Speed (max.) ¹	Up to 50ppm
Time to First Page ²	Less than 6.7 seconds
Print Resolution (max.)	Up to 1200 x 1200 dpi
Print Emulations	PCL6, BR-Script3 ³ , IBM Proprinter XL, Epson FX-850, PDF Version 1.7, XPS Version 1.0
Connectivity & Compatibility	·
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
Operating Systems Compatibility ⁴	Windows 10 Home, 10 Pro, 10 Education, 10 Enterprise, 11 Home, 11 Pro, 11 Education, 11 Enterprise; Windows Server 2012, 2012 R2, 2016, 2019, 2022 mac0S v11, v12, v13 Chrome 0S, Linux, Windows Universal Print Driver
Mobile Device Compatibility ⁵	AirPrint [®] , Mopria [™] , Brother Mobile Connect, Wi-Fi Direct [®]
Security	
Security Features	Secure Function Lock, Enterprise Security (802.1x), Secure Print, TLS/SSL, IP Filter, IPSec, Syslog Reporting, SNMP v3, Secure BIOS, Password Intelligence, Lock Slot
Paper Handling	
Paper Input Capacity (max.) ⁶	(2) 520 sheet paper trays, 100-sheet multipurpose tray
Optional Paper Input Capacity (max.) ⁶	1,660 sheets via optional trays
Output Capacity (max.) ⁶	150 sheets (face down), 1 sheet (face up)
Paper Sizes (max.)	Paper Tray: Letter, Legal, Executive, A4, A5, A6 Multipurpose Tray: 3.0" - 8.5" (W), 5.0" - 14" (L)
Media Types	Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 20)
Media Weights ⁷	Standard Paper Tray: 16 to 43 lbs. Multipurpose Tray: 16 to 60 lbs.
General	
Automatic Duplex Capability	Print (default setting)
Display	1-line LCD
Processor	1.2 GHz
Memory (std. / max.)	256MB / 256MB
Included Software ⁸	Brother iPrint&Scan (desktop) for Windows and Mac $^{\otimes}$ Brother Mobile Connect for iOS $^{\otimes}$ and Android^M
Optional Brother Value Added Services	Barcode Print+, ThinPrint Client
Optional Solutions	Kofax ControlSuite, PaperCut, nddPrint, uniFLOW
Maximum Monthly Duty Cycle ⁹	Up to 125,000 pages
Recommended Monthly Volume ¹⁰	Up to 8,000 pages
Warranty	1-year limited warranty

Replacement Supplies & Optional Accessories:

Standard Yield Toner Cartridge (3,000 pages) ¹¹	
High Yield Toner Cartridge (6,000 pages) ¹¹	
Value High Yield Toner Cartridge (6,600 pages) ¹¹	
High Yield Toner Cartridge Twin-Pack (6,000 pages/Cartridge) ¹¹	
Super High Yield Toner Cartridge (11,000 pages) ¹¹	
Ultra High Yield Toner Cartridge (18,000 pages) ¹¹	
20 Drum Unit (45,000 pages) ¹²	
Optional 250-Sheet Capacity Paper Tray ⁶	
Optional 520-Sheet Capacity Paper Tray ⁶	
Optional 15.7" Printer Cabinet / Stand	

at your side

Setup Information:

UPC Code	012502670667
Unit Dimensions / Weight	14.7" (W) x 15.3" (D) x 16.6" (H) / 35.4 lbs.
Carton Dimensions / Weight	26.1" (W) x 20.6" (D) x 28.6" (H) / 53.4 lbs.
Pallet Quantity / Tiers	4/1
Country of Origin	Vietnam
Tariff / Harmonized Code	8443.32.1010

Carton Contents:

Brother HL-L6210Dw, LT-6505 520-Sheet Capacity Paper Tray, TN920 Toner Cartridge (3,000 pages)¹¹, DR920 Drum Unit (45,000 pages)¹², AC Power Cord, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.



- Based on one-sided printing. Change from default setting required.
 From ready mode and standard tray.
 PostScript²³Mc compatibile.
 For the latest OS compatibility and to download drivers, visit support.horther.com. Printing via macOS requires the use of AirPrint. Mac printer drivers are not provided.
 Requires connection to a wireless network.
 Maximum capacity based on using 20 lb, paper.
 May require free download. Compatibility may vary by device and operating system.
 Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- Based on one-sided printing. Change from default setting required.
 From ready mode and standard tray.
 Forom ready mode and standard tray.
 Forom ready mode and standard tray.
 For the latest OS compatibility and to download drivers, visit support. Torbitcom. Printing induces and printer fife. Printers are intended to handle or oeffect. Consistently printing above the row effect. Consistently printing above the row effect. Consistently printing needs.
 Requires connection to a wireless network.
 Maximum capacity based on using 20 lb, paper.
 May require free download, compatibility may vary by device and opport of gestem.
 Agregating traper output with more tike Brother products. For maximum printer itrie, it, is best to compase designed durability between like Brother products. For maximum printer itrie, it, is best to choose a printer with a duty cycle that far international state.

©2023 BROTHER INTERNATIONAL CORPORATION • All trademarks and registered trademarks referenced herein are the property of their respective companies. macOS, AirPrint, and the AirPrint logo are registered trademarks of Apple Inc., registered in the U.S. and other countries. IOS is a trademark or registered trademark of Coogle LLC. MopriaTM and the MorpriaTM Logo are registered trademarks of Apple Inc., registered trademarks of Apple Inc., in the United States and other countries. INC is a under license. Android and Google Drive are trademarks of Google LLC. MopriaTM and the MopriaTM Logo are registered trademarks of Mopria Alliance, Inc. in the United States and other countries. Inauthorized use is strictly prohibited. WI-Fi Direct®, the Wi-Fi CERTIFIEDTM logo and the Wi-Fi Protected SetupTM Identifier Mark are trademarks of WI-Fi Alliance[®]. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. All specifications subject to change without notice.