

Powerful graphics and 7 USB ports support provide excellent performance for daily



DDR5 Memory



Triple Storage



PCIe 4.0x4 M.2 SSD



HDMI CEC



USB 4



2.5G LAN



Wi-Fi 6E 802.11ax



Anti-Dust Self-Cleaning



PD Input



AI noise-canceling



8K



4 Displays

Maximum possibilities in only 0.9L compact size

- Powered by AMD Ryzen™ 7000HS Series Processor with Radeon™ graphics
- Performance of Radeon™ graphics is better than entry level discrete graphics
- DDR5 4800 memory support allows your computer to transfer data faster than DDR4
- Onboard 2.5GbE LAN delivering faster Ethernet connectivity

ExpertCenter series features:

Trustworthy

- Tested to MIL STD 810H military standard to ensure it's ready for harsh environments 24/7 testing reduce maintenance cost and improve cost effectiveness
- Padlock-ring design for more security
- Eco-friendly design, recipients EPEAT Silver and ENERGY STAR

Professionalism

- Providing the flexibility to operate fan mode depends on your needs
- ASUS Control Center option for IT Management
- Two-Way AI Noise Cancellation provides crystal-clear online voice communication

Efficiency

- One configurable port support (options: HDMI 2.1/DP1.4/VGA/COM/2.5G LAN)
- A total of 7 USB ports to connect external devices
- 2 easy steps optimization and upgrade

Over view:



Accessories list:



- Power Cord (80cm)
- AC Adapter
- Quick Start Guide & Warranty Card
- VESA Mount Kit (Optional)
- Keyboard & Mouse (Optional)
Wired / Wireless

Feature table:

Power	
PD input	Y
Extended Power Button	N
Security	
fTPM 2.0	Y
dTPM 2.0	optional
Kensington lock	Y
Pad-lock Ring	Y
Chassis Intrusion Notice	N
Reliability	
24/7 Durability Test	Y
Military-grade Durability	Y

BIOS	
AC Power loss	Y
HDMI-CEC	Y
CrashFree	Y
EZ Flash	Y
USB Single Port Control	Y
BIOS Customization	
boot logo	optional
BIOS setting	optional
PXE	optional
WOL	optional
SMBIOS (DMI)	optional

MyASUS	
Smart Fan Control	Y
AI Noise Cancellation	Y
Wi-Fi Smart Connect	Y
Enterprise Support	
Windows Autopilot Registration Service	Y
ASUS Cooperate Stable Model	optional
ASUS Control Center	optional
Others	
Watchdog timer	optional
Fanless	N

*For more information about Windows Autopilot Registration Service, please scan the QR code provided for reference.



Model		ASUS ExpertCenter PN53
OS		Windows®11 64bit, Windows®11 Pro 64bit, Linux, or W/O OS (Please check with local rep on validated Linux version)
CPU		AMD Ryzen™7 7735HS, Ryzen™5 7535HS (cTDP: 35W) Ryzen™9 6900HX, Ryzen™7 6800H, Ryzen™5 6600H (cTDP: 35W)
Chipset		Integrated
Graphics		Integrated AMD Radeon™ Graphics 680M (R9/ R7) or 660M (R5)
Memory		2 x SO-DIMM, DDR5-4800MHz memory, up to 32GB*2* *32GB memory support only on 7000 Series CPU
Storage		2 x M.2 2280 PCIe Gen4x4, supports 256GB~2TB NVMe™ SSD 1 x 2.5" SATA 6Gb/s, supports 1TB 7200rpm 7mm HDD *For higher capacity please refer to QVL (location: official website → Support → CPU / Memory Support)
Wireless Network		MTK Wi-Fi 6E or MTK Wi-Fi 6 and Bluetooth 5
LAN		Realtek® LAN, 10/100/1000/2500 Mbps Supports Wake on LAN / PXE / Auto Power on / RTC Wake
Interface	Front I/O	1 x USB 4 Type-C (40 Gbps, support DP1.4) 2 x USB 3.2 Gen1 (5 Gbps) 1 x Audio Jack(Line out/ Mic in/ Headphone out) *All data transfer speed is according to ASUS testing result, actual performance may vary depending on objective environmental changes.
	Side I/O	1 x Kensington Lock
	Rear I/O	1 x USB 4 Type-C (with DP1.4, PD-in*) 3 x USB 3.2 Gen1 Type-A 2 x HDMI 2.1 (Up to 4K@60Hz) 1 x Configurable (options: HDMI*/DP1.4/COM/VGA) 1 x 2.5G RJ45 LAN 1 x Padlock ring 1 x DC-in *Supports up to 4 display simultaneously *Configurable HDMI2.1 support up to 8K@60Hz *Power supply device need to support Power Delivery & at least 100W output *The lateral HDMI port supports CEC
TPM		fTPM 2.0 or TPM 2.0 chip (Optional)
BIOS Function		64 Mb Flash ROM, UEFI AMI BIOS, PnP, DMI2.0, WfM2.0, SM BIOS 2.8, ACPI 5.0, Multilanguage BIOS, ASUS EZ Flash 3, ASUS CrashFree BIOS 3, My Favorites, Quick Note and ASUS DRAM SPD (Serial Presence Detect) memory information
Software		The following software are included in OS: MyASUS, ASUS Product registration program, Asus Control Center test, Watchdog timer
Support		Windows Autopilot Registration Service
Power Supply		19Vdc, 6.32A, 120W (i7 12700H/ i5 12500H) 19Vdc, 4.74A or 19.5Vdc, 4.62A 90W (i3 1220P)
Physical	Dimension	120 x 130 x 58 mm (0.9L)
	Weight	0.75 kg (barebone)
Max Resolution	HDMI	7680 x 4320 @ 60Hz
	DP	5120 x 2160 @ 60Hz
	VGA	1920 x 1200 @ 60Hz
Temperature	Operating	0°C ~50°C
	Storage	-40°C ~85°C
Humidity		0%~95% Relative Humidity
Acoustic	Idle mode	<25 dBA
	Full loading	<35 dBA * Test results will vary slightly depending on the HDD/SSD SKU selected by customer
Certificates		BSMI / CB / CE / FCC / UL / CCC / Energy Star / C-Tick / WiFi / RF / VCCI