



- PRINTER HIGHLIGHTS**
- Speeds up to 45 ppm
  - 550-sheet input tray; 25-sheet manual tray
  - Automatic duplex printing
  - USB & Gigabit Ethernet connectivity
  - Mobile print-ready on iOS & Android
  - ABBYY® FineReader® PDF for Windows®/ Mac® included

## Fast, professional printing for home and office

Bring high-speed professional printing from your desktop, laptop or mobile device to your home or office with the Visioneer® Rabbit™ P45dn Printer. From Visioneer, leaders in intelligent document solutions and office automation, the P45dn is the latest addition to the Visioneer® Rabbit™ family, delivering exceptional print technology and ease-of-use.

With print speeds up to 45 pages per minute, the monochrome laser Rabbit™ P45dn features LED print head technology with automatic double-sided (duplex) printing capability. Offering both USB and Gigabit Ethernet connectivity, the P45dn printer includes a 550-sheet input tray along with a 25-sheet manual tray. A 500 MHz processor, 512 MB of RAM and a 45,000-sheet recommended

monthly print volume will handle all your day-to-day prints needs. A U.S. government TAA trade-compliant version is also available.

Your Visioneer Rabbit P45dn Printer is compatible with Windows®, Mac® and Linux® Ubuntu operating systems, and mobile-ready for use on Android® and iOS (Apple® AirPrint). Full-version ABBYY® FineReader® PDF and OCR software is included with your Rabbit™ P45dn, to create, edit, secure-sign, and search PDFs.

Ideal for legal, finance, healthcare, manufacturing and government services industries, the Visioneer® Rabbit™ P45dn Printer keeps it fast and hassle-free. Wherever and whenever you need to print, Visioneer® Rabbit™ makes easy, so you can **#CreateAndGo**.

# Visioneer® Rabbit™ P45dn Printer

## SPECIFICATIONS

Model name	Visioneer Rabbit P45dn Printer	
Model number	92-0007	TAA: 92-0018
Print technology	Laser, LED Print Head (LPH)	
Function	Print	
Device color	White, black	
Print color	Monochrome	
Print speed	45 ppm	
Main paper tray capacity	550 sheets (70 g/m <sup>2</sup> , plain paper)	
Manual paper tray	25 sheets (70 g/m <sup>2</sup> , plain paper)	
Duplex printing	Automatic	
Operation panel	1.77" LCD display + buttons	
CPU	500 MHz	
Memory	512 MB	
Printer language	GDI, PCL6	
Connectivity	USB 2.0, LAN 10/100/1000	
Supported operating systems	Windows® 7, 10, 11; MacOS® 11, 12, 13	
Drivers	Windows®, Linux®	
Mobile print capability	Android®, AirPrint® for iOS/iPadOS	
Network print compatibility	AirPrint for MacOS, Windows	
USB print compatibility	Windows	
Included software	ABBYY® FineReader® PDF for Windows or Mac®	
Min/Max print size	Min: 3" x 5" (76 x 127mm); Max: 8.5" x 14" (216 x 356mm)	
Print resolution	1200 x 600 dpi	
Dimensions	15.9" x 15" x 8" (404 x 380 x 204mm)	
Printer weight	18.7 lbs. (8.5kg)	
Recommended duty cycle	45,000 monthly impressions	
System requirements	<b>PC</b> Intel i3 or equivalent CPU 2 GB System Memory (RAM) 350 MB Available HD Space 1GB HD Space for each additional app USB 2.0 and/or network connectivity Windows 7 32-bit or later	<b>Mac</b> Intel i3 or equivalent CPU 2 GB System Memory (RAM) 350 MB Available HD Space 1GB HD Space for each additional app Network connectivity (AirPrint) Mac OS X 10.14 or later

**Box contents:** Visioneer Rabbit P45dn Printer, toner cartridge, drum unit, power supply and adapter, USB cable, Ethernet cable, Quick Install guide, warranty and registration cards

For more information on Visioneer Rabbit printers visit [www.visioneer.com/rabbit](http://www.visioneer.com/rabbit)