

## PERFORMANCE

### Display Size

27"

### View Area

596.7x335.6 mm

### Panel

In-Plane Switching

### Backlight

Mini-LED (with 1152 zones local dimming)

### Aspect Ratio

16:9

### Resolution

3840x2160

### Pixel Pitch

0.155x0.155 mm

### Dot / Pixel Per Inch

163 dpi

### View Angle (H / V)

178° / 178°

### Response Time

4ms (Extreme mode) / 6ms (Normal mode)

### Color Support

1.07 Billion

### Refresh Rate

60Hz

### Brightness

650 cd/m<sup>2</sup> (Typical) / 1200 cd/m<sup>2</sup> (Peak)

### Contrast Ratio

1000:1

### Color Gamut

99% DCI-P3, 99% Adobe® RGB, 100% sRGB, 100% BT.709, 81% BT2020

### Screen Surface Treatment

Anti-glare

### Curvature

Flat Panel

### Camera

Modular Camera Support

### Microphone

None

### Speakers

Modular Speaker Support

### Power Consumption (Typical / Maximum)

26W / 315W

### Power Adapter

Integrated

### Touchscreen

None

### Smart System

None

## DESIGN

### Stand

Tilt, Swivel, Pivot, Height Adjust Stand

### Case Color

Raven Black

### Side Bezel Width

2 mm

### Dimensions with Stand (HxWxD)

549.8x613.5x220.4 mm / 21.65x24.15x8.68 inches

### Weight (Including Stand)

8.8 kg / 19.4 lbs.

### Mounting

Supports VESA mount 100 x 100 mm

### ThinkCentre® M Series Support

Tiny, Nano Support

## CONNECTIVITY

### USB Port

1x USB-C® 3.2 Gen 2 (USB upstream), 1x USB4® (USB upstream), 4x USB 3.2 Gen 2 (1x BC1.2, USB downstream), 1x USB-C® 3.2 Gen 2 (Up to 15W, USB downstream)

### Video Connector

2x HDMI® 2.1 TMDs, 1x DP 1.4, 1x DP 1.4 Out, 1x USB 4 (40Gbps, DP 1.4 Alt Mode)

### Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

## SERVICE

### Base Warranty

3-year

## CERTIFICATIONS

### Environmental Certification

ENERGY STAR® Certified, RoHS, EU Energy Efficiency Level (Level-F), EPEAT™ Gold

### Ergonomic Certification

TÜV Low Blue Light, TÜV Rheinland® Eye Comfort, TÜV Rheinland® Flicker Free

### Sync Technology

None

### Special Features

- Factory Calibration: Avg. Delta E<1.5
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- HDR10 Compliance
- DisplayHDR™ 1000
- HLG
- KVM Switch
- Smart Sensor (Ambient Light Sensor, Human Detection Sensor)
- Smart Power  
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device
- Lenovo® ThinkColour (Lenovo® Display Accessories and Display Manager) Support  
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems). Lenovo® Display Accessories and Display Manager is formerly Lenovo® Display Control Center.

## SOFTWARE

### Operating System

Support Windows® 10, Windows® 11

## ACCESSORIES

### Video Cables

DP cable, HDMI® cable, USB-C® to USB-A Gen 2 cable, USB 4 cable

## MODEL

Announce Date

EAN / UPC : 0196804350608 / 196804350608 / None

JAN

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...



### ThinkCentre Tiny Sandwich Kit II

4XHON04098

The ThinkCentre Tiny Sandwich Kit II is a mechanical bracket which can mount your ThinkCentre Tiny PC between monitor and ThinkCentre Extend Arm. The Tiny Sandwich kit enables more desktop and floor space while provid...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference