

## PERFORMANCE

### Processor

AMD Ryzen™ 9 PRO 7940HS (8C / 16T, 4.0 / 5.2GHz, 8MB L2 / 16MB L3)

### Graphics

NVIDIA® RTX 2000 Ada Generation 8GB GDDR6

### Chipset

AMD SoC Platform

### Memory

1x 16GB SO-DIMM DDR5-5600 Non-ECC

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory

Up to 64GB (2x 32GB DDR5 SO-DIMM)

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

### Storage Support<sup>[1]</sup>

Up to two drives, 2x M.2 SSD  
• M.2 2280 SSD up to 4TB, 2TB each

### Storage Slot

Two M.2 2280 PCIe 4.0 x4 slots

### Card Reader

SD 7.0 Card Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

### Camera

5.0MP + IR Hybrid with Privacy Shutter and Human Presence Detection

### Microphone

2x, Array

### Battery

Integrated 90Wh

### Power Adapter

170W Slim Tip (3-pin)

## DESIGN

### Display<sup>[2]</sup>

16" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC

### Keyboard

Backlit, English

### Case Color

Thunder Black

### Case Material

PC-ABS (Top), PC-ABS (Bottom)

### Pen

No Support

### Dimensions (WxDxH)<sup>[3]</sup>

365 x 262 x 24.66 mm (14.37 x 10.31 x 0.97 inches)

### Weight<sup>[4]</sup>

Starting at 2.2 kg (4.85 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth<sup>[5]</sup>

Qualcomm® Wi-Fi® 6E NFA725A, 11ax 2x2 + BT5.3

### Standard Ports<sup>[6]</sup>

- 2x USB 3.2 Gen 1 (one Always On)
- 2x USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x SD Express 7.0 card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Security keyhole

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit .

[Docking for ThinkPad® P16v Gen 1 \(AMD\)](#)

## SECURITY & PRIVACY

### Security Chip

Microsoft® Pluton TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Ultrasonic Human Presence Detection for IR camera
- Camera privacy shutter
- Bottom cover tamper detection
- IR camera for Windows® Hello

## MANAGEABILITY

### System Management

AMD PRO Manageability 2.0

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

### Included Upgrade

3Y Sealed Battery Add On, 3Y Premier Support Upgrade from 3Y Courier/CCI

## CERTIFICATIONS

### Green Certifications<sup>[7]</sup>

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 9.0

### Mil-Spec Test

MIL-STD-810H military test passed

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

## MODEL

TopSeller : Yes

Announce Date : 2023-09-27

EAN / UPC / JAN : 197532974920

End of Support : 2030-02-25

Product image is a sample, it may not match the real color of this model

· Lenovo reserves the right to change specifications without notice.  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2342?M=21FE0029US>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1M86981)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39490)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS1H31743)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference