


VG275 - 27" ERGONOMIC IPS DESIGNED FOR SURFACE MONITOR WITH USB-C

Key Features


- Designed for Surface
- Single-Cable Solution
- A More Comfortable Workspace
- USB HUB
- Frameless Design
- Command and Control Made Easy



27
DISPLAY



IPS
PANEL



1920 x 1080
RESOLUTION



Product Description

Designed for Surface (DfS) products must meet the rigorous standards of Microsoft to ensure optimal compatibility with Microsoft Surface products.* The ViewSonic® VG275 monitor is compatible with all USB-C Surface devices and is ideal for office and home use. USB-C connectivity offers convenient charging power, video and audio over a single cable, and will charge your Surface device without the need for an additional power cable. Along with USB-C, additional connectivity options include HDMI, DisplayPort, VGA, and a USB hub. This 27" monitor also includes an advanced ergonomic design that features height adjustment, pivot, swivel and tilt for maximum comfort and enhanced productivity. This monitor is shipped in eco-friendly biodegradable packaging, along with an easy-to-install quick release stand that makes for simple out-of-the box setup. The quick release stand also includes an integrated client mount and cable management features. *Microsoft, Microsoft Surface, Designed for Surface are trademarks of the Microsoft group of companies.

Specifications

| | More Information |
|------------------------------------|--|
| UPC | 766907024203 |
| Screen Size | 27 |
| Viewable Area (in.) | 27 |
| Panel Type | IPS |
| Display Resolution | 1920 x 1080 |
| Display Resolution | Full HD (1920x1080) |
| Static Contrast Ratio | 1,000:1 |
| Dynamic Contrast Ratio | 50,000,000:1 |
| Light Source | LED |
| Brightness | 300 cd/m2 |
| Colors | 16.7M |
| Color Space Support | 8 bit (6 bit + Hi-FRC) |
| Aspect Ratio | 16:9 |
| Response Time (Typical GTG) | 5ms |
| Viewing Angles | 178° horizontal, 178° vertical |
| Backlight Life (Hours) | 30,000 |
| Panel Surface | Anti-Glare type, Hard-coating (3H), Haze 25% |
| Refresh Rate | 60Hz |
| PC Resolution (max) | 1920 x 1080 |
| Mac® Resolution (max) | 1920 x 1080 |
| USB Type A | 3 |
| USB Type B | 1 |
| USB Type C | 60W x 1 |
| VGA | 1 |
| HDMI 1.4 In | 1 |
| DisplayPort | 1 |
| Internal Speakers | 2W (x2) |
| Eco Mode (Conserve) | 14.5W |
| Eco Mode (optimized) | 17.1W |
| Consumption (typical) | 20.7W |
| Consumption (max) | 45.8W |
| Voltage | AC 100-240V (universal), 50-60Hz |
| Stand-by | 0.3W |

| | |
|-------------------------------------|---|
| Power Supply | Internal |
| Cable Organization | Yes |
| Kensington Lock Slot | 1 |
| Physical Controls | Key 1 (eye), Key 2, Key 3, Key 4, Key 5, Key 6 (power) |
| On Screen Display | Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu |
| Temperature | 32-104° F (0 - 40° C) |
| Humidity (non-condensing) | 20-90% |
| VESA Compatible | 100 x 100 mm |
| Frequency Horizontal | HDMI 1.4, DisplayPort, USB Type C: 15 ~ 82 KHz; VGA: 24 ~ 82 KHz |
| Frequency Vertical | HDMI 1.4, DisplayPort, USB Type C: 24 ~ 75 Hz; VGA: 50 ~ 75 Hz |
| Height Adjust | 130 mm / 5.1 in |
| Swivel | 60° |
| Pivot (Right/Left) | 90° / 90° |
| Tilt (Forward/Back) | 5° / 40° |
| Net (lbs) | 16.1 |
| Net Without Stand (lbs) | 11.2 |
| Gross (lbs) | 23.1 |
| Net (kg) | 7.3 |
| Net Without Stand (kg) | 5.1 |
| Gross (kg) | 10.5 |
| Packaging (in.) | 27.2 x 16.9 x 8.6 |
| Physical (in.) | 24.1 x 15.99~20.99 x 8.0 |
| Physical Without Stand (in.) | 24.1 x 14.2 x 2.0 |
| Packaging (mm) | 692.0 x 430.0 x 218.0 |
| Physical (mm) | 612.0 x 406.19~533.24 x 202.0 |
| Physical Without Stand (mm) | 612.0 x 362.0 x 52.0 |
| Regulations | cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Gold, CEC, MX-CoC, Mexico Energy |
| Package Contents | VG275, Power Cable, HDMI to HDMI Cable, USB Type C cable, USB Type A/B Cable, Quick Start Guide |
| Recycle/Disposal | Please dispose of in accordance with local, state or federal laws. |
| Warranty | Three-year limited warranty on parts, labor and backlight |

UPC: 766907024203



Contact Sales

ViewSonic.com

888.881.8781

email:

salesinfo@viewsonic.com