



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.736(H) x 335.664(V)
Curvature	1000R
Panel Type	Rapid VA
Panel Resolution	2560x1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	2500 : 1 (Typ.)
DCR	100000000:1
Signal Frequency	91.2~386.2 KHz(H) , 48~240 Hz(V)
ACTIVATED RANGE	48Hz - 240Hz
Refresh Rate	240Hz
Response time	1ms (GTG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive sync support
HDR Support	VESA DisplayHDR 400
Video ports	2x HDMI™ (Supports 2560x1440 P@144Hz as specified in HDMI™ 2.0b) 1x DP (Supports 2560x1440 P@240Hz as specified in DisplayPort 1.4a) 1x USB Type C (DisplayPort Alternate)
USB ports	2x USB 2.0 Type A 1x USB 2.0 Type B
Audio ports	1x Earphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	90% / 92% / 116%
Surface Treatment	Anti-glare
Display Colors	1.07B (8 bits + FRC)
Power Type	External Adaptor
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Height)	0 ~ 130mm
Kensington Lock	Yes
Dimension (W x D x H)	607 x 267 x 427 mm 607 x 112 x 372 mm (without stand)
Carton Dimension (W X D X H)	WW carton: 985 x 171 x 490 mm Outer: 1000 x 186 x 515 mm

FEATURES



Rapid VA

Provide ultra-fast 1ms GTG response time, make sure the intensity and purity of colors when gaming.



1000R

Enjoy the most immersive gameplay with 1000R curvature rate.



WQHD High Resolution

Game titles will even look better, displaying more details.



240Hz Extremely High Refresh Rate

Experience smooth gaming with a blazing fast 240Hz refresh rate, that gives you the upper hand in fast moving games.



Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms GTG response time.



VESA Certified DisplayHDR 400

Provide eye-catching detail through contrast and shadows adjustment.

Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm
Weight (NW / GW)	6.2kg/9.4kg
Note	Display Port: 2560x1440 (Up to 240Hz) HDMI: 2560x1440 (Up to 144Hz) *sRGB and DCI-P3 follow CIE1976 standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. 1 x Power Jack
3. 2 x HDMI™ (2.0b)
4. 1 x DisplayPort (1.4a)
5. 1 x USB Type C (DisplayPort Alternate)
6. 1 x USB 2.0 Type B
7. 2 x USB 2.0 Type A
8. 1 x Earphone out