



## SPECIFICATIONS

<b>Panel Size</b>	31.5" (80 cm)
<b>Active Display Area (mm)</b>	697.344(H)x392.256(V)
<b>Curvature</b>	1500R
<b>Panel Type</b>	VA
<b>Panel Resolution</b>	2560x1440 (WQHD)
<b>Pixel Pitch (H x V)</b>	0.2724(H) x 0.2724(V)
<b>Aspect Ratio</b>	16:9
<b>Brightness (nits)</b>	250
<b>Contrast Ratio</b>	3000:1
<b>DCR</b>	100000000:1
<b>Signal Frequency</b>	90.9~251.1 KHz(H) / 48~170Hz(V)
<b>ACTIVATED RANGE</b>	48~170Hz
<b>Refresh Rate</b>	170Hz
<b>Response time</b>	1ms (MPRT)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>HDR Support</b>	HDR Ready
<b>Video ports</b>	1x DP(1.2a) 2x HDMI™ (2.0b)
<b>Audio ports</b>	1x Earphone out
<b>Viewing Angle</b>	178°(H) / 178°(V)
<b>Adobe RGB / DCI-P3 / sRGB</b>	88% / 91% / 115%
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B
<b>Power Type</b>	External Adaptor
<b>Power Input</b>	100~240V, 50~60Hz
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Height)</b>	0 ~ 90 mm
<b>Kensington Lock</b>	YES
<b>Dimension (W x H x D)</b>	710 x 287 x 556 mm 710 x 103 x 418 (without stand)
<b>Carton Dimension (W X H X D)</b>	carton: 945 x 173 x 545 mm Outer: 961 x 189 x 565 mm
<b>Frameless Design</b>	Yes
<b>VESA Mounting</b>	75 x 75 mm
<b>Weight (NW / GW)</b>	6.7 kg / 9.2 kg

## FEATURES

- 1500R**  
 Enjoy the most immersive gameplay with 1500R curvature rate.
- 1ms Fast Response Time**  
 Eliminate screen tearing and choppy frame rates with 1ms response time.
- Night Vision**  
 Get the jump on enemies before they even notice you. The Night Vision is built to be easy on the eyes.
- Wide Color Gamut**  
 Game colors and details will look more realistic and refined, to push game immersion to its limits.
- 170Hz High Refresh Rate**  
 Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.
- Frameless Design**  
 With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.
- Adjustable Stand**  
 Maximize your productivity and comfort with the adjustable stand.

### Note

Display Port: 2560 x 1440 (Up to 170Hz)  
HDMI 2.0b: 2560 x 1440 (Up to 144Hz)  
Adobe RGB, sRGB and DCI-P3 follow  
CIE1976 standard

## CONNECTIONS



1. 5-way joystick navigator
2. 2x HDMI 2.0b
3. 1x DisplayPort 1.2a
4. 1x Earphoneout
5. 1x DC Jack 1x Kensington lock