



SAKER TAB-TENSION CINEGREY 5D® SERIES

Elite ProAV's *Saker Tab-Tension CineGrey 5D®* is 1.5 gain ambient and ceiling light rejecting® (CLR®) projector screen that comes in Elite's Saker electric "roll-up" configuration. ALR and CLR® projection screens enhance picture quality with brighter imagery and more defined contrast levels. However, its greatest value comes from its ability to counter the "wash out" effect of ambient light. The material is also ISF certified for its ability to achieve D65 color neutrality, superb contrast and dynamic range bringing a world class performance to any installation.



Screen Material

- CineGrey 5D® 1.5 Gain Ceiling/Ambient Light Rejecting (CLR®/ALR) projector screen
- ISF Certified – D65 color neutrality, superb contrast and dynamic range performance
- Standard black masking borders absorb projector overshoot
- Extra top black masking border for high ceiling installations
- Compatible with standard "long" throw projectors ONLY
- Curved aluminum enamel case with parallel grooves
- Tab-tension design helps maintain a flat projection surface
- 4K/8K Ultra HD and HDR Ready
- Available in diagonal sizes 100", 120", 135", 150" and 180" in 16:9 format

Design & Control System

- Floating wall/ceiling brackets allow screen to slide horizontally for proper centering (100"-150" models only)
- Suspended ceiling installation using built-in rings for 180" model
- Mounting hardware kit included for wall or ceiling installation
- Includes handheld Infrared (IR) and Radio Frequency (RF) remote controls, and a wall box controller for manual on-wall operation.
- User-friendly programmable vertical drop position
- Wall box controller is detachable for a clean look
- Built-in selectable channels allow one RF remote programming
- 12v trigger feature allows the screen's UP/DOWN operation to synchronize with the projector's power cycle
- 5-year manufacturer's warranty