

HP Pro t550 Thin Client (9A8T9UT)



Overview

Essential virtual desktop solution

Enable workforce productivity with support for solid performance requirements and security-conscious features for IT peace-of-mind. The durable HP Pro t550 Thin Client helps end users tackle daily tasks and optimize workspaces with versatile configuration options, while multiple VDI options keep your teams synchronized.

Space-saving design

Designed for a versatile workspace and specially equipped for team engagement with diverse communications.[2]

Coming soon: HP Cloud Endpoint Manager

Skillfully deploy and manage your Pro t550 Thin Clients with real-time monitoring in the cloud or on-prem.[3]

Productivity. Performance

Share ideas and content with seamless communications[2], powered by the Intel® Celeron® J-Series processor.[1]

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[2] Internet access required and not included.

[3] Select HP Thin Clients are pre-loaded with HP Cloud Endpoint Manager (CEM) and includes Tech Preview until full availability. CEM supports endpoints running Windows 10 IoT 2016 or later or ThinPro 7.2 SP11 or later. CEM term is a 12-month period beginning after device enrollment after full availability. A new license will be required to continue accessing all features after the 12-month term. For complete details, configuration requirements, and feature listings as they become available, see datasheet at the following URL:
<https://www8.hp.com/h20195/v2/GetDocument.aspx?hdocname=c08045808> .

Specifications

Operating system	IGEL OS
Processor	Intel® Celeron® J6412 (up to 2.6 GHz burst frequency, 1.5 MB L2 cache, 4 MB L3 cache, 4 cores, 4 threads)
Memory	4 GB DDR4-3200 MT/s (1 x 4 GB)
Memory Slots	1 SODIMM
Internal Storage	32 GB eMMC
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Audio	Internal amplified speaker system for basic audio playback
Dimensions (W x D x H)	3.5 x 20 x 20 cm
Dimensions (W x D x H)	1.38 x 7.87 x 7.87 in
Weight	1.3 kg <i>(Weight will vary depending on configuration.)</i>
Weight	2.87 lb <i>(Weight will vary depending on configuration.)</i>
Keyboard	HP USB 320K wired keyboard
Pointing device	HP Wired 320M Mouse
Ports	1 SuperSpeed USB Type-A 5Gbps signaling rate; 1 3.5 mm headphone/microphone combo; 2 SuperSpeed USB Type-A 5Gbps signaling rate
Ports	1 RJ-45; 1 AC power; 2 USB 2.0 Type-A; 2 SuperSpeed USB Type-A 10Gbps signaling rate; 2 DisplayPort™ 1.4
Wireless	Realtek RTL8852AE Wi-Fi 6 (2x2) and Bluetooth® 5.2 wireless card; Realtek Wi-Fi 6 RTL8852BE (2x2) and Bluetooth® 5.3 wireless card
Protocols	Citrix® HDX; Citrix® ICA; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme; Remote Desktop Services Remote FX (RFX), RDP
Power	HP Smart 45 W External AC power adapter
Energy star certified	ENERGY STAR® certified
Software included	HP Device Manager; HP Easy Shell; HP Easy Tools; HP Smart Zero Client Services; HP ThinUpdate; HP True Graphics; Microsoft SCCM/EDM Agent ^[5]
Browser supported	Mozilla Firefox (for models with HP ThinPro); Microsoft Edge (for models with Windows 10 IoT Enterprise LTSC 2021)
UPC number	197961206241

Additional specifications

Bluetooth version	Bluetooth® 5.2
Certifications and compliances	EMC; EN 60601-1-2
ECC memory	non-ECC
I/O Port location	Front
I/O Port location	Back
Keyboard connectivity	Wired
Keyboard interface	USB
Memory layout (slots & size)	1 x 4 GB
Memory module type	SODIMM
Memory size	4
Memory size uom	GB
Memory speed	3200
Memory speed uom	MT/s
Memory type	DDR4
Number of memory slots	1
Operating temperature range	10 to 40°C
Operating temperature range	50 to 104° F
Processor Brand	Intel®
Processor base frequency	2.0
Processor cache	4 MB L3
Processor core	4
Processor family	Celeron®
Processor frequency UOM	GHz
Processor maximum frequency	2.6
Processor maximum frequency uom	GHz
Processor model	J6412
Processor threads	4
Product long name specifications	HP Pro t550 Thin Client, IGEL OS, Intel® Celeron®, 4GB RAM, 32GB eMMC
Product short name specifications	HP Pro t550 Thin Client, Intel® Celeron®, 4GB RAM, 32GB eMMC
Standard memory note	Transfer rates up to 3200 MT/s.
Storage capacity	32
Storage capacity uom 01	GB
Storage type	eMMC

Storage type 01	eMMC
UNSPSC code	43211506
Wireless Model	RTL8852BE
Wireless antenna	2x2
Wireless standard	Wi-Fi 6
Wireless supplier	Realtek

[5] Software is dependent on operating system installed. Please refer to this product's QuickSpec for more details.

Hybrid Work Solutions

Audio

★ : Recommended

Wired Headset

Poly EncorePro 525 USB-A Stereo Headset	783R3AA ★
Poly EncorePro 320 Stereo USB-A Headset TAA	767G0AA ★
Poly Blackwire C5220 USB-A Headset	7S4L8AA ★
Poly EncorePro 310 Monaural USB-A Headset TAA	767G1AA
Poly EncorePro 525 Microsoft Teams Certified Stereo with USB-A Headset	783R2AA

Accessories for PC

Components/Upgrades

★ : Recommended

Memory

16GB DDR4 (1x16GB) 3200 SODIMM Memory	13L75AA
HP 8GB DDR4 (1x8GB) 3200 SODIMM NECC Memory	13L77AA

Storage

HP 256GB 2280 PCIe NVMe Value Solid State Drive	A92L2AA
---	---------

Internal ports/Modules/Controllers

HP USB to Serial Port Adapter	J7B60AA
-------------------------------	---------

Stands/Mounting Brackets

Mounting Brackets

Dual VESA Mount Bracket for HP TClient	9UB87AA
HP B300 PC Mounting Bracket	2DW53AA
HP B550 Z Display PC Mounting Bracket	16U00AA
HP B560 PC Mounting Bracket	763U8AA
HP Quick Release Bracket 2	6KD15AA
HP Thin Client Mounting Bracket	2FT00AA

Stands

HP t5/t6 Thin Client Stand	AK6D5AA
----------------------------	---------

Keyboards/Other Input Devices

Wired Keyboards

HP 125 USB Wired Keyboard	266C9AA
HP 320K Wired Keyboard	9SR37AA
HP 320K Wired Keyboard	9SR37UT
HP Business Slim Smartcard Keyboard	Z9H48AA
HP USB Promo Bus Slim CCID SmartCard Kyd Z9H48AT	Z9H48AT

Wireless Combo

HP 235 Wireless Mouse and Keyboard Combo	1Y4D0AA
HP 235 Wireless Mouse and Keyboard Combo	1Y4D0UT
HP 655 Wireless Keyboard and Mouse Combo	4R009AA
HP 655 Wireless Keyboard and Mouse Combo	4R009UT

Mice/Pens/Other Pointing Devices

Wired Mice

HP 125 Wired Mouse	265A9AT
HP Wired 320M Mouse	9VA80AA

Video Devices

Video Devices

HP 325 FHD USB-A Webcam	53X27AA
HP 435 FHD Webcam	77B10AA
HP 625 FHD Webcam	6Y7L1AA
HP 625 FHD Webcam	6Y7L1ET

Port Replicators/Dongles/Docking

Cables/Cable Adapters/Dongles

HP DisplayPort Cable Kit	VN567AA
HP DisplayPort To VGA Adapter	AS615AA
HP DisplayPort To VGA Adapter	F7W97AA
HP DisplayPort to DVI-D Adapter	FH973AA
HP USB-C to VGA Adapter	4SH06AA

Docking

HP USB-C Dock G5	5TW10AA
HP USB-C Dock G5	5TW10ET
HP USB-C G5 Dock	26D32AA

Security

Security Cables

HP Keyed Cable Lock	T1A62AA
---------------------	---------

Power

Power Adapters

HP Thin Client 45W Power Supply	Y3U71AA
HP Thin Client 45W Power Supply Cable Y3U68AA	Y3U68AA

Monitors

Business Monitors

★ : Recommended

E-Series

HP E24m G4 FHD USB-C Conferencing Monitor	40Z32A7	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AA	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AS	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32E9	
HP E24u G5 FHD USB-C Monitor	6N4D0A5	obsolete
HP E24u G5 FHD USB-C Monitor	6N4D0AA	
HP E24u G5 FHD USB-C Monitor	6N4D0AS	obsolete
HP E24u G5 FHD USB-C Monitor	6N4D0E9	obsolete
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29A7	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AA	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AS	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29E9	
HP E27u G5 QHD USB-C Monitor	6N4D3A5	
HP E27u G5 QHD USB-C Monitor	6N4D3AA	
HP E27u G5 QHD USB-C Monitor	6N4D3AS	
HP E27u G5 QHD USB-C Monitor	6N4D3E9	

Series 5 Pro

HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7A5	
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7AA	
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7AS	
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7E9	
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5A5	
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5AA	
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5AS	
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5E9	

Disclaimer — Copyright

Intel, Pentium, the Intel logo, Intel Core, Thunderbolt, vPro, Optane, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB

Implementers Forum. Adobe PDF is a trademark of Adobe Systems Incorporated. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. NVIDIA, the NVIDIA logo, Quadro, and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the US. and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jul 22, 2025 7:54 AM UTC+0000