


AK-C8112F MEDICAL KEYBOARD WL DUO

Cordless/Wireless disinfectable Medical Keyboard with full layout and flat key profile



Product images may vary depending on the country layout

The disinfectable full-sized AK-C8112 Medical Keyboard Duo is the all-rounder for hygiene-sensitive areas and will impress even the most discerning keyboard user in hospitals, medical practices, or laboratories. Due to its flat surface, it can be thoroughly wiped clean, preventing germ growth on contaminants and disinfectant residues in cavities. It comes either fully sealed with an IP65 rating or with an IP68 rating when the USB cable is replaced by a watertight plug for cleaning. In addition to its cleaning properties, the AK-C8112 scores with outstanding typing experience, durability, and ergonomics. With the standard layout of 104 or 105 keys, the AK-C8112 combines all the advantages of a hygienic keyboard with the typing feel of an office keyboard. It offers the greatest possible flexibility in the areas of use thanks to the selectable radio or cable connection by means of a detachable USB cable.

FUNCTION AND PERFORMANCE

- Fully sealed silicone membrane provides all-around protection from dirt and fluids
- Approved for wipe disinfection according to CDC Guideline for Disinfection and Sterilization in Healthcare Facilities (2008)

- Fully sealed with IP68 rating silicone membrane that can be sterilized in an autoclave
- CleanFunction enables the keys to be switched off during cleaning
- Standard office keyboard layout with 104 keys
- Flat surface for effective and efficient wipe disinfection
- Smooth, comfortable tactile typing experience

TECHNICAL DATA

Weight main product:	26 oz
Dimensions product without packaging:	17,72 in x 5,75 in x 1,3 in
Weight of product incl. packaging (g):	38.8 oz
Dimensions product incl. packaging:	18,5 in x 7,87 in x 1,57 in
Content of master carton (pieces):	10
Weight of master carton incl. content:	352.74 oz
Dimensions master carton:	16.73 in x 8.27 in x 19.88 in
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 122 °F
Product approvals:	<ul style="list-style-type: none"> • CE • EU RoHS • FCC • CAN/ISED • EN60601-1-2-2015 (IEC 4th edition)
System Requirements-Hardware:	USB-A
Operating system:	All operating systems that support USB keyboard interface
Scope of delivery:	<ul style="list-style-type: none"> • Keyboard • Manual
USB dongle:	yes
Wireless range (m):	33 ft
Number of batteries:	4
Battery design:	AAA
Battery rechargeable:	no

Battery replaceable:	yes
Switching characteristics:	tactile
Key labeling:	Silk screen printing on silicon membrane
Special key functions:	<ul style="list-style-type: none"> • FN Key • CleanFunction
Status LEDs:	in housing
Key technology:	Scissor

Keycap material:	ABS
Reprocessing:	<ul style="list-style-type: none"> • Recommended for Wipe Disinfection • Approved for wipe disinfection according to CDC Guideline for Disinfection and Sterilization in Healthcare Facilities according to manufacturer's instructions.

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Designation

AK-C8112F Medical Keyboard WL Duo