



HP DesignJet T850 36-in Printer (2Y9H0A)



Overview

The world's easiest A3-A1 printing experience to maximize your team's agility[1]

Maximize your team's agility with the world's easiest A3-A1 experience.[1] Simplify multi-size printing with the integrated input tray. Streamline print workflows with HP Click. And meet office and environmental needs with this compact plotter.

THE EASIEST[1]—Multi-size printing in one click

Do it all—also print A3 jobs using the integrated input tray, without manually changing from roll to sheets.

GO BEYOND—Meet office and environmental needs

Advance environmental goals—printer is made with at least 35% recycled plastics[3] and recyclable supplies[4].

CONNECTED—Work securely from virtually anywhere

Save time with HP Click—print in fewer steps and avoid reprinting with print preview.

[1] Based on test results using HP Click with the HP DesignJet T850. This solution enables printing in fewer steps compared to main competitor printing solutions. Printing a 5-page mixed job set with A1 and A3 takes 3 steps using HP Click vs. 12 steps with competitor A and 8 steps with competitor B. Testing performed by Sogeti, April 2023. Detailed test report is available upon request.

[3] Declared %RCP content is based on the quantity and weight of parts made with RCP resin over the total plastic parts.

[4] Program availability varies. See <https://www.hp.com/go/recycle>

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print
Connectivity, standard	Gigabit Ethernet (1000Base-T), Wi-Fi 802.11b/g/n
Software included	HP Click for Windows and macOS, HP app for Windows, macOS, Android, and iOS
Technical features	A3 input tray;Auto-power on/off scheduler;130/300 ml cartridges;Max. resolution 2400 x 2400 dpi;Sheet organizer accessories;HP Wolf Pro Security;HP Flex Tech Inks
Energy star certified	Yes
Minimum dimensions (W x D x H)	1407 x 701 x 967 mm
Minimum dimensions (W x D x H)	55.4 x 27.6 x 38.1 in
Weight	47 kg
Weight	103.6 lb
Power consumption	35 W (printing), <5.5 W (ready), <2.5 W (sleep), <0.2 W (standby). Auto-scheduled printer on/off usage.
Environmental certification	ENERGY STAR, EPEAT, UL ECOLOGO® certified inks, CE marking (including WEEE, RoHS, REACH, ErP). In compliance with applicable WW RoHS materials restriction requirements.
What's in the box	HP DesignJet T850 Printer, printhead, introductory ink cartridges, printer stand, spindle, guide, warranty flyer, power cord

Additional specifications

Acoustic power emissions (active, printing)	5.8 B(A) (operating), <3.4 B(A) (idle)
Acoustic pressure emissions	42 dB(A) (operating), <16 dB(A) (idle)
Color(s) of printing supplies	Cyan, magenta, yellow, matte black
Datasheet photo 1	AHID/f689be319754814d8d25b9577c2aebd56c8b2cd4
Dynamic security	Dynamic security enabled printer
Electromagnetic compatibility	Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (RED Directive), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI); Korea (KCC)
Finished output handling	Sheet feed, roll feed, input tray (50 sheet capacity), media bin, automatic horizontal cutter
HP ePrint capability	Yes
Ink drop	6 pl (C, M, Y); 12.6 pl (mK)
Ink types	Pigment-based (C, M, Y, mK)
Internal Storage	None
Line accuracy	±0.1%[2]
Maximum optical density (black)	15 L* min/1.7 D[3]
Media sizes standard (metric rolls)	369 to 914 mm
Media sizes standard (sheets, rolls)	14.5 to 36 in
Media sizes supported	Input tray: A, B; Manual feed: A, B, C, D, E
Media sizes supported	Input tray: A4, A3; Manual feed: A4, A3, A2, A1, A0
Media sizes, custom	Input tray: 210 x 279 to 305 x 457 mm; Manual feed: 210 x 279 to 914 x 1676 mm
Media sizes, custom	Input tray: 8.3 x 11 to 12 x 18 in; Manual feed: 8.3 x 11 to 36 x 66 in
Media thickness	Up to 11.8 mil
Media thickness (metric)	Up to 0.3 mm
Media types	Bond and coated paper (bond, coated, heavyweight coated, plain, bright white, blueprint), technical paper (natural tracing), film (clear, matte), photographic paper (ID satin, ID gloss), self-adhesive (adhesive matte/gloss, adhesive polypropylene gloss), Polypropylene (matte)
Media weight, recommended	60 to 280 g/m ² (roll/manual feed); 60 to 220 g/m ² (input tray)
Media width, maximum	914 mm
Media width, maximum	36 in
Memory	1 GB
Model size	914 mm

Model size	36 in
Network ready	Standard
Non-Operating Humidity Range	0 to 95% RH
Non-printable area (cut-sheet)	0.2 x 0.2 x 0.2 x 0.2 in
Non-printable area (cut-sheet)	5 x 5 x 5 x 5 mm
Non-printable area (roll media)	5 x 5 x 5 x 5 mm
Non-printable area (roll media)	0.2 x 0.2 x 0.2 x 0.2 in
Number of print cartridges	4 (C, M, Y, mK)
Operating altitude	Up to 9843 ft
Operating altitude	Up to 3000 m
Operating humidity range	20 to 80% RH
Operating temperature range	41 to 104°F
Operating temperature range	5 to 40°C
Orderable supplies	HP Original Ink: HP 738 cartridges (Black, Cyan, Magenta, Yellow), and HP 739 printhead
Package dimensions (W x D x H)	1575 x 570 x 650 mm
Package dimensions (W x D x H)	62 x 22.5 x 25.5 in
Package weight	156.5 lb
Package weight	71 kg
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png
Playbook TS icon display AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169148.png
Post consumer recycled plastic in hardware by weight of plastic	42%
Power	Input voltage (auto ranging): 100-240 V (±10%), 50/60 Hz (±3 Hz), 1.2 A max
Print Technology	Ink
Print cartridge volume delivered	300 ml, 130 ml
Print head nozzles	1376 per color; 5504 in total
Print heads	1 (C, M, Y, mK)
Print languages	TIFF, JPEG, URF, HP-GL/2, HP-RTL, CALS G4
Print multi-size files in one click	Yes
Print speed	25 sec/page on A1, 90 A1 prints per hour[1]
Print speed	25 sec/page for D size, 90 D size 24" x 36" prints per hour[1]
Print technology	HP Thermal Inkjet
Printer drivers included	Raster driver for macOS and Windows, HP-GL/2 driver for Windows

Printing path	Wi-Fi Direct, remote printing, Apple AirPrint and HP app for Android and iOS devices, Windows and macOS printer drivers, printing support for Chrome OS
Product logos	AirPrint; CE marking; ENERGY STAR; EPEAT green; IPv6 Ready; Mac; Wi-Fi Certified; Windows 11 Compatible
Recommended media	HP Universal Bond Paper (FSC® certified)[4] (recyclable)[5]; HP Coated Paper (FSC® certified)[4] (recyclable)[5]; HP Heavyweight Coated Paper (FSC® certified)[4] (recyclable)[5]
Remote print enabled	Yes
Roll external diameter	100 mm
Roll external diameter	3.9 in
Roll maximum input	1
Roll maximum weight	13.6 lb
Roll maximum weight	6.2 kg
Safety	USA and Canada (CSA certified); EU (RED Directive, EN 62368-1 compliant); Singapore (PSB); China (CCC); Mexico (NYCE); Argentina (IRAM); India (BIS)
Security features	HP Secure Boot, whitelisting, Security event logging, Disable network ports and protocols, SNMPv3, 802.1x compatibility, TLS/SSL, HP Web JetAdmin, HP Security Manager, SIEM Integration
Storage temperature range	-25 to 55°C
Storage temperature range	-13 to 131°F
Supported Primary Applications	Line drawings; Renderings; Presentations; Maps; Posters
Technology logo 1	AHID/cce10ebbd356d96074154a12dc62032a64b058f3
Technology logo 2	AHID/60d2a69d632efba286c546dd6a2fcfdb5c3c9e1f
Technology logo 3	AHID/cd33e848211911e4369b10008531951b0aa3cde7
Technology logo 4	AHID/c51bf05ff1023abad6fda02c5a970763b91946f4
Technology logo 5	AHID/6615658f92b8dd21f3c5b78f3bea628bd257123b
Technology logo 6	AHID/0e41ea2a916263d4c3403cc03016fcaae7311969
Technology logo 7	AHID/1f8b1ff3a68a6ba2a0939f2536845c50fe9dec4f
Theoretical minimum line width	0.0008 in (via raster driver)
Theoretical minimum line width	0.02 mm (via raster driver)
UNSPSC code	43212104
UPC number	(AB1) 198701770633; (ABG) 196548313037; (AC4) 197498560564; (ACJ) 196548313044; (AKV) 197498560571; (B19) 196548313051; (B1K) 196548313068; (BCD) 196548313075
Web address for additional information	https://www.hp.com/go/designjet-t850

Ink Supplies

★ : Recommended

HP Graphic Arts Inks/Printheads

HP 738 130-ml Black DesignJet Ink Cartridge	498N4A
HP 738 130-ml Cyan DesignJet Ink Cartridge	498N5A
HP 738 130-ml Magenta DesignJet Ink Cartridge	498N6A
HP 738 130-ml Yellow DesignJet Ink Cartridge	498N7A
HP 738 300-ml Black DesignJet Ink Cartridge	498N8A
HP 738 300-ml Cyan DesignJet Ink Cartridge	676M6A
HP 738 300-ml Magenta DesignJet Ink Cartridge	676M7A
HP 738 300-ml Yellow DesignJet Ink Cartridge	676M8A
HP 738B 130-ml Black DesignJet Ink Cartridge	498P2A
HP 738B 300-ml Black DesignJet Ink Cartridge	498P6A
HP 739 DesignJet Printhead Replacement Kit	498N0A

Accessories

Paper Handling

★ : Recommended

Spindles

HP DesignJet 36-in Spindle	B3Q37A
----------------------------	--------

Output Trays and Stackers

HP DesignJet Sheet Organizer	698G7A
HP DesignJet Sheet Organizer and Stacker Kit	698G8A

Scanners

★ : Recommended

Large Format Scanners

HP HD Pro 2 42-in Scanner	5EK00A
HP SD Pro 2 44-in Scanner	5EK01A

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.