



BUSINESS & PRODUCTIVITY ALL-IN-ONE PC

Modern AM242TP 12M

MODERN AM242TP 12M-053US

Specification

Manufacturer Part #	MAM242TP12M053
Color	BLK
Operating System	Windows 11 Home
Processor	Intel® Core™ i7-1260P 4P+8EC/16T 18MB Cache
Chipset	Intel® SoC
Display	23.8" FHD IPS-Grade 1920x1080, LED, Matte, Multi-Touch
Display Type	Multi-Touch (10)
Graphics	Intel® Iris Xe
Memory	16GB DDR4 (2 x 8GB)
Memory Slots	2x DDR4 2666/3200MHz SO-DIMM, up to 64GB
Storage	512GB M.2 NVMe SSD
Optical Drive Type	N/A
LAN	1 x RJ45 (1GbE)
WLAN	WiFi 6 (802.11ax) 2.4Gbps, Dual Band 2.4GHz, 5GHz
Bluetooth	BT 5.2
Included Peripherals	Wireless Keyboard & Mouse
Audio	2 x 2.5W Speakers HD Audio (Realtek ALC256)
VGA	N/A
Video I/O	1 x HDMI-out, 1 x HDMI-in
USB 2.0	2 x USB 2.0 (rear)
USB 3.1/3.2	2 x USB 3.2 Gen2 Type-C (side) 2 x USB 3.2 Gen2 Type-A (side)
Mic in / Headphone out	1 x Mic-in/Headphone-out Combo
Card Reader	N/A
Webcam	Built-in 2M 720p (HD) w/IR & Dual-array Mic
Stand	Adjustable Stand
Power Adapter	120W
VESA	75x75mm
Dimensions	21.31" x 7.66" x 21.06"
Weight	13.58 lbs
Warranty	1 Year