



L A P T O P S

Stealth 17 Studio

STEALTH 17STUDIO A13VI-012US

Specification

Manufacturer Part #	STEALTH1713012
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU	Intel® Core™ i9-13900H
CPU Speed	2.6-5.4 GHz
Chipset	-
Color	Core Black
Screen Size	17.3" QHD, Anti-Glare Wide View Angle 240Hz 3ms DCI-P3 100%
Resolution	2560x1440 16:9
GPU	NVIDIA® GeForce RTX™ 4090 Laptop GPU Up to 1455MHz Boost Clock 105W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	16G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Speaker	Dynaudio Speakers 2W*2 + 2W*4 woofer
Memory	32GB (16GB*2) DDR5 5200MHz
HDD Capacity	2TB NVMe SSD
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675i
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	IR FHD
USB	2x USB 3.2 Gen2
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	HDMI v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240 W
Battery Pack	4 cell (99.9Whr) Li-Polymer
Dimension	15.65"x 11.16"x 0.79"
Weight	6.17 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)