

# 2N Clip

# The power of IP for every home

Bring the convenience and safety of high-quality video to mid-priced residential projects. The 2N Clip is a 4" video IP indoor station designed to meet the rising demand for more affordable housing.

#### Perfect for mid-range projects

The 2N Clip was designed with the mid-range sector in mind. You'll get IP video, good design, and the reliability of 2N's products without the premium price tag

#### Fits seamlessly into the 2N ecosystem

The 2N Clip runs on the powerful, reliable 2N OS – the same as the most premium of products from our workshop. Plus, it can be remotely managed and configured via the My2N Management Platform

# **Doorbell button support**

No need to install additional electronics and save money on a traditional doorbell, too: simply connect the doorbell button to the 2N Clip directly

### Increase security. Upgrade to IP video

Forget blurry videos from outdated analog units - high-quality IP video is the new norm in modern living and is much more secure. Meet the market's standards with the 2N Clip!

#### Install it in 3 minutes!

Drill in two screws and – wait for it – 'clip' the 2N Clip to the wall! This has got to be the fastest indoor station installation on the market

# Help the hearing-impaired

The 2N Clip also comes in a variant with a built-in induction loop for projects where accessibility is a priority.

#### **Variants**









#### **Technical Parameters**

#### **Power supply**

 Type
 PoE

 PoE
 802.3af Class 0, 48 V DC, 200 mA

#### **User interface**

Controls 3 capacitive buttons

**Operation** press and hold the RESET button to restore

factory settings

# Audio

MicrophoneintegratedSpeakerintegrated, 2WIntegrated induction loopoptional

Codecs G.711a/u, G.722, G.729, L16/16 kHz

#### Video

Display 4.3" display

Resolution 480x272 pixels

Codecs H.264

# Interface

LAN 10/100BaseT, RJ-45

Recommended cabling Cat5e or higher

# **Doorbell input**

Input type switching contact (button/relay)

Contact type normally open (NO)

Contact parameters 12V/20mA, DC

#### **Mechanical properties**

Operating temperature 32 to 122°F Storage temperature -4 to 158°F

Relative operating humidity 10 to 90 % (non-condensing)

Recommended altitude 0 to 6,500 ft

**Dimensions** 4.88 (W) x 5.91 (H) x 1.10 (D) in

Weight 0.52 lb

#### Warranty

5-years warranty see

https://www.2n.com/en\_GB/support/warranty-and-repairs

# Member of the AXIS group

