

4MP H.265 IP Turret Camera with Advanced Analytics

04T9M

2.8-12mm motorized lens, white housing













Features

- Supports up to 4MP @ 30fps
- 4x Optical Zoom
- Built-in standard PoE (IEEE 802.3af)
- H.265/H.264/MJPEG compression supported
- True Day/Night operation (IR cut filter)
- Adaptive IR LEDs reduce IR saturation
- IR range: Up to 165 FT (depending on scene reflection)
- Micro SD slot up to 256GB (card not included)
- True WDR (wide dynamic range) operation
- IP67 compliant, weather resistant
- Junction box included (works with NPT/BSP specifications)
- Conformant with ONVIF Profile G/S/T
- UI-listed
- 5 year warranty





Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2592 x 1520
Field of View	100°~95.3°(H), 54.5°~16.7°(V), 104.8°~33.1°(D)
Minimum Illumination	0.003 lux @ F1.3, AGC ON, 0 lux (IR LED on)
Day/Night	Smart IR
White Balance	Auto, Indoor, Outdoor, Manual
Compensation	True WDR (120dB), BLC, HLC
Electronic Shutter Speed	1/3 - 1/100000 sec.
DNR	3D DNR

Video Specifications

Main Resolution	2592x1520 / 2560x1440 / 2304x1296 / 1920x1080 / 1280x720 @ 30fps	
Sub Stream	720P/ D1, CIF	
Third Stream	D1/CIF/480 X 240	
Compression	H.265, H.264 (HP/MP/BP), MJPEG	
Video Settings	Region of Interest, Privacy masking, Brightness, Contrast, Hue, Saturation, Denoise, Antiflicker, Day/Night mode, Infrared settings, Exposure, Gain, Corridor Pattern, Image flip/mirror	
Bitrate Control	itrate Control VBR, CBR (64Kbps ~ 10Mbps)	
Multiple Streaming	Ultiple Streaming 3 streams	

Network Specifications

Network Specifications		
Protocols	UDP, IPv4, IPv6, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, SNMP, $802.1x$, UPnP, HTTP, HTTPS	
DDNS support	Speco DDNS (free of charge)	
Security	User ID & Password protection, IP/Mac address filtering, digest authentication	
User Access	Max. 10 simultaneous users, Actual number of users may vary depending on bandwidth	









*Products are in compliance with NDAA Section 889 Part B Guidelines

Client Specifications

Web Browser Support	Google Chrome, Edge, Safari, Fire Fox, Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS, SecureGuard® CMS
Mobile	SecureGuard® Client, Speco Blue (iPhone® and Android™)

Audio Specifications

Interfaces		
Ethernet	10/100 Mbps	
Power	DC jack	
Microphone Input	Mono 3.5mm + built-in mic	
Audio Output	No	
Card Slot	MicroSD, up to 256GB (not included)	
Alarm	No	
Reset	Yes	

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion, Exception, Line Crossing, Region Intrusion, Object Detection, Vehicle/People Detection, Face Detection, People/Vehicle Counting & Tampering Detection
Alarm Triggers	Analytics, SD card error
Alarm Events	FTP upload, email upload
Image Settings	Watermark, IP address filtering, video mask, password protection

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	< 7.5W
Operating Temperature	-40°F ~ 140°F
Operating Humidity	Less than 95 % (non-condensing)
Unit Dimensions	3.7" (φ) x 3.25" (H)
Unit Weight	1 lb.
Certifications	FCC, UL-listed

















CLT4

Cameras Interfaces











25.5W

PoE Injector











Ceiling Mount

ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 11/21/22
Apps available from the following:









