



# 4MP H.265 IP Turret Camera, NDA A Compliant

## O4VT2M

2.8-12mm motorized lens, white housing



### Features

- Captures up to 4MP @ 30fps
- Up to 4x optical zoom
- H.265/H.264 compression supported
- Built-in standard PoE (IEEE 802.3af)
- True Day/Night operation (IR cut filter)
- IR range: Up to 167' (depending on scene reflection)
- True WDR
- Micro SD card slot up to 256GB (card not included)
- Built-in Microphone
- Conformant with ONVIF Profile G/S/T
- Line crossing, object detection, region intrusion and video blurring detection
- IP67 Weather Resistance
- 5 year warranty
- NDA A Compliant



### Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2560 x 1440 (4MP)
Field of View	92° ~ 31°(H), 48° ~ 17.2° (V), 112° ~ 35.6° (D)
Minimum Illumination	0.005 lux @ F1.6, AGC ON; 0 lux with IR
Image Settings	Region of interest, Saturation, Brightness, Chroma, Contrast, Wide Dynamic, Defog, Sharpen, Noise Reduction
Day/Night	Smart IR up to 167' (depending on scene reflection)
Compensation	True WDR, BLC, HLC
Electronic Shutter Speed	1/2 - 1/100000 sec.
DNR	3D DNR
Angle Adjustment	Pan 0°-360°, Tilt 0°-80°, Rotation 0°-360°

### Video Specifications

Main Resolution	2560x1440 / 2304 x 1296 / 1920x1080 up to 30fps
Sub stream Resolution	720p (1-15fps), D1, CIF (1-30fps)
Third Stream	D1, CIF, 480x240 (1-30fps)
Compression	H.265, H.264
Bitrate Control	VBR, CBR (64Kbps ~ 5Mbps)
Multiple Streaming	3 streams

### Network Specifications

Protocols	UDP, IPv4, IPv6, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, 802.1x, UPnP, HTTP, HTTPS, QoS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP/Mac address filtering, digest authentication
User Access	Max. 4 simultaneous users, Actual number of users may vary depending on bandwidth

### Audio Specifications

Audio Compression	G.711A / G.711U
-------------------	-----------------

### Interfaces

Ethernet	RJ45 Jack
Power	DC Jack
Audio Input	3.5mm input, built-in mic
Audio Out	No
Card Slot	MicroSD, up to 256GB (not included)
Alarm In/Out	No
Reset	Yes

### System Specifications

PoE	Standard (IEEE 802.3af)
Detection Events	Line crossing, object detection, region intrusion and video blurring detection
Alert Triggers	Motion, Detection Events, SD card error
Image Settings	Watermark, IP address filtering, video mask, password protection, Corridor mode

### Client Specifications

Web Browser Support	Chrome, Edge, Safari, Firefox, Internet Explorer
PC Application	SecureGuard® VMS, SecreGuard® CMS
Mobile	SecureGuard® Client, Speco Blue (iPhone® and Android™)

### Operating & Unit Specifications


Power	PoE, 12VDC (power supply not included)
Power Consumption	< 9W
Operating Temperature	-40°F ~ 140°F
Operating Humidity	Less than 95 % (non-condensing)
Unit Dimensions	5.125" (Dia.) x 4.1" (H)
Unit Weight	1.41 lb.
Certifications	FCC



\*Products are in compliance with NDA A Section 889 Part B Guidelines



### Optional Accessories



### Cameras Interfaces



ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 12/19/22

Apps available from the following:

