HL-L5210dwt

Business Laser Printer with Dual Paper Trays, Wireless Networking, and Duplex Printing

Specifications:

Electrophotographic Laser
Up to 48ppm
Less than 6.7 seconds
Up to 1200 x 1200 dpi
PCL6, BR-Script3 ³ , IBM Proprinter XL, Epson FX-850, PDF Version 1.7, XPS Version 1.0
Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
Windows 10 Home, 10 Pro, 10 Education, 10 Enterprise, 11 Home, 11 Pro, 11 Education, 11 Enterprise; Windows Server 2012, 2012 R2, 2016, 2019, 2022 macOS v11, v12, v13 Chrome OS, Linux, Windows Universal Print Driver
AirPrint [®] , Mopria™, Brother Mobile Connect, Wi-Fi Direct [®]
Secure Function Lock, Enterprise Security (802.1x), Secure Print, TLS/SSL, IP Filter, IPSec, Syslog Reporting, SNMP v3, Secure BIOS, Password Intelligence, Lock Slot
250-sheet paper tray, 520-sheet paper tray, 100-sheet multipurpose tray
1,390 sheets via optional trays
150 sheets (face down), 1 sheet (face up)
Paper Tray: Letter, Legal, Executive, A4, A5, A6 Multipurpose Tray: 3.0" - 8.5" (W), 5.0" - 14" (L)
Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 20)
Standard Paper Tray: 16 to 43 lbs. Multipurpose Tray: 16 to 60 lbs.
Print (default setting)
Print (default setting) 1-line LCD
1-line LCD
1-line LCD 1.2 GHz
1-line LCD 1.2 GHz 256MB / 256MB Brother iPrint&Scan (desktop) for Windows and Mac®
1-line LCD 1.2 GHz 256MB / 256MB Brother iPrint&Scan (desktop) for Windows and Mac [®] Brother Mobile Connect for iOS [®] and Android [™]
1-line LCD 1.2 GHz 256MB / 256MB Brother iPrint&Scan (desktop) for Windows and Mac [®] Brother Mobile Connect for iOS [®] and Android TM Barcode Print+, ThinPrint Client

Replacement Supplies & Optional Accessories:

TN920	Standard Yield Toner Cartridge (3,000 pages) ¹¹
TN920XL	High Yield Toner Cartridge (6,000 pages) ¹¹
TN920V	Value High Yield Toner Cartridge (6,600 pages) ¹¹
TN920XL 2PK	High Yield Toner Cartridge Twin-Pack (6,000 pages/Cartridge) ¹¹
TN920XXL	Super High Yield Toner Cartridge (11,000 pages) ¹¹
DR920	Drum Unit (45,000 pages) ¹²
LT-5505	Optional 250-Sheet Capacity Paper Tray ⁶
LT-6505	Optional 520-Sheet Capacity Paper Tray ⁶
CB-2000	Optional 15.7" Printer Cabinet / Stand

at your side

Setup Information:

012502670681
14.7" (W) x 15.3" (D) x 15.3" (H) / 32.7 lbs.
26.1" (W) x 20.6" (D) x 27.4" (H) / 51 lbs.
4/1
Vietnam
8443.32.1010

Carton Contents:

Brother HL-L5210Dw, LT-6505 520-Sheet Capacity Paper Tray, TN920 Toner Cartridge (3,000 pages)¹¹, DR920 Drum Unit (45,000 pages)¹², AC Power Cord, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.



1 Based on one-sided printing. Change from default 10 The recommended range of monthly printed

- Based on one-side priming. Unlarge from denain setting required.
 From ready mode and standard tray.
 PostScript² 3^m compatibility and to download drivers, visit support. Irother.com. Printing via macOS requires the use of AirPrint. Mac printer drivers are not provided.
 Requires connection to a wireless network.
 Maydium consolity to a printer driver are are provided to a printer driver and provided to a wireless network.
- Requires connection to a wireless network.
 Maximum capacity based on using 20 lb. paper.
 Half speed and straight paper output with more than 28 lb.
 May require free download. Compatibility may vary by device and operating system.
 Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume. however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
 Approximate tomer cartridge yield in accordance with ISO/IC 19752 (letterA4).
 Approximately 45,000 pages based on 1 page per job and 75,000 pages based on 3 pages pri job (letter/A4 simplex pages). The number of pages may be affected by a variety of factors including but not limited to media type and media size.