



Poly Blackwire 3315 Monaural Microsoft Teams Certified USB-C Headset +3.5mm Plug +USB-C/A Adapter (8X218AA)

Overview

Style, comfort and audio quality

Built for style with a sleek design that focuses on comfort and reliability. Poly signature audio quality so you know you will sound great. And intuitive and simple features so every user can connect to their preferred device simply and easily.

Connect quickly and easily

The Blackwire 3300 Series is completely plug-n-play with USB devices, so users can take calls in the office or on the go. Its robust design delivers reliability you can count on. This is the hassle-free headset you've been looking for.

Look good, feel good, sound amazing

Boost your on-the-call confidence with professional-quality audio and a customized fit with a headset that can connect to your devices quickly and easily and is ready to go with you wherever you go.

Features

High-quality audio

Makes collaboration easy with Poly signature audio quality and reliability.

Headset flexibility

With professional voice quality and a customized fit, this fully adjustable headset has 180-degree pivoting speakers and a flexible microphone boom.

Connectivity options

Enhanced connectivity for your devices: USB Type-C® cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

Wearing Style

Monaural wearing style for those who prefer to leave one ear open.

Long-lasting comfort

Supports long-wearing comfort with a plush, padded headband and pillow soft ear cushions.

Microsoft Teams

Microsoft Teams version to support an easy collaboration and communication with a dedicated Teams button for instant access to the Teams App.

Specifications

Weight	103 g
Weight	0.24 lb
Package weight	300 g
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	User guide; Headset; USB Type-C® to USB Type-A adapter; Travel case

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Boom mic length (ft)	0.44 ft
Boom mic length (mm)	135 mm
Boom mic rotation	280°
Button user controls	Call answer/end; Mute; Volume +/-; Microsoft Teams
Cable length	66.5 cm (inline module to headset); 90 cm (USB to inline module); 215 cm (total USB to headset)
Cable length (imperial)	3.85 ft (inline module to headset); 2.95 ft (USB to inline module); 7.05 ft (total USB to headset)
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Microsoft Teams
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm (BW3315/BW3325) and devices that support USB Type-C®
Compatible Operating Systems	Windows 11; Windows 10; macOS; Android™; iOS
Connection type	USB Type-A/C®
Connection type	Wired: USB Type-C®, USB Type-C®/A adapter, 3.5 mm audio
Country of origin	Made in China or Mexico
Datasheet photo 1	AHID/f9fd8d3e8a032fcb77611c54ae96c74c9dfe1682
Ear cushions	Artificial leather (surface material)
Ecolabels	TCO Certified
Headphone type	On-ear (monoaural)
Impedance	32 ohm
Management Software	Poly Lens
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Noise cancelling
Multiple order quantity	10
Nominal sound pressure level	94 dB SPL
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	8
Pallet dimensions	40 x 48 x 76.37 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 194 cm

Pallet weight	787.05 lb
Pallet weight	357 kg
Products per pallet	800
Products per pallet layer	100
Sensitivity (microphone)	11 dB SLR
Sensitivity (speaker)	3 dB RLR
Signal-to-noise ratio	>24 dB
Speaker bandwidth	20 Hz to 20 kHz
Speaker size	32 mm
UNSPSC code	43191638

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Communication & Collaboration

★ : Recommended

Poly Support Services

3 year Poly+ Blackwire Service	PBLKWIRE312 ★
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 29, 2025 7:56 AM UTC+0000