



# Poly Blackwire 5210 Monaural USB-A Headset (80R98AA)



## Overview

### Wear it well

The Blackwire 5200 Series fits your busy workday. Ergonomically designed for long lasting comfort. And with the easy-to-use connectivity you can work on a variety of devices throughout the day.

### Get great sound

When you can hear and be heard clearly, you get more work done. Tune out the inevitable workplace distractions with a headset full of features – soft, conforming ear cushions that provide passive noise canceling and a precisely tuned microphone masks nearby conversations.

### Enjoy long lasting comfort

Your ears will thank you, especially after long conference calls. This headset is built to stay comfortable. Adjust it to fit the way you work. Need to move locations? The headset folds up for easy portability in the carrying case.

# Features

## Connectivity options

Select the right option for your device: USB-A or USB Type-C® for PC and 3.5 mm for mobile connectivity.

## Wearing style

Monaural wearing style for those who prefer to leave one ear open.

## Audio quality

Premium PC wideband audio with noise-canceling microphone and Digital Signal Processing (DSP) for a more natural voice sound.

## Comfort and durability

Ultra-soft leatherette ear cushion(s) wrapped around pillow-soft memory foam provide long lasting comfort. A lightweight cushioned metal headband offers durability and a comfortable custom fit.

## Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

## Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

---

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Dynamic EQ optimized; Noise cancellation (NC); Dynamic mute alert; Digital signal processing (DSP)
<b>Boom mic rotation</b>	280°
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-
<b>Cable length</b>	116 cm (inline module to headset); 94 cm (USB to inline module); 217 cm (total USB to headset)
<b>Cable length (imperial)</b>	3.81 ft (inline module to headset); 3.08 ft (USB to inline module); 7.12 ft (total USB to headset)
<b>Certified collaboration software</b>	Skype for Business; Microsoft Teams; Zoom; Cisco Jabber; Works With Chromebook Certified; Avaya
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
<b>Compatible Operating Systems</b>	macOS; Windows
<b>Connection type</b>	USB Type-A; 3.5 mm audio
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (monoaural)
<b>Impedance</b>	32 ohms
<b>Management Software</b>	Poly Lens
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone bandwidth</b>	100 Hz to 10 kHz
<b>Microphone type</b>	Omnidirectional
<b>Minimum System Requirements</b>	USB Type-A port
<b>Sensitivity (microphone)</b>	-38 dBV/Pa
<b>Sensitivity (speaker)</b>	90 dB
<b>Signal-to-noise ratio</b>	>118 dB
<b>Speaker size</b>	28 mm
<b>Special features</b>	Adjustable headband
<b>UNSPSC code</b>	43191638
<b>What's in the box</b>	Quick start guide; Warranty card; Carrying case; Headset

---

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and

*controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 year Poly+ Blackwire Service	<b>PBLKWIRE312 ★</b>
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

# Hybrid Work Solutions

## Audio

★ : Recommended

### Audio Accessories

Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3200 USB-A Inline Controls	85R03AA
Poly Blackwire 3200 USB-C Inline Controls	85R04AA
Poly Blackwire 3300 Case	85R06AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 USB-A Inline Controls	85Q62AA
Poly Blackwire 5200 USB-C Inline Controls	85Q64AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 7225 Case	85Q69AA
Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 12, 2023 5:27 AM UTC+0000