



SPECIFICATIONS

Panel Size	23.8" (60cm)
Active Display Area (mm)	527.04(H) x 296.46(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.2745(H) x 0.2745(V)
Aspect Ratio	16:9
Brightness (nits)	300
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	55.3~200 KHz(H) /48~180 Hz(V)
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	1ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	N/A
Video ports	1x Display Port (1.2a) 2x HDMI™ (2.0b)
USB ports	N/A
Audio ports	1x Earphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	91% / 88% / 118%
Surface Treatment	Anti-glare
Display Colors	16.7M
Power Type	External Adaptor 12V 3A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	541.9 x 231.9 x 424.3 mm 541.9 x 59.7 x 322.3 mm (Without stand)
Carton Dimension (W X D X H)	622 x 160 x 409 mm (WW carton) 637 x 174 x 433 mm (JP carton)
Frameless Design	Yes

FEATURES



Rapid IPS

Provides 1ms GTG fast response time, optimizes screen colors and brightness.



180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Console Mode - FHD only

Best solution for console users: FHD@120Hz



Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.

PIP / PBP Function	N/A
VESA Mounting	75 x 75 mm
Weight (NW / GW)	4.2 kg / 5.6 kg 2.7 kg (without stand)
Note	Display Port: 1920 x 1080 (Up to 180Hz) HDMI™: 1920 x 1080 (Up to 180Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-way joystick navigator
2. 2 x HDMI™ (2.0b)
3. 1 x Display Port (1.2a)
4. Headphone out
5. DC jack
6. Kensington lock