
## HL-EX415DW





# Low total cost of ownership, advanced security features, and reliable business performance

## **Enterprise Monochrome Laser Printer**

The Brother HL-EX415DW is a great choice for mid to large-sized workgroups that need fast, high-quality output, a low total cost of ownership, scalable paper handling, and advanced security features.

- Fast printing up to 52ppm<sup>1</sup>
- Includes 25,000-page toner cartridge for built-in value.
   Low total cost of ownership using 25,000-page toner cartridge<sup>13</sup>
- Enterprise level security features
- 620-sheet paper capacity<sup>8</sup>, expandable up to 2,700 sheets with tower tray option<sup>15</sup>
- Gigabit Ethernet and dual band (2.4GHz / 5GHz) wireless networking

# HL-EX415DW





### **Specifications:**

Print	
Print Technology	Electrophotographic Laser
Print Speed (max.) <sup>1</sup>	Up to 52ppm
Time to First Page <sup>2</sup>	Less than 6.7 seconds
Print Resolution (max.)	Up to 1200 x 1200 dpi
Print Emulations	PCL6, BR-Script3 <sup>3</sup> , IBM Proprinter XL, Epson FX-850, PDF Version 1.7, XPS Version 1.0
<b>Connectivity &amp; Compatibility</b>	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
USB Host	Front: Print from USB memory stick; external card reader Back: Store secure print jobs and macros / streams; external card reader
Operating Systems Compatibility <sup>4</sup>	Windows 10 Home, 10 Pro, 10 Education, 10 Enterprise, 11 Home, 11 Pro, 11 Education, 11 Enterprise; Windows Server 2012, 2012 R2, 2016, 2019, 2022 mac0S v11, v12, v13 Chrome 0S, Linux, Windows Universal Print Driver
Mobile Device Compatibility⁵	AirPrint®, Mopria™, Brother Mobile Connect, Wi-Fi Direct®
Cloud Services (Web Connect) <sup>6</sup>	Google Drive $^{\intercal M}$ , Evernote $^{\circledast}$ , OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps <sup>7</sup>	Cloud Secure Print; Attach, Email, and Print
Security	
Security Features	Integrated NFC Card Reader, External Card Reader Compatibility, Active Directory, LDAP, Secure Function Lock, Enterprise Security (802.1x), Secure Print, TLS/SSL, IP Filter, IPSec, Syslog Reporting, SNMP v3, Secure BIOS,
Paper Handling	
Paper Input Capacity (max.) <sup>8</sup>	520-sheet paper tray, 100-sheet multipurpose tray
Optional Input Capacity (max.)8	2,700 sheets via optional tower tray
Output Capacity (max.)8	250 sheets (face down), 10 sheets (face up)
Optional Output Capacity (max.)8	1,050 sheets via optional mailbox / sorter / stacker
Paper Sizes (max.)	Paper Tray: Letter, Legal, Executive, A4, A5, A6 Multipurpose Tray: 3.0" - 8.5" (W), 5.0" - 14" (L)
Media Types	Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 20)
Media Weights <sup>9</sup>	Standard Paper Tray: 16 to 43 lbs. Multipurpose Tray: 16 to 60 lbs.
General	
Automatic Duplex Capability	Print (default setting)
Display	3.5" Color Touchscreen
Processor	1.2 GHz
Memory (std. / max.)	1GB / 1GB; USB memory stick (optional)
Included Software <sup>10</sup>	Brother iPrint&Scan (desktop) for Windows and Mac <sup>®</sup> Brother Mobile Connect for iOS <sup>®</sup> and Android™
Included Brother Value Added Services	Secure Print+, Barcode Print+, ThinPrint Client, Remote Panel, Request Help, Order Supplies
Optional Solutions	Kofax ControlSuite, PaperCut, nddPrint, uniFLOW
Maximum Monthly Duty Cycle <sup>11</sup>	Up to 160,000 pages
Recommended Monthly Volume <sup>12</sup>	Up to 16,000 pages
Warranty	1-year limited warranty

#### **Replacement Supplies & Optional Accessories:**

TN920	Standard Yield Toner Cartridge (3,000 pages) <sup>13</sup>	
TN920XL	High Yield Toner Cartridge (6,000 pages) <sup>13</sup>	
TN920XL 2PK	High Yield Toner Cartridge Twin-Pack (6,000 pages/Cartridge) <sup>13</sup>	
TN920XXL	Super High Yield Toner Cartridge (11,000 pages) <sup>13</sup>	
TN920UXXL	Ultra High Yield Toner Cartridge (18,000 pages) <sup>13</sup>	
TNE90	Max Yield Toner Cartridge (25,000 pages) <sup>13</sup>	
DR925	Drum Unit (75,000 pages) <sup>14</sup>	
LT-5505	Optional 250-Sheet Capacity Paper Tray <sup>8</sup>	
LT-6505	Optional 520-Sheet Capacity Paper Tray <sup>8</sup>	
TT-4000	Optional Tower Tray with Stabilizer (520-sheet capacity x 4 trays) <sup>8</sup>	
SF-4000	Optional Stapler Finisher	
SR-100	Replacement Staple Cartridge (10,000 staples)	
MX-4000	Optional 4-bin Mailbox / Sorter / Stacker	
CB-2000	Optional 15.7" Printer Cabinet / Stand	
CH-1000	Optional Card Reader Holder	

#### **Dimensions / Weights:**

Unit Dimensions / Weight	15.8" (W) x 15.6" (D) x 12.6" (H) / 29.6 lbs
Carton Dimensions / Weight	19.6" (W) x 19.4" (D) x 17.1" (H) / 35.8 lbs.

#### **Carton Contents:**

Brother HL-EX415DW, TNE90 Toner Cartridge (25,000 pages)<sup>13</sup>, DR925 Drum Unit (75,000 pages)14, AC Power Cord, USB Port Cover, Quick Setup Guide



At your side support. One-year limited warranty with free online, live chat, or phone technical assistance for the life of your product.



#### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, Act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

















- Based on one-sided printing. Change from default setting required.
   From ready mode and standard tray.
   PostScript\*3™ compatible.
   For the latest OS compatible.
   Requires in the sort of AirPrint. Mac printer drivers are not provided.
   Requires connection to a wireless network.
   Requires an Internet connection and an account with desired service.
   Requires an Internet connection.
   Maximum capacity based on using 20 lb. paper.
   Half speed and straight paper output with more than 28 lb. paper.
   Maximum capacity based on Compatibility may vary by device and operating system.
   Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- 1 Based on one-sided printing. Change from default setting required.
  2 From ready mode and standard tray.
  2 From ready mode and standard tray.
  4 For the latest OS compatibility and to download drivers, visit support brother com. Printing via macOS requires the use of AirPrint. Mac printer drivers are not provided.
  5 Requires connection to a wireless network.
  6 Requires an Internet connection and an account with desired service.
  7 Requires an Internet connection.
  8 Maximum capacity based on using 20 lb, paper.
  9 Half speed and straight paper output with more than 28 lb, paper.
  10 May require free download. Compatibility may vary by device and operating system.
  11 Maximum number of printed pages promoth can be used to compare designed durability between the compare designed durability between the compared designed to the c