

HP OfficeJet Pro 8139e All-in-One Printer (40Q51A)



Print at home like a Pro. Fax included.

Say hello to the professional color inkjet printer for your home office from the World's #1 Printer Company, paired with the easiest-to-use print app. Enjoy easy printing designed to make you succeed at work. Fax included.[1,2]



Reliable technology uniquely built to work at home

Say goodbye to noisy printing and stay focused on your work with quiet mode.

Print from your couch with the best print app[2]

Print, scan, copy, or fax right from your smartphone with the best and easiest-to-use print app. [2]

Always be ready to print. Never run out of ink.[6]

With an Instant Ink subscription, you can get ink delivered directly to your door before you run out.[6]

Specifications

Print Resolution Technologies	HP Thermal Inkjet
Print quality black (best)	1200 x 1200 rendered dpi
Print quality color (best)	Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Print speed black (ISO, A4)	Up to 20 ppm
Print speed black (ISO, letter)	Up to 20 ppm
Print Speed Color (ISO)	Up to 10 ppm
Print speed color (ISO)	Up to 10 ppm
Print speed	Print speed up to 20 ppm (black) and 10 ppm (color)
Functions	Print, copy, scan, fax
Duplex printing	Automatic (standard)
Duty cycle (monthly, A4)	Up to 20,000 pages
Duty cycle (monthly, letter)	Up to 20,000 pages ^[7]
Printer smart software features	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On
Scanner advanced features	OCR (Optical Character Recognition); Smart Tasks shortcuts: 1-click customizable scan to cloud destinations, email, and print, create editable, searchable documents by scanning from phone or printer; Smart Tasks destinations: Dropbox, Google Drive, One drive, email recipients
Fax smart software features	Fax and Digital Fax - Fax to PC is available with Windows (Please use: Visit http://www.hp.com/support to download the latest software.
Energy savings feature technology	Schedule On and Schedule Off; HP Auto-On/Auto-Off Technology; HP Auto-Off Technology
Replacement cartridges	HP 923 Black Original Ink Cartridge (~500 pages) 4K0T3LN; HP 923 Cyan Original Ink Cartridge (~400 pages) 4K0T0LN; HP 923 Magenta Original Ink Cartridge (~400 pages) 4K0T1LN; HP 923 Yellow Original Ink Cartridge (~400 pages) 4K0T2LN. HP EvoMore planned to be available April 2024: HP 923e EvoMore Black Original Ink Cartridge (~1,000 pages) 4K0T7LN; HP 923e EvoMore Cyan Original Ink Cartridge (~800 pages) 4K0T4LN; HP 923e EvoMore Magenta Original Ink Cartridge (~800 pages) 4K0T5LN; HP 923e EvoMore Yellow Original Ink Cartridge (~800 pages) 4K0T6LN. Actual yield varies considerably based on content of printed pages and other factors. For details, see https://www.hp.com/go/learnaboutsupplies
Supplies feature	HP Instant Ink eligible
Connectivity, standard	1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band); 2 RJ-11 Fax/Modem port/phone line
Modem	Synaptics Troy modem; data rate up to 33.6 kbps
Network capabilities	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n/ac
Wireless capability	Yes, with built-in dual-band Wi-Fi 802.11 a/b/g/n/ac and a self-heal solution
Mobile printing capability	Chrome OS; HP Smart app; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified
Network protocols, supported	Supported Network Protocols configurations (IPv4, IPv6); DHCPv4, DHCPv6; DHCP options: 81/RFC4702/RFC4704, 12-Hostname; 44; LLMNR; Bonjour/mDNS; LP/ APIPA (Auto IP); NetBIOS/WINS; Port9100; DNS Resolver; SNMPv1/v2; Web Services Discovery; Web Services Print; SSL/TLS (HTTPS); Password-protected network Embedded Web server; Enable/disable network ports & device features, 802.1x wireless authentication (EAP-TLS, LEAP, and PEAP) & 802.1x Wired
Software included	HP Printer Software
Compatible Operating Systems	Windows 11; Windows 10; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; Linux; Chrome OS (Windows Server 2016 64-bit, Windows Server 2019 64-bit, Windows Server 2022 64-bit; Linux (For more information see http://developers.hp.com/hp-linux-imaging-and-printing))
Technical features	Borderless Printing; Automatic two-sided printing; Wireless; Wireless Direct; AirPrint; Touchscreen; ADF
Sustainable impact specifications	Forest First product with HP+; FSC Certified Packaging; Contains ocean-bound recycled plastic; 45% post-consumer recycled plastic; Recyclable through HP Planet Partners
Energy star certified	Yes
Ecolabels	EPEAT® registered
Blue Angel compliant	No, please refer to the ECI (Ecolabel Comparison Information) document
Copy speed black (best, A4)	Up to 3 cpm

Copy speed black (best, letter)	Up to 3 cpm
Copy speed color (best, A4)	Up to 2 cpm
Copy speed color (best, letter)	Up to 2 cpm
Digital sending standard features	Scan to Email; Scan to USB; Scan to Computer
Fax Resolution Black (best)	300 x 300 dpi
Faxing	Yes, color
Scan speed (normal, A4)	Up to 8 ppm (200 ppi, b&w), up to 3.5 ppm (200 ppi, color)
Scan speed (normal, letter)	Up to 8 ppm (200 ppi, b&w), up to 3.5 ppm (200 ppi, color)
Scan file format	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
Scan input modes	Front-panel scan, copy, HP Software, EWS, Mobile apps
Scan technology	Contact Image Sensor (CIS)
Scanner type	Flatbed, 1-sided ADF
Display	2.7" (6.86 cm) Capacitive Touchscreen CGD (Color Graphic Display)
Minimum dimensions (W x D x H)	460.3 x 337.5 x 233 mm
Minimum dimensions (W x D x H)	18.12 x 13.29 x 9.17 in
Weight	8.0 kg
Weight	17.6 lb
Power consumption	4.45 watts (ready), 1.15 watts (sleep), 0.12 watts (manual-off) ^[3]
Power supply type	Internal (Built-in) Universal Power Supply
What's in the box	NA: HP 923 Setup Black Ink Cartridge; HP 923 Setup Cyan Ink Cartridge; HP 923 Setup Magenta Ink Cartridge; HP 923 Setup Yellow Ink Cartridge; Power Cord; Regulatory Flyer; Ink Caution Flyer; Setup Poster; Reference Guide; EMEA/AP DM: HP 924 Setup Black Ink Cartridge; HP 924 Setup Cyan Ink Cartridge; HP 924 Setup Magenta Ink Cartridge; HP 924 Setup Yellow Ink Cartridge; Power Cord; Regulatory Flyer; Ink Caution Flyer; Setup Poster; Reference Guide ^[8]
Manufacturer Warranty	One-year limited hardware warranty with option to extend to two-years with acceptance of HP+ Offer. For more info please visit us at http://support.hp.com . [9]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Based on 2022 Q4 shipments in the IDC Worldwide Quarterly Hardcopy Peripherals Tracker®, 2022 Q4 Release. Includes shipments of all printing devices (inkjet printers, laser printers, copiers and multifunction devices, including production units).

[2] Compared to OEM printing apps for the majority of top-selling, network-capable inkjet/laser printers and all-in-ones for the home and office, priced ≤\$450 USD. Printers selected by market share as reported by IDC Quarterly Hardcopy Peripherals Tracker – Final Historical CYQ1 2023. Claim based on research of printer manufacturer's print apps and Keypoint Intelligence hands-on testing and study commissioned by HP, July 2023. For details, please see: keypointintelligence.com/HPSmartapp. Requires HP app download available at www.hp.com/go/mobileprinting. Certain features are available in English language only, and may vary by printer model/country, and between desktop/mobile applications. HP reserves the right to introduce charges for use of functionality facilitated by the HP app. Internet access required and may not be available in all countries. HP account required for full functionality. Fax capabilities are for sending a fax only. List of supported operating systems available in app stores. See details at www.hpsmart.com.

[6] Based on plan usage, Internet connection to eligible HP printer, valid payment method, email address, and delivery service in your geographic area.

Technical Specifications Footnotes

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

[8] For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

