

PERFORMANCE

Processor

Intel® Core™ i7-13700, 16C (8P + 8E) / 24T, Max Turbo up to 5.2GHz, P-core 2.1 / 5.1GHz, E-core 1.5 / 4.1GHz, 30MB

Processor Sockets

1x FCLGA1700

Integrated Graphics

Integrated Intel UHD Graphics 770

Discrete Graphics

1x NVIDIA® RTX A3000 Laptop GPU 12GB

Chipset

Intel W680 Chipset

Memory

1x 32GB SO-DIMM DDR5-4800 Non-ECC

Memory Slots

Four DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[1]

Up to 128GB (4x 32GB DDR5 SO-DIMM)

PCIe® NVMe® Controller

Integrated NVMe controller

PCIe NVMe Drive

1x 1TB SSD M.2 2280 PCIe 4.0x4 Performance NVMe Opal

SATA Controller

Integrated SATA controller

SATA/SAS Drive

None

Storage Support^[2]

Up to 1x 2.5" HDD or SSD + 2x M.2 SSD

- 2.5" HDD up to 1TB
- 2.5" SSD up to 7.68TB
- M.2 SSD up to 4TB each

Audio Chip

High Definition (HD) Audio, Realtek® ALC897-Q codec

Power Supply

300W 90% Adapter

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

Two PCIe slots with one PCIe 4.0 x16 and one PCIe 3.0 x8.

- Slot 1: PCIe 4.0 x16 (via MXM to PCIe riser card), low profile, 75W, double-width
- Slot 2: PCIe 3.0 x8 (x4 lanes), low profile, 25W

M.2 Slots

- Two M.2 PCIe Gen 4x4 slots (for SSD)
- One M.2 slot (for WLAN)

Bays

1x 2.5" disk bay (optional, comes with disk)

Dust Filter

None

Dimensions (WxDxH)^[3]

87 x 223 x 202 mm (3.43 x 8.78 x 7.95 inches)

Weight^[4]

3.6 kg (7.94 lbs, maximum configuration)

CONNECTIVITY

Onboard Ethernet

Intel I225-LM + I210-AT, 2x RJ-45, 2.5GbE + GbE

Optional Ethernet

None

WLAN + Bluetooth^[5]

Intel Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1, vPro®

Front Ports

- 2x Thunderbolt™ 4
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 4x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 3x DisplayPort™ 1.2
- 1x Ethernet (2.5GbE RJ-45)
- 1x Ethernet (GbE RJ-45)

Optional Rear Ports (configured)

None

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

Kensington® Security Slot™, 3 x 7 mm

Chassis Intrusion Switch

Chassis Intrusion Switch

MANAGEABILITY

System Management^[6]

Intel® vPro® Enterprise with Intel AMT 16

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite

CERTIFICATIONS

Green Certifications^[7]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 9.0

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

Mil-Spec Test

MIL-STD-810H military test passed

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

None

MODEL

TopSeller : Yes

Announce Date : 2023-12-04

EAN / UPC / JAN : 197531618252

End of Support : 2031-05-23



Product image is a sample, it may not match the real color of this model
· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to
<https://psref.lenovo.com/Detail/2235?M=30HA003FUS>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Recommended Services

BEST

4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39058)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference