

ThinkPad L14 Gen 4 (AMD)

Powered by AMD Ryzen 7 processors, the ThinkPad L14 Gen 4 (AMD) delivers fast and fluid performance for the modern workforce. Experience the most detailed and true-to-life colors possible with 72% NTSC color gamut and 1500:1 contrast ratio. Integrated with AMD Radeon graphics, this 14" device is capable of handling the most graphically demanding tasks, including video editing, 3D modelling and designing. Its all-day battery life and rapid charge support lets users' power through a day of meetings and offsite work.



With the AMD Wi-Fi 6E connectivity feature, get access to consistent and high-speed wireless connection from anywhere. The standard and optional connectivity ports including, USB-C 3.2 Gen 1 enable data transfer and seamless connectivity to external monitors and peripherals.

The 1080p FHD, IR camera uses a wide aperture to let in more light whereas the Dolby Audio stereo speakers delivers room-filling sound during video/audio calls.

Minimal preloaded applications mean maximum battery life and fast responsiveness for users.

Lenovo devices that are a class apart

The mid-range ThinkPad L Series offers enterprise docking, enhanced security features and optional remote management capabilities.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo USB-C Universal Business Dock

Features a universal USB-C connection that delivers effortless plug-and-play with most USB-C notebooks.

Has 11+ helpful expansion ports to optimize your workspace and workflow.

Enjoy lightning-quick data transfers, dual 4K monitors, and rapid charging for notebooks up to 65W.



PN: 40B30090xx

Lenovo Essential Wireless Keyboard & Mouse Combo

Simple design that is comfortable for all day use and tough enough to handle spills
 Convenient and easy to use wireless connection
 Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

ThinkPad L14 Gen 4 (AMD)

Performance

Processor

AMD Ryzen 3/5/7 PRO 7000 U Series

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Linux
Ubuntu Linux

Graphics

AMD Radeon Graphics (integrated)

Memory ¹

Up to 64GB DDR4-3200, 2x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage ²

Up to 1x 2TB M.2 2242 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Dolby Audio speakers
Dual-microphone array, far-field, Dolby Voice

Camera *

HD 720p, with privacy shutter
FHD 1080p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter

Battery ³

46.5Wh, 57Wh, or 63Wh battery, up to 14.12 hr
Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0
100W USB-C slim adapter, PD 3.0

Design

Display ⁴

14" HD (1366x768) TN Anti-glare 16:9
- 220nits, 45% NTSC, 60Hz

14" FHD (1920x1080) IPS Anti-glare 16:9
- 250nits, 45% NTSC, 60Hz
- 300nits, 45% NTSC, 60Hz, touch
- 400nits, 72% NTSC, low power, 60Hz

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, optional backlight

Touchpad

TrackPoint and Mylar surface touchpad
56 x 115 mm (2.24 x 4.53 inches)

Dimensions ⁵

Starting at 325.4 x 217 x 18.73 mm (12.81 x 8.54 x 0.74 inches)

⁵The system dimensions may vary depending on configurations.

Weight ⁶

Starting at 1.4 kg (3.09 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Thunder black

Case material

Aluminium (top), PC-CF (bottom)
Aluminium (top), PC-ABS (bottom)
PC-ABS (top), PC-CF (bottom)
PC-ABS (top), PC-ABS (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth* ^{7 8}

AMD Wi-Fi 6E RZ616, 802.11ax, Bluetooth 5.3*

⁷Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

⁸Bluetooth 5.3 operation requires Windows 11.

WWAN*

4G LTE CAT4 with embedded eSIM
4G LTE CAT16 with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB 3.2 Gen 1
1x USB 3.2 Gen 1 (Always On)
2x USB-C 3.2 Gen 2 (data, PD 3.0, DP 1.4)
1x HDMI 2.1, up to 4K/60Hz
1x microSD card reader
1x Headphone / microphone combo jack (3.5mm)
1x Ethernet (RJ-45)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via USB-C

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello*

Manageability

System Management*

DASH

Certifications

Green Certifications ^{9 10}

EPEAT Gold Registered*
ENERGY STAR 8.0*
ErP Lot 6
ErP Lot 26
TCO Certified 9.0
RoHS compliant

⁹The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

¹⁰EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country

Other Certifications

MIL-STD-810H