

PATH TO THE FUTURE

The Most Efficient & Professional Monitor The MSI PRO MP273QP WQHD monitor, with DisplayPort & HDMI interfaces, is optimized for the finest image and color quality with an IPS grade panel. It is designed for your programming, coding & website design workspace. It not only makes every line & detail clear for your projects but also lets you enjoy the smoothest streaming & online video experience.



Picture and logos

SELLING POINTS

- 27-inch IPS panel with 178° Wide Viewing Angle designed for a truly premium quality picture.
- Red Dot Design Award 2021 Winner – Match the décor of your home or office with the most elegant & stylish design.
- TÜV certified display ensures the protection and health of eyesight.
- MSI EyesErgo technology with Anti-Flicker technology helps prevent eye strain and fatigue.
- Less Blue Light PRO technology simultaneously protects the eyes and preserves vivid colors & details.
- MSI Eye-Q Check helps have self-check eyes & reminds to take a rest while using the monitor for a long time.
- The stand is designed with ergonomic features, including tilt, swivel, height, and pivot adjustments.
- Exclusive ergonomic software: MSI Productivity Intelligence (P.I.) brings the most intuitive and efficient productivity.
- The KVM function allows the seamless control of multiple devices using a single set of keyboard, mouse, and Modern MD272 series monitor.
- 100 Hz refresh rate provides a better viewing experience.
- Built-in USB Type-C connection with 65W power delivery allows you to connect to and charge your devices effortlessly.
- Maintain versatility across various devices by utilizing multiple input sources, such as Type-C, HDMI™, and DP ports.
- Enjoy the cleanest environment with a convenient and re ...



1. 1x DC Jack
2. 1x Type C (DP Alternate)
3. 1x DisplayPort (1.2a)
4. 1x HDMI™ (1.4b)
5. 1x Headphone-out
6. 1x USB 2.0 Type B
7. 2x USB 2.0 Type A

SPECIFICATION

Barcode Info	EAN	4711377089753
	UPC	824142320884
	UCC14	10824142320881
Model	Part No	9S6-3PB19H-093
	MKT Name	Modern MD272XP
	MKT Spec	Modern MD272XP
	Entity MKT Name	Modern MD272XP
	Color	ID1/Black-Black
Display	Screen Size	27" (69 cm)
	Active Display Area (mm)	597.888(H) × 336.312(V)
	Curvature	Flat
	Panel Type	IPS
	Resolution	1920x1080 (FHD)
	Aspect Ratio	16:9
	Dynamic Refresh Rate technology	FreeSync
	HDR (High dynamic range)	HDR Ready
	SDR Brightness (nits)	300
	Contrast Ratio	1000:1
	DCR (Dynamic Contrast Ratio)	100000000:1
	Signal Frequency	52.32~109 KHz (H) / 48~100 Hz(V)
	Refresh Rate	100HZ
	Response Time (MPRT)	1ms(MPRT)
	Response Time (GTG)	4ms
	View Angles	178°(H)/178°(V)
	Surface Treatment	Anti-glare
	NTSC (CIE1976 area percentage/overlap)	103%/83%
	NTSC (CIE1931 area percentage/overlap)	81%/75%
	sRGB (CIE1976 area percentage/overlap)	118%/99%
	sRGB (CIE1931 area percentage/overlap)	114%/99%
	Adobe RGB (CIE1976 area percentage/overlap)	101%/87%
	Adobe RGB (CIE1931 area percentage/overlap)	85%/77%
	DCI-P3 (CIE1976 area percentage/overlap)	94%/89%
	DCI-P3 (CIE1931 area percentage/overlap)	84%/83%
	Rec.709 (CIE1976 area percentage/overlap)	118%/99%
	Rec.709 (CIE1931 area percentage/overlap)	114%/99%
	Rec.2020 (CIE1976 area percentage/overlap)	67%/67%
	Rec.2020 (CIE1931 area percentage/overlap)	60%/60%
	Display Colors	16.7M
	Color bit	8 bits (6 bits + FRC)
	Note_DP	1920 X 1080 (Up to 100Hz)
	Note_HDMI™	1920 X 1080 (Up to 100Hz)
Note_DVI	N/A	
I/O Ports	HDMI™	1
	HDMI™ version	1.4b
	HDMI™ HDCP version	1.4
	DisplayPort	1
	DisplayPort version	1.2a
	DisplayPort HDCP version	2.2
	USB Type C (DisplayPort Alternate)	1
	Headphone-out	1
	Lock type	Kensington Lock
	Speaker	2
	USB 2.0 Type B	1
I/O Ports (Front)	USB 2.0 Type A	2
I/O Ports (Rear)	Card Reader	N/A

Power	Annual Energy Consumption (KWh)	17
	Power Type	External Adaptor 19V 5.79A
	Power Input	100~240V, 50/60Hz
	Energy Efficiency Rating	D
	Adapter's KC safety Number	HU10450-13034
	Power Cord Type	C5
	QC Output Power	N/A
	PD Output	Type C
	PD Output Power	65W
In The Box	3.5mm Mic Cable	0
	Switch Case	0
	Portable Screen Protection Case	0
	Monitor Hood	0
	Speaker (Accessories)	0
	DisplayPort Cable	0
	HDMI™ Cable	1
	DVI Cable	0
	USB Type A to Type B Cable	1
	USB Type C to Type A Cable	0
	USB Type C to Type C Cable	0
	Thunderbolt Cable	0
	VGA Cable	0
	3.5mm audio Cable	0
	3.5mm combo audio Cable	0
	Mouse Bungee Unit	0
	VESA Screw	4
	Power Cord	1
	AC Adaptor	1
	Warranty Card	0
Quick Guide	1	
Design	Adjustment (Tilt)	-5° ~ 20°
	Adjustment (Swivel)	-30° ~ 30°
	Adjustment (Height)	0 ~ 110 mm
	Adjustment (Pivot)	-90° ~ 90°
	VESA Mounting	75x75mm
Frameless Design	Yes	
Outer Carton Dimension (WxDxH)	Outer Carton Dimension (WxDxH) (inch)	N/A
Product Dimension with Stand (WxDxH)	Product Dimension with Stand (WxDxH) (mm)	613.5 x 200.8 x 413.3
	Product Dimension with Stand (WxDxH) (inch)	24.15 x 7.91 x 16.27
Product Dimension without Stand (WxDxH)	Product Dimension without Stand (WxDxH) (mm)	613.5 x 57.5 x 362.5
	Product Dimension without Stand (WxDxH) (inch)	24.15 x 2.26 x 14.27
Stand Dimension (WxDxH)	Stand Dimension (WxDxH) (mm)	230.81 x 200.81 x 427.68
	Stand Dimension (WxDxH) (inch)	9.09 x 7.91 x 16.84
Dimension & Weight	Inside Carton Dimension (WxDxH) (inch)	N/A
	Weight (Net kg)	5.7
	Weight (Gross kg)	8.
Weight	Weight Without Stand (kg)	3.75
Warranty	Warranty	36M