



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.736(H) x 335.664(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	400
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	64.56~266.4 KHz(H) / 48~180 Hz(V)
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	1ms (GTG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive Sync
HDR Support	DisplayHDR 400
Video ports	1x Display Port (1.4a) 2x HDMI™ (2.0b) 1x Type-C (DP alt.) w/ PD 65W charging
USB ports	2 x USB 2.0 Type A 1 x USB 2.0 Type B
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	94%/98%/150%
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Power Type	External Adaptor
Power Input	100 ~ 240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-45° ~ 45°
Adjustment (Pivot)	0 ~ 130mm
Adjustment (Height)	-90° ~ 90°
Kensington Lock	Yes
Dimension (W x D x H)	613.5 x 196.5 x 402.1 mm 613.5 x 69.8 x 362.5 (without stand)
Carton Dimension (W X D X H)	WW carton: 847 x 145 x 491 mm Outer: 862 x 158 x 515 mm
Frameless Design	Yes

FEATURES



Rapid IPS

Provides 1ms GTG fast response time, optimizes screen colors and brightness.



WQHD High Resolution

Game titles will even look better, displaying more details.



180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Quantum Dot

Provide accurate color imagery and support a cinema-standard DCI-P3 color gamut.

VESA CERTIFIED



VESA Certified DisplayHDR 400

Provide eye-catching detail through contrast and shadows adjustment.

DisplayHDR



KVM

Control multiple devices via one set of keyboard, mouse, and MSI gaming monitor.



Console Mode - FHD/2K

Perfectly support 120Hz at FHD resolution with next-gen consoles like PS5 and Xbox series X/S and QHD 2K Resolution PS5™ Optimization



Type-C 65W PD

Built-in an USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices.



Gaming Intelligence APP

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.

PIP / PBP Function	N/A
VESA Mounting	75x 75 mm
Weight (NW / GW)	6.05 kg / 13.3 kg 3.95 kg (without stand)
Note	DisplayPort: Display Port: 2560x1440 (Up to 180Hz) Type C: 2560x1440 (Up to 180Hz) and 65W PD charging HDMI™: 2560x1440 (Up to 144Hz) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard
Accessories	1x DisplayPort 1.4a 1.5M cable 1x C5 1.5M power cord

CONNECTIONS



1. 5-Way Joystick Navigator
2. DC Power Jack
3. Headphone Out
4. 2 x HDMI™ (2.0b)
5. DisplayPort (1.4a)
6. USB Type-C (PD65W)
7. USB 2.0 Type-B
8. 2 x USB 2.0 Type-A