

ThinkStation P3 Ultra

Business professionals can level up their work experience and performance with this 3.9-liter mini-tower powered by up to 13th Gen Intel Core i9 Processor. Enhance productivity with optional Wi-Fi 6E that enables faster connection speeds even in densely congested areas while with dual Thunderbolt 4 port, connect displays and share files at high speed. A slew of security features includes a discrete TPM 2.0 chipset, Kensington security slot, and BIOS security that keeps data well-protected.



Configured with up to 4TB of high-speed storage via 2x M.2 SSD modules and up to 128GB DDR5 memory, this device offers extreme portable power and enables users to multitask on compute-intensive workflows.

To view and compare detailed spreadsheets, professionals can connect to up to eight independent displays via an onboard Display Port, Thunderbolt, and discrete graphics.

EPEAT Gold, ENERGY STAR 8.0, TCO Certified 9.0, and ROHS compliant certification makes it an energy-efficient device.

Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- If a problem can't be fixed remotely, we will visit your location
- Normally next business day service
- Agreed appointment times



Accessories

Lenovo Go Wireless Numeric Keypad

- 21-key numeric keypad with industry-leading scissor switch keys
- Minimalist design with ultra slim profile at 13 mm with dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
- Rechargeable, up to 3 months use in single charge (may vary based on usage)



PN: 4Y41C33791, QY41C33979

Lenovo Essential Wireless Keyboard & Mouse Combo

- Simple design that is comfortable for all day use and tough enough to handle spills
- Convenient and easy to use wireless connection
- Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

ThinkStation P3 Ultra

Performance

Processor

Up to one 12th Gen Intel Core i5/i7/i9 processor or 13th Gen Intel Core i3/i5/i7/i9 processor, supports up to 24 cores, up to 5.8GHz

Operating System*

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Ubuntu Linux
Red Hat Enterprise Linux (certified only)

Graphics

Supports up to one NVIDIA RTX A5500 Laptop GPU

Chipset

Intel W680 chipset

Memory¹

Up to 128GB, 4 DDR5 SO-DIMM slots

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage²

Up to 1x 2.5" HDD + 2x M.2 SSD
• 2.5" HDD up to 1TB
• M.2 SSD up to 4TB each

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Design

Dimensions³

87 x 223 x 202 mm (3.43 x 8.78 x 7.95 inches)

³The system dimensions may vary depending on configurations.

Weight⁴

3.6 kg (7.94 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

Two onboard Ethernet, GbE and 2.5GbE
Additional Ethernet options via PCIe adapter

WLAN + Bluetooth⁵

Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1, vPro

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Security

Discrete TPM 2.0
Kensington Security Slot, 3x 7 mm
Chassis intrusion switch

Manageability

System Management⁶

Intel vPro Enterprise with Intel AMT 16.0*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications^{7 8}

EPEAT Gold Registered
ENERGY STAR 8.0
TCO Certified 9.0
RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications

MIL-STD-810H