



cTILE 22 Gen3

Commercial Chrome All-in-One



Features

- Ruggedized, metal design
- Front panel IP65 dust and water resistant
- 22" at 1920x1080 px (16:9)
- 250 nits, VA panel
- VESA compatible mount (100 x 100)
- Tamper proof, fanless, and solid-state design
- Glove touch support – Nitrile / Latex
- Supports Chrome Enterprise Upgrade, Chrome Education Upgrade, and Kiosk & Signage Upgrade



The next chapter of commercial-grade ChromeOS all-in-one computing is here with the cTILE 22 Gen3, where advanced technology meets compact design. This device integrates the Chromebox Commercial 3 with a 22" commercial-grade touchscreen, enclosed in a compact '2 in 1' form factor. With a sleek aluminum build, this compact solution offers robust connectivity and a fanless design for a reliable computing, kiosk, or digital signage experience. Step into the next chapter of reliable, ChromeOS all-in-one computing.

cTILE 22 Gen3



Model name		cTILE 22 Gen3
Housing Material		Metal
Dimensions	W x H x D (mm)	525.4 x 332 x 56.7 mm
	W x H x D (inch)	20.7 x 13.1 x 2.23 inch
Weight	Net Weight	8.54 kg / 18.8 lb
	Gross Weight	9.73 kg / 21.45 lb
CPU		Intel® Celeron
Memory		4GB
Graphics		Intel HD graphic, integrated on CPU
Front Panel	Resolution	22" 1920 x 1080 (16:9)
	Maximum Brightness	250 nits
	Panel Type	VA
	Viewing angle	178°/178°
	Response time	22ms
	Contrast Ratio	1000:1
	Touch	PCT (10 points)
Audio		Audio combo jack x1
LAN		WIFI 6E 802.11 b/g/n/ac/ax + BT5.2, dual band

Storage		EMMC 64G
Security		Google TPM, Kensington lock
Rear Panel IO	Power Button	x 1 (Hidden type)
	DC Jack	x 1
	HDMI Out Port	-
	USB 3.2 Port	x 2
	TYPE C	x 1
	Audio Set	Audio Combo Jack x 1
	Line-Out Mic-in	
Others	Recovery button x 1	
IP Grade		Front IP65 / Rear IPX2
Adapter		90W
Input Voltage		DC19V
Warranty		1 year
Others		Glove touch support (Nitrile / Latex)
Environment		
MTBF		50000 hours
Operating Temperature		0 ~ 40°C (32 ~ 104°F)
Storage Temperature		-20 ~ 60°C (-4 ~ 140°F)
Relative Humidity		90% RH max

Supports:

