


Model Name		RNUC13L3HV70000UI	
ASUS® NUC 13 Pro Tall Barebone Kit			
OS		Supports Windows® 11 Home/Pro, Windows® 10 IOT Enterprise	W/O OS
CPU		Intel® Core™ i7-1370P Processor vPro support (24M Cache, P-core up to 5.20 GHz / E-core up to 3.90 GHz)	cTDP 28W
Chipset		Integrated - Intel® SoC	
Graphics		Integrated - Intel® Iris® Xe Graphics	
Memory	Installed	n/a	
	Supported	2 x SO-DIMM DDR4-3200MHz memory slots	Max. 64GB
Storage	Installed	n/a	
	Supported	1 x M.2 2280 PCIe G4x4 NVMe™ SSD (supports 128GB ~ 8TB) 1 x M.2 2242 PCIe G3x1 or SATA SSD (supports 256GB ~ 1TB) 1 x 2.5-inch SATA 6Gb/s support for HDD (supports up to 4TB)	Key type M Key type B
Wireless Network		Intel® Wi-Fi 6E AX211 (Gig+, 2x2, and Bluetooth® 5.3 vPro support	(M.2 2230)
LAN		1 x Intel® i226-LM LAN (10/100/1000/2500 Mbps) vPro support	2.5 GbE
Wake-on-LAN Support		Wake on from S5 & Modern Standby	
Optical Drive		n/a	
Integrated Speaker		n/a	
Audio		Realtek® ALC269, 2 channels	
Card Reader		n/a	
TPM		dTPM 2.0 (Discrete Hardware)	
Chassis Intrusion Detection		n/a	
HDMI CEC		Onboard Yes, on both HDMI	
Interface	Front I/O	1 x USB 3.2 Gen2 Type-A (with BC1.2 5V/0.9A, 10Gbps) 1 x USB 3.2 Gen2 Type-A (5V/0.9A, 10Gbps) 1 x 3.5mm Audio Jack (Line out/Mic in/Headphone out)	
	Side I/O	1 x Kensington Lock Slot	
	Rear I/O	2 x Thunderbolt™ 4 (with DP1.4 5V/3A, 40Gbps) 1 x USB 3.2 Gen2 Type-A (5V/0.9A, 10Gbps) 1 x USB 2.0 Type-A (5V/0.5A, 480Mbps) 2 x HDMI 2.1 (with TMDS, up to 4K@60Hz) 1 x Intel® 2.5G LAN (RJ45) 1 x Cable Locking Arm 1 x DC-in <i>Supports up to four 4K@60Hz displays simultaneously (2 x HDMI + 2 x TB4)</i>	
Physical	Dimensions	4.61" x 4.41" x 2.13" 117 x 112 x 54mm	(0.7L)
	Weight	1.30 lbs. 0.59 kg	
Power Supply		120W Power Adapter	
Power Cord		US Cord for USA	
Accessories		VESA Mount & Screws / AC Power Adapter / Power Cord	