



# 24B3HA2

**High-performance clarity with 23.8" FHD monitor featuring 100Hz refresh rate and HDMI**

Dive into the extraordinary world of crystal-clear visuals and vibrant colors with our solid 24-inch FHD IPS Monitor. Elevate your viewing experience to new heights as every detail comes alive on the compact screen, making your content truly immersive. Experience smooth 100Hz refresh rate, ensuring each frame is a visual delight. No more lag or motion blur – just pure and clear for eye pleasure. The 1ms MPRT takes your working experience to the next level, making fast-paced scenes sharper and more exhilarating. 24B3HA2 isn't just about visuals; it's a feast for your ears too. Enjoy rich sound with built-in 2W speakers, turning every movie night or watching multimedia session into action which can fulfil basic audio needs without the need for additional audio equipment. Sleek and stylish narrow borders provide you with more screen real estate, featuring a 9.5mm ultra-narrow chin that is almost half as thin as standard monitors. Lastly, the low blue light feature ensures your eyes stay fresh during extended use. This is a statement piece for your setup.

GENERAL	
Model Name	24B3HA2
Channel	B2C
Product line	Basic-line
Design family	B3

## SCREEN

Screen size (inch)	23.8
Screen size (cm)	60.5
Flat / Curved	Flat
Display hardness	3H
Panel treatment	Antiglare (AG)
Panel resolution	1920x1080
Resolution name	FHD
Aspect ratio	16:9
Panel type	IPS
Backlight type	WLED
Max Refresh rate	100 Hz
Response time GtG	4 ms
Response time MPRT	1 ms
Static contrast ratio	1300:1
Dynamic contrast ratio	20M:1
Viewing angle (CR10)	178/178
Display colours	16.7M (6bits+FRC)
Brightness in nits	250 cd/m2
Pixel Pitch (mm)	0.2745
Pixels per Inch	93

## EXTERIOR

Bezel type (front)	Ultra Narrow
Bezel Colour (front)	Black
Bezel finishing (front)	Texture
Cabinet colour (backside)	Black
Cabinet finishing (backside)	Texture

## ERGONOMICS

Vesa wallmount	100x100
Tilt	Retrieving data. Wait a few seconds and try to cut or copy again.

**CONNECTIVITY AND MULTIMEDIA**

HDMI	HDMI 1.4 x 1
Digital HDCP (HDMI version)	HDCP 1.4
RJ45	No
D-SUB (VGA)	1x
DVI	0x

**MULTIMEDIA**

Speakers	✓
Speaker power	2 W x 2
Audio Output	1x Audio out

**FEATURES**

Sync technology (VRR)	Adaptive Sync
Flicker-Free	Flicker Free
Kensington Lock	✓
Colour space (sRGB) CIE 1976 %	95.2
Colour space (DCI-P3) CIE 1931 %	73.8
Colour space (DCI-P3) CIE 1976 %	73.8
Colour space (Adobe RGB) CIE 1931 %	74.2
Colour space (Adobe RGB) CIE 1976 %	81.6

**SUSTAINABILITY**

Energy star	Energy star 8
-------------	---------------

**POWER / ENVIRONMENTAL**

Power supply	Internal
Power source	100 - 240V 50/60Hz
Power consumption standby in watts	0.5
Power consumption off in watts	0.3
Energy class	E

**PRODUCT DIMENSIONS (METRIC)**

Product dimensions incl. base (WxHxD) mm	542.4 x 412.1 x 202.3
Product dimensions excl. base (WxHxD) mm	542.4 x 316.2 x 44.6
Packaging dimensions (WxHxD) mm	614 x 126 x 394
Packaging dimensions (WxHxD) mm (CN)	614 x 126 x 394
Gross weight incl. package (in kg)	4.65
Product with stand (kg)	2.97
Gross weight incl. package (in kg) (CN)	4.65
Product without stand (kg)	2.65

**WHAT'S IN THE BOX**

HDMI cable	1.5
Power Cable	✓

**OTHER INFORMATION**

MTBF	50.000 hours
------	--------------