

Digital Signage Display

Sharp/ NEC MultiSync PN-ME652



- Seamless connectivity – native USB-C supports Bring Your Own Device workflows, safeguarding inclusion and boosting productivity, with a single cable connection between notebook and display.
- Quick input detection – removing potential frustration and smoothing the way to productive meeting outcomes, the display responds immediately when a device is connected.
- New feature-ready – regular OTA Android OS updates ensure availability of the latest features and system security.
- Best readability – aiding high productivity in well-lit meeting spaces, a high haze filter eliminates glare and reflections from windows and other light sources.
- Third-party compatibility – not simply a display, but an out-of-the-box solution, compatible with popular workplace and content management systems through the integrated SoC platform.

Specifications

DISPLAY MODULE DATA

Panel Technology	IPS with Direct LED backlights
Native Resolution (Pixels)	3840 x 2160
Diagonal Size (inches / cm)	65 / 163.9
Aspect Ratio	16:9
Backlight Technology	LED
Brightness (cd/m2)	450
Contrast Ratio	1200:1
Response Time (grey to grey avg) ms	8
Viewing Angle (H/V)0 CR >10	178 horizontal / 178 vertical (typ. at contrast ratio 10:1)
Colour Depth [bn]	1.073 (8bit + FRC)
Haze Level [%]	Standard (25)

POWER SUPPLY AND OPERATING ENVIRONMENT

Operating Voltage(ACV) / Frequency(Hz)	100-240 V AC; 50 / 60 Hz
Power Consumption (W) (Operating MAX)	140 shipping
Operating Temperature (oC)	0 to 40
Storage Temperature [°C]	-20 to 60
Humidity (%)	20 to 80
Storage Humidity [%]	10 to 90

INSTALLATION

Landscape	•
Portrait	•
Mounting (VESA/Number of Points/Pitch mm)	600 x 400 (FDMI); 4 holes

CONNECTIVITY (AUDIO/VIDEO) OUTPUT

HDMI	1
Audio/Headphone 3.5mm Jack	1

ACCESSORIES

Shipping Content	2x AAA batteries; Display; HDMI Cable; Power Cable; Remote Control; Setup Manual
Remote Control Transmitter	Yes
Power Cord	Yes
Mounting Bracket	Optional
Tabletop Stand	Optional
Battery	Yes

KEY SPECIFICATIONS

Special Characteristics	DICOM Simulation; HDMI ARC; Powered USB Port (15 W); Removable Logo
HDR High Dynamic Range	HDR10; HLG; PQ
Limited Manufacturer's Warranty (yrs.)	3
Built in Speakers (W)	10 W + 10 W
Power Management	•
Cabinet Colour	Black

WEIGHTS AND MEASURES

Bezel Size (L/R) mm	15.9
Bezel Size (U/L) mm	15.9
Product Dimensions (W/H/D) mm	1,463.3 x 838.2 x 68
Shipping Carton Dimensions (W/H/D) mm	1,628 x 942 x 185
Product Weight Without Stand (Kg)	23.7
Shipping Weight (Kg)	34.5

CONNECTIVITY (AUDIO/VIDEO) INPUT

HDMI	3
Audio 3.5mm Jack	1

CONNECTIVITY (CONTROL/SERIAL DATA)

RS232C IN	1
LAN Port	1
USB	4