



Surface Pro 10

An AI PC built for business, designed for versatility

Surface Pro 10 blurs the boundary between hardware and software for peak performance in a secured, lightweight device that adapts to any work style. Employees get the benefits of an AI PC that accelerates Microsoft Copilot* experiences and offers integrated AI engines that enable the next wave of business features.




Secure sign-in and authentication with Windows Hello for Business or the built-in NFC reader³

Anti-reflective technology and adaptive color on the PixelSense™ Flow touchscreen shifts the balance of color based on your environment, making your screen look vivid in almost any lighting condition



Inking that feels like pen on paper with Surface Slim Pen²



Simplified repairs with instructional QR codes built into the device. Clear icons inside identify the number of screws and driver types needed for key components⁴

A new era of workplace collaboration

Take advantage of seamless hardware and software symmetry with features that remove boundaries around how work happens.

Productivity realized with Microsoft Copilot*


Experience the productivity of Microsoft Copilot* with inclusive features only Surface can deliver through effortless touch gestures, voice commands, and Surface Slim Pen¹ inking.

Never-ending, on-the-go impact

Keep pace with the flow of business through relentless performance, durability, and portability.

Multi-layered security and manageability

Safeguard your sensitive data with industry-leading security and remote management that maintains control of sensitive data.



AI-enhanced 1440p ultrawide Surface Studio Camera that supports Windows Studio Effects and has a 114-degree field of view, the widest ever put into a Windows PC⁸

Up to 19 hours of battery life⁶ and supported fast charging⁷



Intel® Core™ Ultra processor with Intel® AI Boost and up to 64GB of RAM⁵

*Copilot in Windows (in preview) is available in select global markets and will be rolled out to additional markets over time. ¹Learn more. Copilot with commercial data protection is available at no additional cost for users with an Entra ID with an enabled, ²eligible Microsoft 365 license. Copilot for Microsoft 365 sold separately and requires a qualifying volume license or subscription - ³Microsoft Copilot for Microsoft 365 | Microsoft 365. ⁴Sold separately. Software license required for some features. ⁵NFC is available on Wi-Fi configurations of Surface Pro 10. ⁶Replacement components available through Surface Commercial authorized device resellers. Components can be replaced on-site by a skilled technician following Microsoft's Service Guide. Microsoft tools (sold separately) may also be required. Availability of replacement components and service options may vary by product, market and over time. See ⁷Surface service options - Surface | Microsoft Learn. Opening and/or repairing your device can present electric shock, fire and personal injury risks and other hazards. Use caution if undertaking do-it-yourself repairs. Unless required by law, device damage caused during repair will not be covered under Microsoft's Hardware Warranty or protection plans. ⁸System software uses significant storage space. Available storage is subject to change based on system software updates and apps usage. 1GB = 1 billion bytes. 1TB = 1,000 GB. ⁹Surface.com/Storage more details. ¹⁰Battery life varies significantly based on usage, network and feature configuration, signal strength, settings and other factors. See ¹¹aka.ms/SurfaceBatteryPerformance for details. ¹²In select markets, only specific configurations come with 39W Surface power supply. Fast charging is supported with minimum 45W Surface power supply or USB Type-C PD charger rated at 45W or higher, sold separately. Testing conducted by Microsoft in February 2024. For details on Fast Charging see - ¹³USB-C and Fast Charging for Surface - Microsoft Support. ¹⁴Based on a comparison of published tech specs for Windows laptops and 2:1s as of 2/20/24.



Surface Pro 10

PROCESSOR

Intel® Core™ Ultra 5 processor 135U
Intel® Core™ Ultra 7 processor 165U
NPU: Intel® AI Boost

MEMORY AND STORAGE¹

Memory options:
8GB, 16GB, 32GB, 64GB LPDDR5x

Storage options:
Removable² solid-state drive (Gen 4 SSD): 256GB, 512GB, 1TB

SECURITY

Hardware TPM 2.0 chip for enterprise-grade security and BitLocker support
Windows Hello facial recognition with Enhanced Sign-in Security
NFC authentication
Windows 11 Secured-core PC

BATTERY LIFE

Up to 19 hours of typical device usage³

PORTS AND CHARGING

2 x USB-C® with USB4®/Thunderbolt™ 4 with support for:
Charging
Data transfer
DisplayPort 2.1 with support up to 1 x 8K monitor
Supports fast charging with minimum 45W power supply via Surface Connect or USB-C®⁴
Surface Connect port
Surface Pro Keyboard port

CAMERAS

Quad HD front-facing Surface Studio Camera
1440p Quad HD camera with ultrawide field of view
Windows Studio Effects with automatic framing, eye contact, and background blur
10.5 MP Ultra HD rear-facing camera
Windows Hello face authentication camera

SIZE AND WEIGHT^{5, 6}

Length: 11.3 inch (287 mm)
Width: 8.2 inch (208.6 mm)
Height: 0.37 inch (9.3 mm)
Weight: 1.94 lbs (879 g)

SOFTWARE

Windows 11 Pro or Windows 10 Pro⁷
Preloaded Microsoft 365 Apps⁸
Microsoft 365 Business Standard, Microsoft 365 Business Premium, or Microsoft 365 Apps 30-day trial⁹

AUDIO

Dual Studio Mics with voice focus¹⁰
2 W stereo speakers with Dolby® Atmos®¹¹
Support for Bluetooth® LE Audio

DISPLAY

Touchscreen: 13" PixelSense™ Flow display¹²
Resolution: 2880 x 1920 (267 PPI)
Aspect ratio: 3:2
Contrast ratio: 1300:1
Refresh rate: up to 120Hz (Dynamic refresh rate supported)
Color profile: sRGB and Vivid
Individually color-calibrated display
Adaptive color
Touch: 10-point multi-touch
Dolby Vision IQ™ support¹³
Touch: 10-point multi-touch
Corning® Gorilla® Glass 5
Anti-reflective
Brightness: SDR 600 nits maximum (typical)

SERVICEABILITY

Replacement components:¹⁴

- Display module
- Removable solid-state drive
- Battery
- Motherboard (including main processor and main memory)
- Surface Connect
- Thermal module
- Microphone module
- Solid-state drive door
- Speakers
- Enclosure (bucket)
- Front camera
- Rear camera
- Power and volume buttons
- Kickstand
- Device entry kit

ACCESSIBILITY

Compatible with the Surface Pro Keyboard with bold keyset¹⁵
Compatible with Surface Adaptive Kit
Compatible with Microsoft Adaptive Accessories
Includes Windows Accessibility Features – Learn More [Accessibility Features | Microsoft Accessibility](#)
Discover more Microsoft Accessible Devices & Products – [Accessible Devices & Products for PC & Gaming | Assistive Tech Accessories - Microsoft Store](#)

SENSORS

Ambient color sensor
Accelerometer
Gyroscope
Magnetometer
NFC

WHAT'S IN THE BOX

Surface Pro 10
39W Power Supply (In select markets, available only with specific configurations)
Quick Start Guide
Safety and warranty documents

BATTERY CAPACITIES⁵

Battery Capacity Nominal (Wh) 48
Battery Capacity Min (Wh) 47

EXTERIOR

Casing: Anodized aluminum
Colors:¹⁶ Platinum, Black
Physical buttons: Volume, Power

SUSTAINABILITY

More recycled materials
Enclosure is made with a minimum of 72% recycled content, including 100% recycled aluminum alloy and 100% recycled rare earth metals¹⁷

More energy efficient
ENERGY STAR® certified

WARRANTY¹⁸

1-year limited hardware warranty

PEN AND ACCESSORIES COMPATIBILITY

Pen compatibility:
Designed for Surface Slim Pen¹⁹
Integrated storage and wireless charging for Surface Slim Pen with Surface Pro Keyboard with pen storage¹⁹
Supports tactile signals with Surface Slim Pen¹⁹
Supports Microsoft Pen Protocol (MPP)

Keyboard compatibility:

- Surface Pro Keyboard
- Surface Pro Signature Keyboard
- Surface Pro X Signature Keyboard
- Surface Pro X Keyboard

KICKSTAND

Kickstand with 165 degrees full friction hinge

NETWORK AND CONNECTIVITY

Wi-Fi 6E: 802.11ax compatible²⁰
Bluetooth® Wireless 5.3 technology

GRAPHICS

Intel® Graphics

¹System software uses significant storage space. Available storage is subject to change based on system software updates and apps usage. 1GB = 1 billion bytes. 1TB = 1,000 GB. [Surface.com/Storage](#) more details. ²Solid State Drive (SSD) Retention is only available on Microsoft Surface devices in which the SSD is marketed as removable per the Technical Specifications. Solid State Drive (SSD) Retention is included in both Extended Hardware Service Plus and Microsoft Complete for Business Plus and is also available as an Optional Add-on when purchasing Microsoft Extended Hardware Service and Microsoft Complete for Business. Devices returned to a Solid State Drive (SSD) are subject to a Solid State Drive (SSD) replacement fee unless the device is enrolled in the Drive (SSD) Retention offer. ³Battery life varies significantly based on usage, network and feature configuration, signal strength, settings and other factors. See [aka.ms/SurfaceBatteryPerformance](#) for details. Testing conducted by Microsoft in February 2024 using preproduction Windows 11 software and preproduction Surface Pro 10 Intel® Core™ Ultra 7 processor 165U, 512GB, 16GB RAM devices. Testing consisted of full battery discharge with a mixture of active use and modern standby. The active use portion consists of (1) a web browsing test accessing eight popular websites over multiple open tabs, (2) a productivity test utilizing Microsoft Word, PowerPoint, Excel, OneNote and Outlook, and (3) a portion of time with the device in use with idle applications. Personalization colors set to Light mode for Windows and apps. All settings were default except screen brightness was set to 150 nits with auto-brightness and adaptive color disabled. Wi-Fi was connected to a network. Tested with Windows 11 Version 22H2.3085. Battery life varies significantly with settings, usage, and other factors. ⁴In select markets, only specific configurations come with 39 W Surface power supply, Fast Charging (from 5% to 80%) is supported with minimum 45W Surface power supply or USB-C® PD charger, sold separately. Testing was conducted at Microsoft in February 2024, using pre-production devices, software, and minimum of 45W USB-C® charger under controlled conditions. The device was powered on to the desktop screen with default display brightness settings. Actual charge time will vary based on operating conditions. Measured at typical office ambient temperature of 23C. ⁵Might vary depending on manufacturing processes. ⁶Weight not including Keyboard. ⁷Windows 10 is not available for purchase but is supported by Surface Pro 10. Visit [https://aka.ms/SurfaceSupportedOperatingSystems](#) for more information. ⁸Requires license or subscription (sold separately) to activate and use. ⁹Activation required. If your device is managed by your organization's IT department, contact your IT administrator for activation. After 30 days, you will be charged the applicable monthly or annual subscription fee. Credit card required. Cancel any time to stop future charges. See [https://aka.ms/m365businesstrialinfo](#). ¹⁰Voice focus requires activation, Windows 11 and is available in apps which use integrated device microphones and use certain Windows audio processing modes. ¹¹Requires Dolby® Atmos® encoded content/audio. ¹²Surface Pro 10 display has rounded corners within a standard rectangle. When measured as a standard rectangular shape the screen is 13" diagonally (actual viewable area is less). ¹³Requires Dolby Vision™ encoded content and video. ¹⁴Replacement components available through Surface Commercial authorized device resellers. Components can be replaced on-site by a skilled technician following Microsoft's Service Guide. Microsoft tools (sold separately) may also be required. Availability of replacement components and service options may vary by product, market and over time. See [Surface service options - Surface | Microsoft Learn](#). Opening and/or repairing your device can present electric shock, fire and personal injury risks and other hazards. Use caution if undertaking do-it-yourself repairs. Unless required by law, device damage caused during repair will not be covered under Microsoft's Hardware Warranty or protection plans. ¹⁵Surface Pro Keyboard with bold keyset is only in US English. ¹⁶Colors available on selected models only. Available colors, sizes, finishes, and processors may vary by store, market, and configuration. ¹⁷Enclosure includes Bucket and Kickstand. 100% recycled aluminum alloy in Bucket and Kickstand. 100% recycled rare earth metals in magnets. Based on validation performed by Underwriter Laboratories, Inc. using Environmental Claim Validation Procedure, UL 2809-2, Second Edition, November 7, 2023. ¹⁸Microsoft's Limited Warranty is in addition to your consumer law rights. ¹⁹Sold separately. ²⁰Wi-Fi 6E not available in all areas.