



Surface Laptop 6 for Business

Power and design in an AI PC, built for business workloads

Surface Laptop 6 elevates business with an elite level of performance, power, and sleek design. Built for demanding workloads, Surface Laptop 6 unleashes a new era of productivity through the power of the Intel® Core™ Ultra H-series processors. With Surface Laptop, employees get the benefits of an AI PC that accelerates Microsoft Copilot* experiences.

Relentless power for demanding workloads

Fuel productivity through a full workday with power and performance designed to keep pace with business.

Productivity realized with Microsoft Copilot*

Experience Copilot in Windows 11 Pro* and Microsoft Copilot for Microsoft 365¹ in ways only Surface can create, with detailed support for inclusive styles of work.

A sleek and durable Microsoft design

Surface Laptop 6 will surpass expectations: meticulously crafted, designed for longevity, and featuring collaborative tools and AI-driven features.

Multi-layered security and manageability

Windows 11's industry-leading security safeguards sensitive data, and remote management provides protection at every layer—hardware, firmware, application, cloud, and identity.



Intel® Core™ Ultra H-series processors with up to 2x faster performance⁴

Anti-reflective technology reduces reflections by up to 50%, to make it easier to see what's on screen in bright light and even outdoors

Up to 19 hours of battery life² and supported fast charging³

AI-enhanced 1080p HD Studio Camera with Windows Studio Effects

Secured-core PC designed to elevate the benefits of Windows 11 security

Optional integrated smart card reader on select models in select markets⁵


Multitasking with Surface Laptop 6 and Windows 11 Pro AI experiences, intelligent workflows, and unmatched personalization



New Copilot key⁶ for quick access to Copilot in Windows 11 Pro*

Simplified repairs and replaceable parts including the motherboard and battery⁷

Omnisonic® Speakers with Dolby® Atmos⁸ and dual Studio Mics with voice focus⁹



*Copilot in Windows (in preview) is available in select global markets and will be rolled out to additional markets over time. ¹Learn more. Copilot with commercial data protection is available at no additional cost for users with an Entra ID with an enabled, ²eligible Microsoft 365 license. ³Copilot for Microsoft 365 sold separately and requires a qualifying volume license or subscription - ⁴Microsoft Copilot for Microsoft 365 | Microsoft 365. ⁵Battery life varies significantly based on usage, network and feature configuration, signal strength, settings and other factors. See ⁶aka.ms/SurfaceBatteryPerformance for details. ⁷13.5" Surface Briggs comes with 39 W Surface power supply. Fast charging (from 5% to 80%) is supported with minimum 45W Surface power supply or USB-C® PD charger, sold separately. Testing was conducted at Microsoft in February 2024, using pre-production devices, software, and minimum of 45W USB-C® charger under controlled conditions. The device was powered on to the desktop screen with default display brightness settings. Actual charge time will vary based on operating conditions. Measured at typical office ambient temperature of 23C. ⁸Based on 3DMark TimeSpy benchmark measuring graphic performance compared to Surface Laptop 5. ⁹Integrated smart card reader available only on Surface Laptop 6 in Black in one of these configurations: 15" 5/16/512, 7/16/256, 7/16/512, 7/32/512 and only in US and Canada. ¹⁰Feature availability varies by market. See ¹¹aka.ms/WindowsAIFeatures. When Copilot for Windows is not available or enabled on the device, pressing the Copilot key will launch Windows Search. ¹²Replacement components are available through Surface Commercial authorized device resellers. Components can be replaced on-site by a skilled technician following Microsoft's Service Guide. Microsoft tools (sold separately) may also be required. Availability of replacement components and service options may vary by product, market and over time. See ¹³Surface service options - Surface | Microsoft Learn. ¹⁴Opening and/or repairing your device can present electric shock, fire and personal injury risks and other hazards. Use caution if undertaking do-it-yourself repairs. Unless required by law, device damage caused during repair will not be covered under Microsoft's Hardware Warranty or protection plans. ¹⁵Requires Dolby® Atmos™ encoded content/audio. ¹⁶Voice focus requires activation. Windows 11 and is available in apps which use integrated device microphones and use certain Windows audio processing modes.



Surface Laptop 6 for Business

PROCESSOR

Intel® Core™ Ultra 5 processor 135H
Intel® Core™ Ultra 7 processor 165H
NPU: Intel® AI Boost

MEMORY AND STORAGE¹

Memory options:
8GB LPDDR5 RAM, 16GB, 32GB or 64GB LPDDR5x RAM

Storage options:
Removable² solid-state drive (Gen 4 SSD): 256GB, 512GB, 1TB

SECURITY

Hardware TPM 2.0 chip for enterprise-grade security and BitLocker support
Windows Hello facial recognition with Enhanced Sign-in Security
Integrated smart card reader authentication (available on select models and markets)³
Windows 11 Secured-core PC

PORTS AND CHARGING

Surface Laptop 6 13.5”:

USB-C⁴ with USB4⁴/Thunderbolt™ 4 with support for:
- Charging
- Data transfer
- DisplayPort 2.1 with support up to 1 x 8K monitor*
Supports fast charging with minimum 45W power supply via Surface Connect or USB-C⁴
USB-A 3.1
3.5 mm headset jack
Surface Connect port

Surface Laptop 6 15”:

2 x USB-C⁴ with USB4⁴/Thunderbolt™ 4 with support for:
- Charging
- Data transfer
- DisplayPort 2.1 with support up to 1 x 8K monitor*
Supports fast charging with minimum 45W power supply via Surface Connect or USB-C⁴
USB-A 3.1
3.5 mm headset jack
Surface Connect port
Integrated smart card reader (available on select models and markets)³

BATTERY LIFE⁵

Surface Laptop 6 13.5”:

Up to 18.5 hours of typical device usage⁶

Surface Laptop 6 15”:

Up to 19 hours of typical device usage⁷

CAMERAS

Full HD front-facing Surface Studio Camera
1080p Full HD camera
Windows Studio Effects with automatic framing, eye contact, and background blur
Windows Hello face authentication camera

SIZE AND WEIGHT⁸

Surface Laptop 6 13.5”:

Length: 12.1 inch (308 mm)
Width: 8.8 inch (223 mm)
Height: 0.66 inch (16.7 mm)
Weight: 3.06 lbs (1.38 kg)

Surface Laptop 6 15”:

Length: 13.4 inch (340 mm)
Width: 9.6 inch (244 mm)
Height: 0.67 inch (16.9 mm)
Weight: 3.70 lbs (1.68 kg)
With smart card reader:³ 3.71 lbs (1.68 kg)

SOFTWARE

Windows 11 Pro or Windows 10 Pro⁹
Preloaded Microsoft 365 Apps¹⁰
Microsoft 365 Business Standard, Microsoft 365 Business Premium, or Microsoft 365 Apps 30-day trial¹¹

KEYBOARD LAYOUT

Activation: Moving keys
Layout: QWERTY, full row of function keys (F1 – F12)
Windows key and dedicated buttons for media controls, screen brightness
Keyboard backlight
Copilot key¹²
Touchpad

AUDIO

Dual Studio Mics with voice focus¹³
Omnisonic[®] Speakers with Dolby[®] Atmos[®]14
Support for Bluetooth[®] LE Audio

DISPLAY

Surface Laptop 6 13.5”:
Touchscreen: 13.5” PixelSense™ Display
Resolution: 2256 x 1504 (201 PPI)
Aspect ratio: 3:2
Contrast ratio 1300:1
Color profile: sRGB, and Enhanced
Individually color-calibrated display
Adaptive color
Touch: 10-point multi-touch
Dolby Vision IQ™15 support
Corning® Gorilla® Glass 5
Anti-reflective
Brightness: SDR 400 nits maximum (typical)

Surface Laptop 6 15”:

Touchscreen: 15” PixelSense™ Display
Resolution: 2496 x 1664 (201 PPI)
Aspect ratio: 3:2
Contrast ratio 1300:1
Color profile: sRGB, and Enhanced
Individually color-calibrated display
Adaptive color
Touch: 10-point multi-touch
Dolby Vision IQ™15 support
Corning® Gorilla® Glass 5
Anti-reflective
Brightness: SDR 400 nits maximum (typical)

SERVICEABILITY

Replacement components:¹⁶
- Display assembly (including camera)
- Keyboard assembly
- Removable solid-state drive
- Battery
- Motherboard module (main processor and main memory)
- Surface Connect
- Thermal module
- Audio jack
- Speakers
- Touchpad
- Enclosure
- Feet

ACCESSIBILITY

Compatible with Surface Adaptive Kit
Compatible with Microsoft Adaptive Accessories
Includes Windows Accessibility Features – learn more [Accessibility Features | Microsoft Accessibility](#)
Discover more Microsoft Accessible Devices & Products – [Accessible Devices & Products for PC & Gaming | Assistive Tech Accessories - Microsoft Store](#)

SENSORS

Ambient light sensor

WHAT'S IN THE BOX

Surface Laptop 6 13.5” or 15”
Power Supply:
13.5”: 39W
15”: 65W
Quick Start Guide
Safety and warranty documents

BATTERY CAPACITIES^{6,7}

Battery Capacity Nominal (WH) 47
Battery Capacity Min (WH) 46

EXTERIOR

Casing: Anodized aluminum
Colors:¹⁷ Platinum or Black

SUSTAINABILITY

More recycled materials
Enclosure is made with a minimum of 25.8% recycled content, including 100% recycled aluminum alloy and 100% recycled rare earth metals¹⁸

More energy efficient

ENERGY STAR[®] certified

More repairable

More replaceable components than Surface Laptop 5. Built-in QR code provides convenient access to instructions.¹⁶

Surface Trade-in

We make trade-in convenient and secure for our commercial customers in the USA at [Microsoft Trade In Program](#)

Microsoft is committed to be carbon negative, water, positive, and achieve zero waste by 2030. Learn more about how we design with sustainability in mind: [Sustainable Products & Solutions | Microsoft CSR](#)
[Microsoft Surface Sustainability - Microsoft Sustainability](#)

WARRANTY¹⁹

1-year limited hardware warranty

PEN AND ACCESSORIES COMPATIBILITY

Supports Microsoft Pen Protocol (MPP)

NETWORK AND CONNECTIVITY

Wi-Fi 6E: 802.11ax compatible²⁰
Bluetooth[®] Wireless 5.3 technology

GRAPHICS

8GB memory: Intel[®] Graphics
16GB, 32GB or 64GB memory: Intel[®] Arc™ Graphics

¹See [www.displayport.org](#) for details on cables that support DisplayPort 2.1. ²System System software uses significant storage space. Available storage is subject to change based on system software updates and apps usage. 1GB = 1 billion bytes. 1TB = 1,000 GB. [Surface.com/Storage](#) for more details. ³Solid State Drive (SSD) Retention is only available on Microsoft Surface devices in which the SSD is marketed as removable per the Technical Specifications. Solid State Drive (SSD) Retention is included in both Extended Hardware Service Plus and Microsoft Complete for Business Plus and is also available as an Optional Add-on when purchasing Microsoft Extended Hardware Service and Microsoft Complete for Business. Devices returned to Microsoft with a missing Solid State Drive (SSD) are subject to a Solid State Drive (SSD) replacement fee unless the device is enrolled in the Drive (SSD) Retention offer. ⁴Integrated smart card reader available only on Surface Laptop 6 in Black in one of these configurations: 15” 5/16/512, 7/16/256, 7/16/512, 7/32/512 and only in US and Canada. ⁵Battery life varies significantly based on usage, network and feature configuration, signal strength, settings and other factors. See [aka.ms/SurfaceBatteryPerformance](#) for details. ⁶13.5” Surface Laptop 6 comes with 39 W Surface power supply. Fast charging (from 5% to 80%) is supported with minimum 45W Surface power supply or USB-C⁴ PD charger, sold separately. Testing was conducted at Microsoft in February 2024, using pre-production devices, software, and minimum of 45W USB-C⁴ charger under controlled conditions. The device was powered on to the desktop screen with default display brightness settings. Actual charge time will vary based on operating conditions. Measured at typical office ambient temperature of 23C. ⁷Battery life varies significantly based on usage, network and feature configuration, signal strength, settings and other factors. See [aka.ms/SurfaceBatteryPerformance](#) for details. ⁸Up to 18.5 hours of battery life based on typical Surface device usage on Surface Laptop 6 13.8”: Testing conducted by Microsoft in February 2024 using preproduction Windows 11 software and preproduction Surface Briggs Intel[®] Core™ Ultra 7 processor 165H 256GB SSD, 16GB RAM. Testing consisted of full battery discharge with a mixture of active use and modern standby. The active use portion consists of (1) a web browsing test accessing eight popular websites over multiple open tabs, (2) a productivity test utilizing Microsoft Word, PowerPoint, Excel, OneNote and Outlook, and (3) a portion of time with the device in use with idle applications. Personalization colors set to Light mode for Windows and apps. All settings were default except screen brightness was set to 150 nits with auto-brightness and adaptive color disabled. Wi-Fi was connected to a network. Tested with Windows 11 Version 22H2.3085. Battery life varies significantly with settings, usage, and other factors. ⁹Up to 19 hours of battery life based on typical Surface device usage on Surface Laptop 6 15”: Testing conducted by Microsoft in February 2024 using preproduction Windows 11 software and preproduction Surface Briggs Intel[®] Core™ Ultra 7 processor 165H 512GB SSD, 16GB RAM. Testing consisted of full battery discharge with a mixture of active use and modern standby. The active use portion consists of (1) a web browsing test accessing eight popular websites over multiple open tabs, (2) a productivity test utilizing Microsoft Word, PowerPoint, Excel, OneNote and Outlook, and (3) a portion of time with the device in use with idle applications. Personalization colors set to Light mode for Windows and apps. All settings were default except screen brightness was set to 150 nits with auto-brightness and adaptive color disabled. Wi-Fi was connected to a network. Tested with Windows 11 Version 22H2.3085. Battery life varies significantly with settings, usage, and other factors. ¹⁰Might vary depending on manufacturing processes. ¹¹Windows 10 is not available for purchase but is supported by Surface Laptop 6. Visit [https://aka.ms/SurfaceSupportedOperatingSystems](#) for more information. ¹²Sold separately. Software license required for some features. ¹³Activation required. If your device is managed by your organization's IT department, contact your IT administrator for activation. If you activate your trial outside your organization, after 30 days, you will be charged the applicable monthly or annual subscription fee. Credit card required. Cancel any time to stop future charges. See [https://aka.ms/m365businesstrialinfo](#). ¹⁴Feature availability varies by market. See [aka.ms/WindowsAIFeatures](#). ¹⁵When Copilot for Windows is not available or enabled on the device, pressing the Copilot key will launch Windows Search. ¹⁶Voice focus requires activation. Windows 11 and is available in apps which use integrated device microphones and use certain Windows audio processing modes. ¹⁷Requires Dolby[®] Atmos[®] encoded content/audio. ¹⁸Requires Dolby Vision[®] encoded content and video. ¹⁹Replacement components available through Surface Commercial authorized device resellers. Components can be replaced on-site by a skilled technician following Microsoft's Service Guide. Microsoft tools (sold separately) may also be required. Availability of replacement components and service options may vary by product, market and over time. See [Surface service options - Surface | Microsoft Learn](#). ²⁰Opening and/or repairing your device can present electric shock, fire and personal injury risks and other hazards. Use caution if undertaking do-it-yourself repairs. Unless required by law, device damage caused during repair will not be covered under Microsoft's Hardware Warranty or protection plans. ²¹Colors available on selected models only. Available colors, sizes, finishes, and processors may vary by store, market, and configuration. ²²Enclosure includes A Cover, C Cover and D Bucket. 100% recycled aluminum alloy in A Cover. 100% recycled rare earth metals in magnets. Based on validation performed by Underwriter Laboratories, Inc. using Environmental Claim Validation Procedure for Recycled Content, UL 2809-2, Second Edition, November 7, 2023. ²³Microsoft's Limited Warranty is in addition to your consumer law rights. ²⁴WiFi 6E is not available in all areas.