



L A P T O P S

Raider 18 HX

RAIDER 18 HX A14VHG-258US

Specification

| | |
|------------------------------|---|
| Manufacturer Part # | RAIDER18HX14258 |
| OS | Windows 11 Pro |
| CPU | Intel® Core™ i9-14900HX |
| CPU Speed | 1.6-5.8 GHz |
| Chipset | - |
| Color | Core Black |
| Screen Size | 18" UHD+(3840x2400) 120Hz Mini LED HDR 1000 100% DCI-P3 |
| Resolution | 3840x2400 16:9 |
| GPU | NVIDIA® GeForce RTX™ 4080 Laptop GPU |
| Video Memory | 12G GDDR6 |
| Keyboard | SteelSeries per-Key RGB with Anti-Ghost key (99 Key) |
| Speaker | Sound by Dynaudio, 4x2W Speakers 2W x2W Woofer |
| Memory | 128GB (32GB*4) DDR5 5600MHz |
| HDD Capacity | 2TB NVMe SSD Gen4x4 |
| HDD Interface | NVMe |
| LAN | Killer E3100G |
| WLAN | Killer WiFi 7 BE1750 |
| Bluetooth | BT 5.4 |
| Card Reader | SD7.0 |
| Webcam | IR FHD w/shutter |
| USB | 3x USB 3.2 Gen 2 |
| Type-C Port | 2x Thunderbolt™ 4 w DP (1 also with PD3.1) |
| Video Port | HDMI v2.1, |
| Audio Port | 1 Audio Combo (1/8") |
| AC Power Adaptor | 330W |
| Battery Pack | 4 cell (99.9Whr) Li-Ion |
| Dimension | 15.91"x 12.09"x 1.26" |
| Weight | 7.94 lbs |
| Manufacturer Warranty | 3 year Limited warranty (Include 1 Year Global) |