cisco Meraki

MV33 Datasheet

This article outlines the MV33 datasheet, highlighting its 12.4 MP image quality, 360° field of view, and advanced analytics in a compact fisheye form for enhanced surveillance and security across various indoor applications. It emphasizes the camera's high-resolution video, intelligent object detection, and secure, low-bandwidth operation.

Overview

The Meraki MV33 offers 12.4 MP image quality and combines physical security and advanced analytics in a powerful yet compact fixed-lens mini fisheye form factor. Easy to install, with a 360° field of view (FoV), MV33 provides complete visibility and intelligent security for various indoor applications.



Security That Tells a Complete Story

With up to 2880x2880 video resolution and 360-degree views, the ultra-high-performance MV33 camera captures the full picture, providing broad context and clear detail when needed. This panoramic overview increases situation awareness, making surveillance more efficient.


Compact and easy to install, MV33 camera boasts a new universal mounting place compatible with various mounting accessories; the MV33 camera can be installed in various deployment scenarios so that you can see around every corner. The 360° field of view makes it ideal for improving safety and security for a

Product Highlights

- 360° fisheye lens camera with 12.4MP Image Sensor
- Compact form factor with 180° horizontal and vertical FoV
- A large level of detail with up to 2880x2880 video resolution
- · Low bandwidth Consumption for recording and streaming using Smartcodec encoding
- Intelligent motion indexing with search engine
- Built-in search tools like motion search, motion recap, motion heatmaps and Event Search.
- Built-in analytics like Line Crossing, Area Occupancy, MV sense and Custom Computer-Vision capabilities
- SFO12-4-Cafe.1

 Water Standard Standard

- · Machine learning capability for intelligent obj
- Role-based user accounts provide secure via
- Cloud-augmented edge storage for minimal
- · Built-in automatic security with secure boot a
- Suitable for deployments of all sizes, 1-10,00
- NDAA Compliant



Motion Search and Event Search are available on the Meraki Vision Portal.

MV33 Camera Specifications

Category	Specifications
Camera	 1/2.3" 12.4MP (4072x3046) progressive CMOS Backlit image sensor High-performance fisheye lens 256GB high-endurance solid-state storage 1.6 mm focal length f/2.0 aperture Field of view: horizontal 180°, vertical 180° 1/30 second to 1/32,000 second shutter speed
Video	 8MP video recording (2880x2880) with H.264 encoding, up to 8 fps 4.2MP (2112x2112) 360° overview with H.264 encoding, up to 15 fps 1MP (1080x1080) 360° overview with H.264 encoding, up to 24fps Cloud-augmented edge storage (locally stored video; metadata in the cloud) Optimized retention settings (scheduling, motion-based) for variable retention Direct live streaming with no client software (native browser playback)* Stream video anywhere with automatic cloud proxy

Category	Specifications
	Audio recording supported with three (3) built-in microphones
DORI Specifications	 Detect (25 ppm/ 8 ppf) 36.7 m / 120.4 ft Observe (63 ppm/ 19 ppf) 14.6 m / 47.9 ft Recognize (125 ppm/ 38 ppf) 7.3 m / 23.9 ft Identify (250 ppm/ 76 ppf) 3.7 m / 12.1 ft
Networking and wireless	 1x 10/100/1000BASE-T Ethernet (RJ45) DSCP traffic marking Supported frequency bands (country-specific restrictions apply): 2.4 GHz 802.11b/g/n radio 2.412 - 2.484 GHz 5 GHz 802.11a/n/ac radio 5.150 - 5.250 GHz (UNII-1) 5.250 - 5.350 GHz (UNII-2) 5.470 - 5.600, 5.660 - 5.725 GHz (UNII-2e) 5.725 - 5.825 GHz (UNII-3) 1x1 with one spatial stream 20, 40, and 80 MHz channels (802.11ac) Up to 256 QAM on 5 GHz band Integrated omnidirectional antennas (6.3 dBi gain at 5 GHz) MT Gateway Support for all MT sensor
Power	Power consumption 12.95W maximum via 802.3af PoE
Environment	Temperature: 0°C to 40°C (32°F - 104°F)
Data and network security	Full disk encryption (AES 256-bit)

Category	Specifications
	 Automatically purchased and provisioned TLS certificates (publicly signed) Management encryption and two-factor authentication Wireless security: WPA, WPA2-PSK, WPA2-Enterprise with 802.1X EAP-TTLS TKIP and AES encryption
Physical characteristics	 Dimension: 120.66mm x 49.8mm (diameter x height) Weight: 330 grams Fisheye lens Ethernet Connector with RJ45 Interface Multicolor, multifunction status LED External microphone switch Reset button
Warranty	Five-year hardware warranty with advanced replacement
Hardware	MV33-HW: 360° fisheye lens outdoor camera with 256GB storage
Licensing	LIC-MV-XYR: Meraki MV Enterprise license (X = 1, 3, 5, 7, 10 years) [Optional] LIC-MV-SEN-XYR: Meraki MV Sense license (X = 1, 3, 5, 7, 10 years) [Optional] LIC-MV-CA30-XY: MV Cloud Archive license (X = 1, 3, 5 years) [Optional] LIC-MV-CA90-XY: MV Cloud Archive license (X = 1, 3, 5 years) [Optional] LIC-MV-CA180-XY: MV Cloud Archive license (X = 1, 3, 5 years) [Optional] LIC-MV-CA365-XY: MV Cloud Archive license (X = 1, 3, 5 years)
Accessories	 MA-MNT-MV-18: Mounting plate replacement kit MA-MNT-MV-28: Pole mount MA-MNT-MV-38: Wall-mount L-bracket MA-MNT-MV-48: Wall-mount arm bracket MA-MNT-MV-58: Conduit back box MA-MNT-MV-68: T-rail adapter

Category

Specifications

- MA-MNT-MV-88: Corner mount
- MA-MNT-MV-78: Telescopic mount
- MA-INJ-4: 802.3at power over Ethernet injector
- MA-PWR-MV-LV: Low voltage 12V DC/24V AC input
- MV camera hardware
- · Quick Install Guide

Small mounting plate

- Allen Wrench



In the box

Each Meraki camera requires a license to operate.