

Eaton EVBAF132A

Catalog Number: EVBAF132A

Eaton Basic G4 Rack PDU, 0U, 22.5U, IEC-60309 input, 3m cord, 1ph, 7.4kW, 32A, 200-240V, 24 outlets (12)C13, (12)C39

General specifications



| | |
|--|----------------------|
| Product Name | Catalog Number |
| Eaton Rack PDU G4 | EVBAF132A |
| Model Code | EAN |
| PDU G4 BA 0U 309 32A 1P 12xC13,12xC39 | 3553340697197 |
| | Product Length/Depth |
| | 1 mm |
| Product Height | Product Width |
| 1 mm | 1 mm |
| Product Weight | Warranty |
| 1 kg | 3 year |
| Compliances | Certifications |
| CB | IEC 62368-1 |
| LVD Directive | EN IEC 63000 |
| RoHS Directive | CE |
| WEEE Directive | EAC |
| Packaging Directive | UKCA |
| | Cm |
| | Ukr |

Product specifications

Electrical connection

Connecting cord with plug

Wattage

7.4 kW max

Form factor

0U (Vertical)

Mounting direction

Vertical

Number of Outputs 6-20R

0

Number of Outputs C20

0

Amperage Rating

32 A

Input connection

IEC-60309 32A 1Ph

Num of Outputs PC (SCHUKO)

0

Number of Outputs L14-30R

0

Fitted with:

Mounting material

Frequency rating

50/60 Hz

Evaluation

Other

Operating Temperature

0° to 60°C (32° to 140°F)

Number of outlets with earth pin

24

No of Outlet Suisse Stndrd Type25

0

Circuit breaker

(2) single-pole

Mass configuration

Resources

Brochures

[Rack PDU G4 Brochure EN](#)

No

No of Outlet Suisse Stndrd Type23

0

Special features

Versatile C39 outlet
supports C14 or C20 power
cord plug

High retention outlets
designed to securely fit
standard power cords and
support P-Lock power cords

Color-coded outlet banks
and corresponding circuit
breakers

Cord length

3m

Number of Outputs 6-15R

0

Color

Black

SNMP

No

Over voltage category

2

Outlets

(12) C13, (12) C39

Number of Outputs L6-30R

0

Number of Outputs 5-20R

0

Number of UK BS1363 sockets

0

Number of Outputs 5-15R

0

Number of Outputs L5-30R

0

No of Outlet Suisse Stndrd Type15

0

Number of Outputs C13

12

No of Outlet Suisse Stndrd Type13

0

Phase

Single-phase

Mounting dimension (standardized)

Metric

Accessories

Rack PDU

Rack mounting accessories

Quickstart guide

Safety Instructions

Number of outputs hardwired

0

Number of outputs (other)

12

Ethernet interface

No

Communication

No

Number of Outputs C19

12

Outlet control

No

Switchable

No

Input voltage

200-240V

Material

Aluminium

Number of Outputs L6-20R

0

Series

G4

Type

Basic Rack PDU

Amperemeter

No

Serial interface

No

Mounting Dimension (metrical)

52

Number of Outputs L5-20R

0



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)