



## Rugged, convertible Chromebook

The rugged HP Fortis x360 Chromebook provides reliability and performance in a rugged 360-degree design. It features an Intel® quad-core processor<sup>[8]</sup>, plenty of memory, and long battery life for productivity throughout the day. The 360-degree hinge allows multiple modes of use, while enhanced durability testing gives you peace of mind.



### **Immersive 360-degree design**

Work with flexibility in laptop, tablet, tent, or stand mode, thanks to a durable 360-degree hinge.

### **Durable, reliable design**

Designed and tested for durability, featuring a keyboard that resists picking, minor spills, and dust.<sup>[12]</sup>

### **Productivity empowered**

Quickly access data, apps, and more in crowded wireless networks with Wi-Fi 6E<sup>[6]</sup> and an Intel® quad-core processor.<sup>[8]</sup>

## Featuring

### **Universal connectivity and charging with USB-C™**

Use the USB-C™ port to access and charge your USB-C™ accessories from your Chromebook™ or charge your Chromebook™ from any USB-C™ adapter.

### **Apps and content for expanded learning**

Take learning in new directions with access to the Google Play™ Store and Android™ apps, which include thousands of instantly shareable and easily manageable innovative education apps.<sup>[1]</sup>

### **Simple PC management**

Spend less time and get right to the updates you need with HP Support Assistant.<sup>[2]</sup>

## Specifications

<b>Operating system</b>	ChromeOS
<b>Product color</b>	Jack black
<b>Processor family</b>	Intel® Core™ N-series processor
<b>Processor</b>	Intel® Processor N100 (up to 3.4 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores, 4 threads) <sup>[6,7]</sup>
<b>Memory</b>	8 GB LPDDR5x-7500 MHz RAM (onboard)
<b>Internal Storage</b>	64 GB eMMC
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® UHD Graphics
<b>Display</b>	29.5 cm (11.6") diagonal, HD (1366 x 768), touch, BrightView, 250 nits, 50% NTSC
<b>Display</b>	11.6" diagonal, HD (1366 x 768), touch, BrightView, 250 nits, 50% NTSC <sup>[10,11,12,13]</sup>
<b>Display size (diagonal)</b>	29.5 cm (11.6")
<b>Display size (diagonal)</b>	11.6"
<b>Audio</b>	Waves MaxxAudio®, dual speakers, dual array microphones
<b>Minimum dimensions (W x D x H)</b>	29.5 x 20.4 x 2.1 cm
<b>Minimum dimensions (W x D x H)</b>	11.61 x 8.03 x 0.78 in
<b>Weight</b>	Starting at 1.46 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Weight</b>	Starting at 3.21 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Keyboard</b>	Full-size, island-style, flint gray keyboard
<b>Camera</b>	720p HD camera
<b>Ports</b>	2 USB Type-C® 5Gbps signaling rate (USB Power Delivery, video and data support); 2 USB Type-A 5Gbps signaling rate; 1 HDMI 1.4; 1 stereo headphone/microphone combo jack <i>(HDMI cable sold separately.)</i>
<b>Package dimensions (W x D x H)</b>	6.7 x 43.5 x 26 cm
<b>Wireless</b>	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
<b>Power</b>	45 W USB Type-C™ adapter
<b>Battery type</b>	HP Long Life 2-cell, 47 Wh Li-ion polymer
<b>Battery weight</b>	0.42 lb
<b>Battery weight</b>	190 g
<b>Sustainable impact specifications</b>	Low halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 2% post-consumer recycled plastic
<b>UPC number</b>	(ABA) 198122700417; (ABL) 198122700400
<b>Manufacturer Warranty</b>	HP Services offers 1-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty except for Long Life batteries which will have same 1-year or 3-year limited warranty as the platform. Refer to <a href="http://www.hp.com/support/batterywarranty/">http://www.hp.com/support/batterywarranty/</a> for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <a href="http://www.hp.com/go/cpc">http://www.hp.com/go/cpc</a> .

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Internet access required and sold separately. Some apps may require purchase.

[2] Internet access required.

[6] Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs and available in countries where Wi-Fi 6E is supported.

[8] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of clock speed.

[12] HP Total Test Process testing is not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.

## Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[10] FHD/HD content required to view FHD/HD images.

[11] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[12] Actual brightness will be lower with touchscreen.

[13] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2023 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

