



HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk (8Y2K9AA)



Overview

The power to make it real

See ultimate potential before it's real with the ultra-powerful and stunningly precise, HP Series 7 Pro 31.5" 4K Thunderbolt 4 Monitor. Powered by the impressive capabilities of Thunderbolt™ 4, experience your creations in tangible, lifelike detail with IPS Black technology and 4K UHD resolution.[1]

Color that rivals reality

View every detail as if it's true-to-life with captivating color contrast on this precise 31.5" 4K monitor. Through the cutting-edge IPS Black panel, dive into deeper shadows and richer hues with twice the contrast of a traditional IPS panel. Combined with VESA DisplayHDR™ 400, wide 98% Display P3 color gamut, and superb color accuracy[1], what you see on screen rivals reality.

Seamless control

Designed with intelligent controls, this display gets you working quickly and multi-tasking efficiently. Instantly wake your display and PC with Single Power On[4]. And when you're multi-tasking between two devices, simply use the built-in KVM switch to control both with just a single keyboard and mouse.[5]

Unleash the power of Thunderbolt™ 4

Transform your desk into a productivity powerhouse with this Thunderbolt™ 4 monitor.[2] Through a single cable, drive 4K resolution at 60 Hz, daisy chaining support for a second 4K monitor, as well as high-speed data and internet[3]—all while charging your device at up to 100W—without slowing you down.

Our commitment to the planet

A better choice in an innovative solution, this HP Series 7 Pro Monitor is designed using 85% post-consumer recycled materials and 5% ocean-bound plastics[6] with 90% recycled aluminum in the stand. With 100% sustainably sourced packaging[7] and a TCO certified, EPEAT® Registered, and ENERGY STAR® Certified design[8], you can be confident knowing you have a monitor that does good things for the planet while doing amazing things for you.

Features

IPS Black

Stunning colors from any angle thanks to the 2,000:1 contrast ratio and ultra-wide viewing angles.^[1]

4K UHD Resolution

Get lost in the captivating definition and expanded view of 4K resolution.

31.5-inch Diagonal Screen

Dive in and accomplish more on a massive 31.5-inch diagonal screen framed by a 4-sided, virtually borderless bezel.

VESA DisplayHDR™ 400

Replicate reality on your screen and enjoy watching HDR media with enhanced contrast.

Wide Color Gamuts

100% sRGB for ideal color reproduction and 98% Display P3 for deeper, lifelike hues.^[1]

Colors Calibrated to Perfection

Every HP Series 7 Pro Monitor undergoes strict factory color calibration to assure that over 400 colors achieve a Delta E of less than 2, making any color difference virtually indistinguishable to the human eye for superb color accuracy.

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower.

[2] For full Thunderbolt™ 4 functionality, host PC must support Thunderbolt™ 4.

[3] Display supports 1Gb ethernet speed. Host PC requires infrastructure to support 1 Gb ethernet speeds.

[4] Single Power On only compatible with HP PCs with Windows 10 or higher.

[5] For KVM compatibility, if connected PCs do not have USB-C® port, user will need a USB-C® to A cable. Sold separately.

[6] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT® standard. Plastics consist of 90% Post-Consumer Recycled, with 85% post-consumer recycled plastics + 5% Ocean-Bound Plastics (PET).

[7] 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.

[8] Based on US EPEAT® registration according to IEEE 1680.1-2020 EPEAT®. Status varies by country. Visit www.epeat.net for more information.

Specifications

Display size (diagonal)	31.5"
Panel technology	IPS Black
Display size (diagonal)	80 cm (31.5")
Aspect ratio	16:9 ^[1]
Native resolution	4K UHD (3840 x 2160) ^[1,2]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 2560 x 1440; 3840 x 2160
Pixel pitch	0.18 x 0.18 mm
Brightness	400 nits ^[1]
Contrast ratio	2000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	71.35 x 4.7 x 41.59 cm <i>(without stand)</i>
Minimum dimensions (W x D x H)	28.09 x 1.85 x 16.37 in <i>(without stand)</i>
Dimensions With Stand (W x D x H)	71.35 x 21.7 x 60.49 cm
Weight	8.77 kg <i>(with stand)</i>
Weight	19.33 lb <i>(with stand)</i>
Display features	Single Power ON; Anti-glare; Height Adjust/Tilt/Swivel/Pivot; HP Eye Ease; IPS Black; HDR; KVM switch; Daisy chain; Picture-in-Picture; Picture-by-Picture
Onscreen controls	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit
Display colors	Up to 1.07 billion colors supported ^[3]
Display scan frequency (horizontal)	30-135 kHz ^[1]
Display scan frequency (vertical)	29-60 Hz ^[1]
Camera	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	205 W (maximum), 48 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH (non-condensing)

Sustainable impact specifications

Low halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 85% ITE-derived closed loop plastic; Designed with recycled metals; 5% ocean-bound plastic

Certifications and compliances

Australia MEPS; Bauart; CB; CE; CEL; China CCC; China CECP; C-Tick; cTUVus; CU; EAC; EUP Lot-5; EUP Lot-6; FCC; ISO 9241-307; KC (Korean) requirements; KCC (Korean) requirements; Korea MEPS (E-standby); NOM (Mexico); PSB for Singapore; RCM; SEPA eco label (China); S-Mark for Argentina; Taiwan BSMI; VCCI; Vietnam MEPS; EUP Lot-26; California Energy Commission (CEC); South Africa Energy; Mexico Energy; UAE; TUV-GS; NRCS of South Africa; Belarus Energy; India BIS; Cambodia ISC; NRCS; Ukraine EE; South Africa safety; Ukraine CoC; Ukraine DOC; Microsoft WHQL Certification (Windows 11)

Physical security

Security lock-ready^[11]

Management Software

HP Display Center; HP Display Manager

UPC number

(A2K) 197498471280; (A2N) 197498471297; (AB0) 197498471303; (AB1) 197498471310; (AB2) 197498471327; (AB4) 197498471334; (ABA) 197498471341; (ABB) 197498471358; (ABG) 197498471365; (ABJ) 4582712372997; (ABT) 197498471372; (ABU) 197498471389; (ABV) 197498471396; (ABY) 197498471402; (ACJ) 197498471419; (ACQ) 197498471426; (AH3) 197498471433; (AKL) 197498471440; (AR6) 197498471457; (UUF) 197498471464; (UUZ) 197498471471

Manufacturer Warranty

HP three-year limited warranty

What's in the box

Monitor; Thunderbolt™ cable; DisplayPort™ cable; HDMI cable; Warranty card; USB Type-A to B cable; Quick Setup Poster; AC power cord; Color calibration report^[10]

Additional specifications

Backlight lamp life	30,000 hours
Backlight type	Edge-lit
Base area footprint (imperial)	10.24 x 8.54 in
Base area footprint (metric)	26 x 21.7 cm
Bezel	4-sided micro-edge
Color gamut	100% sRGB; 98% DisplayP3
Count of layers in pallet	4 / 5 (slip sheet)
Country of origin	Made in China
Curvature	Flat
Datasheet photo 1	AHID/603a50a78573f6d609860a58c03f7f3c6ca33bfc
Datasheet photo 3	AHID/52c1a20d15b0da53b58112640c1cda795b6a6391
Datasheet photo 4	AHID/3ce9a76dc380f003659f9df0c2628590c74158d1
Datasheet photo 5	AHID/9f4de0b27f340b5eff572c7ef1695dce33355596
Detachable stand	Yes
Display area (imperial)	27.4 x 15.4 in
Display area (metric)	69.7 x 39.2 cm
Display contrast ratio (dynamic)	10000000:1
DisplayPort™	1 DisplayPort™ 1.4
DisplayPort™ Out	1 DisplayPort™ 1.4-out
Energy star certified	ENERGY STAR® certified
Ethernet	1 RJ-45 (10/100/1000 Mbps)
Flicker-free	Yes
HDCP	Yes, DisplayPort™, HDMI and Thunderbolt™
HDMI	1 HDMI 2.0
HDR	HDR 400
Hardness	3H ^[1]
Haze	25%
Height adjustment range	150 mm
Horizontal viewing angle	178°
KVM switch	Yes, OSD switch
Low blue light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
Non-Operating Humidity Range	5 – 95 %
Operating altitude	Up to 5,000 m

Operating altitude	Up to 16,400 ft
Operating temperature range	41 to 95°F
Package dimensions (W x D x H)	81.6 x 18.5 x 50.4 cm
Package dimensions (W x D x H)	32.13 x 7.28 x 19.84 in
Package weight	30.19 lb
Package weight	13.7 kg
Pallet dimensions	44.88 x 32.68 x 84.96 in (20' ft/40' ft); 44.88 x 32.68 x 84.96 in (40' HQ)
Pallet dimensions (W x D x H)	1140 x 830 x 2158 mm (20' ft/40' ft); 1140 x 830 x 2158 mm (40' HQ)
Pallet weight	746.5 lb (20' ft/40' ft); 746.5 lb (40' HQ)
Pallet weight	339.3 kg (20' ft/40' ft); 339.3 kg (40' HQ)
Panel bit depth	10 bit (8 bit + FRC) ^[1]
Picture-in-Picture, Picture-by-Picture	Yes
Pixels per inch (ppi)	140 ppi ^[1]
Power supply type	Internal
Product dimensions with stand (W x D x H)	28.09 x 8.54 x 23.81 in
Products per pallet layer	6
Quantity per pallet	24 sets per pallet (40' ft)
Recommended resolution	4K UHD (3840 x 2160 @ 60 Hz)
Refresh rate (maximum)	60 Hz
Remote manageability	Out-of-Band MAC Address Pass Through (MAPT); Out-of-Band Wake on LAN (WoL); PXE Boot
Resolution (maximum)	4K UHD (3840 x 2160 @ 60 Hz)
Screen treatment	Anti-glare
Stand color	Black; Silver
Storage altitude	Up to 12,192 m
Storage altitude	Up to 40,000 ft
Tilt	-5 to +20°
UNSPSC code	43211902
USB Type-A	4 SuperSpeed USB Type-A 5Gbps signaling rate
USB Type-C® video input	1 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (up to 100 W USB Power Delivery, DisplayPort™ 1.4)
Usb b (hub enablement)	1 USB-B
VESA mounting	100 x 100 mm (bracket included)
Vertical viewing angle	178°
Viewable diagonal size	31.5" (80 cm)

pivot	±90°
swivel	±45°

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] DisplayPort™ 1.4 or HDMI 2.0 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 3840 x 2160 at 60 Hz with 10-bit color using one DisplayPort™, HDMI, or USB-C® (DisplayPort™ alt mode).

[3] Number of colors through A-FRC technology.

[10] Included cables may vary by country.

[11] Lock sold separately.

Accessories

Rack Brackets/Bezels/ Panels/Rails/ Trays/Mounting

★ : Recommended

Mounting Kits

HP B550 PC Mounting Bracket	16U00AA
HP Desktop Mini v4+ VESA Sleeve	99T54AA
HP Quick Release Bracket 2	6KD15AA

Security and Protection

PC Locks

HP Business PC Security Lock v3 Kit	3XJ17AA
-------------------------------------	---------

Audio/Multimedia and Communication Devices

Speakers

HP Z G3 Conferencing Speaker Bar	32C42AA
----------------------------------	---------

Disclaimer — Copyright

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 24, 2024 3:12 PM UTC+0000