



SPECIFICATIONS

Panel Size	34"
Active Display Area (mm)	797.22(H) x 333.72(V)
Curvature	Curve 1000R
Panel Type	VA
Panel Resolution	3440x1440 (UWQHD)
Pixel Pitch (H x V)	0.23175(H) x 0.23175(V)
Aspect Ratio	21:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	3000 : 1 (Typ.)
DCR	100000000:1
Signal Frequency	70.57~268.2 KHz(H) / 48~180 Hz(V)
ACTIVATED RANGE	48 ~ 180Hz
Refresh Rate	180Hz
Response time	1ms (MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive sync support
HDR Support	HDR Ready
Video ports	1 x DisplayPort (1.4a) 2 x HDMI™ (2.0b)
Audio ports	1x Headphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	90% / 95% / 120%
Surface Treatment	Anti-glare
Display Colors	1.07B , 10 bits (8 bits + FRC)
Power Type	External Adaptor, 19V / 3.42A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Height)	0 ~ 100mm
Kensington Lock	Yes
Dimension (W x D x H)	797.53 x 332.31 x 518.9mm 797.53 x 158.18 x 363.02mm (without stand)
Carton Dimension (W X D X H)	WW carton: 985 x 228 x 510 mm Outer: 1000 x 241 x 534 mm
Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm

FEATURES



1000R

Enjoy the most immersive gameplay with 1000R curvature rate.



180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms(MPRT) response time.



RGB light

The mesmerizing RGB lights on the back of the screen create a stunning visual display.



HDR Ready

MSI gaming monitor is equipped with HDR technology that can produce images with more details, wider range of colors. Windows 11 Auto HDR supported



Console Mode

Perfectly support 120Hz at FHD/WQHD resolution with next-gen console like PS5 and Xbox series X/S.

Weight (NW / GW)	7.75kg / 11.3kg
Note	Display Port: 3440 x 1440 (Up to 180Hz) HDMI™ : 3440 x 1440 (Up to 100Hz) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. 2 x HDMI™ (2.0b)
3. DisplayPort (1.4a)
4. 1 x Earphone out
5. DC Power jack
6. Kensington lock