



BUSINESS & PRODUCTIVITY

Prestige 16 AI Evo

PRESTIGE 16 AI EVO B1MG-048US

Specification

Manufacturer Part #	PRE16EVO14048
OS	Windows 11 Pro
CPU	Intel® Core™ Ultra 9 - 185H
CPU Speed	2.3 - 5.1 GHz
Chipset	-
Color	Stellar Gray
Screen Size	16" 16:10 QHD+ (2560x1600), 100% DCI-P3, IPS-Level panel
Resolution	2560x1600 16:10
GPU	Intel® Arc Graphics
Video Memory	-
Keyboard	White backlight keyboard with Finger print reader
Speaker	2x Speakers 2W
Memory	32GB LPDDR5-6400MHz
HDD Capacity	2TB NVMe SSD
HDD Interface	NVMe
LAN	Gigabit Ethernet
WLAN	Intel® Killer™ Wi-Fi 7 BE1750(w)
Bluetooth	BT 5.4
Card Reader	Full Size SD Card
Webcam	FHD IR Webcam with Dual Mic with Privacy shutter Design
USB	1x USB 3.2 Gen2 (Type-A)
Type-C Port	2x Thunderbolt™ 4 [Support Power delivery, DP 1.4a, USB 4.0]
Video Port	HDMI HDMI 2.1 (4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	100W [USB-C]
Battery Pack	4 cell (99.9Whr) Li-Polymer
Dimension	14.11" x 10.02" x 0.75"
Weight	3.31 lbs
Manufacturer Warranty	3 year on site warranty + ADP