



L A P T O P S

Sword 16 HX

SWORD 16 HX B14VGKG-229US

Specification

Manufacturer Part #	SWORD1614229
OS	Windows 11 Pro
CPU	Intel® Core™ i7-14650HX
CPU Speed	1.6-5.2 GHz
Chipset	-
Color	Cosmo Gray
Screen Size	16" FHD+, IPS-Level 144Hz 45% NTSC
Resolution	(1920x1200) 16:10
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
Keyboard	SteelSeries 24-Zone RGB with Anti-Ghost key (99 Key)
Speaker	2x2W Speaker Hi-Res Audio, Nahimic
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel ® PTT
LAN	Gb LAN
WLAN	Intel Wi-Fi 6E AX211(2*2 ax)
Bluetooth	BT 5.3
Card Reader	-
Webcam	720p HD with shutter
USB	3x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen 2/DP(w/PD3.0 Chargin)
Video Port	v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	200W
Battery Pack	4 cell , 65Whr Li-Polymer
Dimension	14.00"x 10.48"x 1.10"
Weight	5.07 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)