



CONTENT CREATION

CreatorPro M16 HX

CREATORPRO M16 HX C14VJG-412US

Specification

Manufacturer Part #	CProM1614412
OS	Windows 11 Pro
CPU	Intel® Core™ i7-14650HX
CPU Speed	1.6-5.2 GHz
Chipset	-
Color	Lunar Gray
Screen Size	16" 16:10 FHD+(1920 x 1200), 144Hz, IPS-level panel
Resolution	(1920x1200) 16:10
GPU	NVIDIA® RTX 2000 ADA
Video Memory	8G GDDR6
Keyboard	White backlight keyboard (99 Key)
Speaker	Speakers 2x Speakers 2W
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
TPM	dTPM2.0 (9672)
LAN	Gb LAN
WLAN	Intel WiFi 6E AX211 (2x2)
Bluetooth	BT 5.3
Card Reader	-
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen1 (Type-A)
Type-C Port	1x USB 3.2 Gen1 Type C
Video Port	HDMI 2.1 (4K @ 120Hz / 8K @60Hz)
Audio Port	1 combo (Hi-Res Audio)
AC Power Adaptor	180W
Battery Pack	3 cell , 65Whr Li-Polymer
Dimension	14.13" x 10.35" x 1.06"
Weight	4.96 lbs
Manufacturer Warranty	3 year on site warranty + ADP