



L A P T O P S

Stealth 16 AI Studio A1V

STEALTH 16 AI STUDIO A1VHG-032CA

Specification

OS	Windows 11 Pro
Color	Star Blue
Screen Size / Type	16" UHD+(3840x2400) 120Hz Mini LED HDR 1000 100% DCI-P3
Resolution/ Ratio	3840x2400 16:9
CPU/Processor	Intel® Core™ Ultra9-185H
CPU Frequency	3.8-5.1 GHz
Chipset	Integrated SoC
Graphics	NVIDIA® GeForce RTX™ 4080 Laptop GPU
Video Memory	12G GDDR6
System Memroy	DDR5 16GB*2
SoDimm	2 Sockets; Max Memory 96GB
HDD Capacity	2TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2 x NVMe M.2 SSD by PCIe Gen4 x4
LAN	Killer E3100G
WLAN	Killer WiFi 7 BE1750
BT	BT 5.4
Card Reader	Micro SD 4.0
HDMI-out	v2.1,
USB Type C	1x Thunderbolt™ 4 w/DP2.1&PD; 1x USB 3.2 Gen 2/DP 1x USB 3.2 Gen2
USB	
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Touch Pad	Silky Glass Touchpad
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Sound by Dynaudio, 2x2W Speaker, 4x2W Woofer
Webcam	1080p FHD with shutter
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	240W
Unit weight	4.39 lbs
Unit Dimension	14"x 10.22"x 0.85"
UPC	824142347560
UCC-14	10824142347567
Warranty	1 year Limited warranty (Include 1 Year Global)