



PDU31116 MONITORED PDU



Designed for datacenters and other electrically demanding applications.

The CyberPower PDU31116, a 20-outlet, 0U rackmount monitored power distribution unit (PDU), provides 120V 15A output. It distributes power to 20 NEMA 5-15R receptacles from a single NEMA 5-15P plug with unfiltered electrical pass-through. Power status can be monitored over the network, using the CyberPower Management Console and the RJ45 Ethernet port for network connection, or locally by using the LCD. The PDU31116 comes with a three-year limited warranty that covers defects in materials and workmanship in the product under normal use and conditions within three years of the purchase date.

TYPICAL APPLICATIONS

- Data Centers
- Network Closets
- Corporate Servers

FEATURES

- Monitored PDU: SNMP Network Interface
- Automated Notifications: Email, SMS Text, and SNMP Trap
- Phase: Single
- Amps: 15A (Derated to 12A)
- Volts: 100 - 120 V
- Frequency: 50Hz/60Hz
- Plug type: NEMA 5-15P
- Outlets: 20 NEMA 5-15R
- Size: 0U Rackmount
- Dimensions: 1.9W x 53.1H x 2.2D in.
- Cord length: 10 ft.
- Warranty: Three-Year

SPECIFICATIONS

INPUT	
Cord Length	10 ft (3.0 m)
Input Frequency Range	50 Hz - 60 Hz
Input Plug Type	NEMA 5-15P
Maximum Input Current	15A (Derated to 12A)
Phase	Single Phase
Plug Style	Straight

OUTPUT	
Meter Readout	Kilowatts Voltage Amperage IP Address
Nominal Output Voltage	100 - 120 VAC
Outlet Banks	1
Outlet Type	20 x NEMA 5-15R
Outlet Total	20 Front, 0 Rear

PDU31116

MONITORED PDU



SPECIFICATIONS - CONT.

MANAGEMENT & COMMUNICATIONS		DIMENSIONS	
Hardware Connection Port	RJ45 Serial	Physical Dimensions - Width/Height/Depth (cm)	4.83 x 134.87 x 5.59 cm
LED Indicators	Load Tx/Rx LINK Outlets	Physical Dimensions - Width/Height/Depth (mm)	48 x 1349 x 56 mm
SNMP / HTTP Remote Monitoring	TCP/IP UDP DHCP SNMP HTTP	Physical Dimensions - Width/Height/Depth (in.)	1.9 x 53.1 x 2.2 in.
PHYSICAL		Weight (kg)	5.22 kg
Adjustable Mounting Brackets	1 set	Weight (lbs.)	11.5 lbs.
Color	Black	SHIPPING DIMENSIONS	
Cord Retention Tray Cord Organizers	Yes	Shipping Dimensions - Width/Height/Depth (cm)	11.43 x 157.99 x 18.03 cm
External Site Ground Pin	Yes	Shipping Dimensions - Width/Height/Depth (mm)	114.3 x 1579.88 x 180.34 mm
Form Factors Supported	Horizontal or Vertical Wallmount Racks Horizontal or Vertical Mount in a Variety of Other Surface Types	Shipping Dimensions - Width/Height/Depth (in.)	4.5 x 62.2 x 7.1 in.
Material of Construction	Metal	ENVIRONMENTAL	
Rack Height	0U	Operating Elevation	0 - 11,482 ft (0 - 3500 m)
Style	Vertical Rackmount Wallmount	Operating Relative Humidity	0 - 95% (non-condensing)
		Operating Temperature	32 - 140 °F (0 - 60 °C)
		Storage Elevation	0 - 49,212 ft (0 - 14,999 m)
		Storage Temperature	5 - 149 °F (-15 - 65 °C)
		CERTIFICATIONS	
		Environmental	RoHS Compliant
		Safety	UL 62368-1 FCC Class A
		WARRANTY	
		Extended Warranty Option	WEXT5YR-PDU1A
		Product Warranty	3-Year Limited