



HP E24q G5 QHD Monitor

Redefining Focus

Intentionally crafted to deliver crisp visuals, personalized comfort, and true flexibility, the HP E24q G5 QHD Monitor redefines comfort, so there's nothing between you and your best. Stylishly designed with the planet in mind, this display is the perfect fit for both the office and home.



*Product image may differ from actual product

See it All, Do it All

- When the difference is in the details, this 23.8-inch diagonal QHD monitor displays the clarity you need to stay focused on the task at hand. With rich 99% sRGB color depth and IPS technology¹, you'll see clear, vivid colors across wide viewing angles².

Bring Comfort to Work

- When doing your best relies on feeling your best, it's easy to find all-day comfort with 4-way adjustability optimized by the step-by-step Ergonomic Setup Guide in HP Display Center³. Help keep your eyes comfortable with a monitor that comes with flicker-free technology, a 75Hz refresh rate¹ and HP Eye Ease, an always-on, built-in low-blue light filter.

Connect Intuitively

- Work how you want with flexible connectivity and settings. Purposefully in reach, the accessible ports make connecting your devices quick and easy, while you effortlessly navigate your on-screen settings with the intuitive joystick OSD button.

Design that Inspires

- Spark joy on your desk and in the world with a monitor built around you. The elegant, efficient design and 3-sided micro-edge bezel elevate your office while maximizing space. Beyond the looks, feel good with a monitor that contains recycled plastics⁴ and metals⁵. And customize your space to boost your productivity with the matching accessory ecosystem⁶.

Featuring

Ergonomic Setup Guide

Achieve all-day comfort when you apply the best practices from the Ergonomic Setup Guide.³

Enhanced Viewing Comfort with HP Eye Ease

Always-on, built-in, low-blue light filter that reduces blue light without the yellow color shift now enhanced with a 75Hz refresh rate.¹

IPS Panel

No matter where you stand, IPS technology ensures image accuracy and consistency across wide, 178-degree horizontal and vertical viewing angles.

99% sRGB Color Space

Enjoy what you see on screen with 99% sRGB color space. This display provides ideal color reproduction for vibrant images and videos.¹

Endless Adjustability

Work effortlessly with 4-way ergonomics that help keep your neck, shoulders, and back comfortable throughout the day. Customize pivot, tilt, 150 mm height adjust, and swivel settings to fit you, your desk, and your needs.

More Ports. More Flexibility.

More ports means more capabilities. With an HDMI, DisplayPort™, USB-B, and 4 USB-A 3.2 ports, you can connect multiple devices like a headset and webcam.⁷

Effortless Joypad OSD Button

It's never been easier to configure your displays settings right from the monitor. Simply navigate the on-screen menu with the joypad OSD button to adjust brightness, contrast, and color.

HP Display Manager

HP Display Manager makes remote management of the monitor easy. Simplify deployment, asset tracking, and remotely control your monitor settings, like turning the power off.⁸

HP Display Center

Customize your display with easy, intuitive HP Display Center software.⁹

3-Sided Micro-Edge Bezel

See and do more on your screen with a 3-sided micro-edge bezel that maximizes your viewing area for a sleek design and virtually seamless dual-monitor setups.

Materials that Matter

This monitor's enclosure consists of 90% recycled and renewable material.⁴

Mindful Metals

At HP, we don't stop when it comes to protecting our shared future. That's why this monitor was engineered to contain 25% recycled metals.¹⁰

Thoughtful Product Packaging

HP is committed to reducing plastic in landfills by using 100% recyclable packaging that meets recycling requirements, so it can stay out of the landfill when customers are finished with it.^{11,12}

Increased Energy Efficiency

Reaching highest energy-saving standards with an ENERGY STAR® rating and EPEAT® Registration.^{13,14}

Customizable Matching Accessories

Customize your desk to fit your work needs with the matching accessory ecosystem.¹⁵

HP E24q G5 QHD Monitor Specifications Table



*Product imagery may differ from actual product

Display size (diagonal, metric)	60.5 cm (23.8")
Display type	IPS
Panel Active Area	20.75 x 11.67 in; 52.69 x 29.64 cm
Brightness	300 nits ¹
Contrast ratio	1000:1 ¹
Response Ratio	5ms GtG (with overdrive) ¹
Product colour	Black head, black and silver stand
Aspect ratio	16:9 ¹
Native resolution	QHD (2560 x 1440) ^{1,2}
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080; 1920 x 1200; 2560 x 1440
Display features	On-screen controls; Anti-glare; Height Adjust/Tilt/Swivel/Pivot; HP Eye Ease
User controls	Management; Information; Exit; Input; Color; Image; Power; Menu; Brightness+
Ports and Connectors	1 HDMI 1.4; 1 DisplayPort™ 1.2; 4 SuperSpeed USB Type-A 5Gbps signaling rate (1 charging); 1 USB-B
HDCP	Yes, DisplayPort™ and HDMI
Environmental	Operating temperature: 5 to 35°C; Operating humidity: 20 to 80% RH;
Power	100 - 240 VAC 50/60 Hz
Power consumption	56 W (maximum), 39 W (typical), 0.5 W (standby)
Dimensions	21.24 x 1.85 x 12.7 in (without hinge); 21.24 x 2.95 x 12.7 in (with hinge); 53.94 x 4.7 x 32.26 cm (without hinge); 53.94 x 7.5 x 32.26 cm (with hinge) (without stand)
Weight	12.83 lb; 5.82 kg (with stand)
Physical security features	Security lock-ready ¹¹
Ecolabels	EPEAT® registered; TCO Certified ³ ; ENERGY STAR® certified
Certification and compliance	BIS; BSMI; CB; CCC; CE; CE Marking; CECP; CEL; CEL Grade 1; cTUVus; EAC; ENERGY STAR®; FCC; ISO 9241-307; KC/KCC; Microsoft WHQL Certification; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV-S; VCCI; WEEE; ISC; eStandby; WW application; ICE; UAE; TGM; Ukraine certificates; NRCS; PSE; Hardware low blue light; GS
Sustainable impact specifications	Low Halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Contains ocean-bound recycled plastic; 85% ITE-derived closed loop plastic; At least 25% recycled metal ^{4,5,6,7,8,9}
What's in the box	Monitor; DisplayPort™ cable; HDMI cable; Warranty card; USB Type-B to A cable; Quick Setup Poster; AC power cord ¹⁰
Pixels per inch (ppi)	123 ppi
Panel bit depth	True 8 bit
Vertical viewing angle	178°
Horizontal viewing angle	178°
Bezel	3-sided borderless
Swivel	±45°
Tilt	-5 to +23°
Pivot	±90°
Height adjustment range	150 mm
VESA mounting	100 mm x 100 mm
Hardness	3H
Screen treatment	Anti-glare
Flicker-free	Yes
Low blue light modes	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
Display scan frequency (vertical)	50-75 Hz
Display scan frequency (horizontal)	30-115 kHz
Pixel pitch	0.21 x 0.21 mm
Display colors	Up to 16.7 million colors supported
Display Color Gamut	99% sRGB
Management software	HP Display Center; HP Display Manager ¹²

HP E24q G5 QHD Monitor

Accessories and services (not included)

HP Business PC Security Lock v3 Kit



Help prevent chassis tampering and secure your PC and display in workspaces and public areas with the affordable HP Business PC Security Lock v3 Kit.
Product number: 3XJ17AA

HP S101 Speaker Bar



Add rich stereo audio to select E-Series monitors and P-Series monitors¹ and keep a clean, clutter-free desk with the HP S101 Speaker Bar, which fits neatly underneath the display head and connects through USB.
Product number: 5UU40AA

HP E24q G5 QHD Monitor

Messaging Footnotes

- ¹ All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- ² More accurate colors compared to 72% NTSC.
- ³ Ergonomic Setup Guide is available through HP Display Center. Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.
- ⁴ Recycled/Renewable materials made up of 85% rPET, 4.5% Ocean Bound Plastics, and 0.5% coffee grounds. Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT® standard. HP defines renewable according to the Global Reporting Initiative Sustainability Reporting Standards.
- ⁵ Consists of 25% recycled metals. Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.
- ⁶ Extended ecosystem sold separately.
- ⁷ AC Power cable, HDMI 1.4 cable, DisplayPort™ 1.2 cable, and USB 3.0 A-B cable included. All other cables sold separately.
- ⁸ HP Display Manager software agent must be running on a web server and host PC. Some limitations may apply to legacy monitors.
- ⁹ Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.
- ¹⁰ Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.
- ¹¹ 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.
- ¹² Recycling facilities not available in all locations.
- ¹³ HP Sustainability Report 2020 and HP Displays Sustainability Story 2021.
- ¹⁴ Based on US EPEAT® registration according to IEEE 1680.1-2020 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
- ¹⁵ Extended ecosystem sold separately. Includes B560 PC Mounting Bracket, Quick Release Single Arm, and S101 Speaker Bar.

Technical Specifications Footnotes

- ¹ All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- ² DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 2560 x 1440 at 60 Hz with 8-bit color using one DisplayPort™, HDMI. The video card of the connected PC must be capable of supporting 2560 x 1440 and include one DisplayPort™ or one HDMI outputs to drive the monitor at the preferred mode.
- ³ EPEAT® registered where applicable. EPEAT® registration varies by country. See www.epeat.net for registration status by country. Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
- ⁴ External power supplies, WWAN modules, power cords, cables, and peripherals excluded. Service parts obtained after purchase may not be Low Halogen.
- ⁵ rPET Derived Closed Loop Plastic percentage is based on the definition set in the IEEE 1680.1-2018 standard.
- ⁶ All plastic parts contain ocean-bound plastic. Percentage of ocean-bound plastic contained in each component varies by product.
- ⁷ Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.
- ⁸ 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.
- ⁹ Molded pulp cushions are made from 100% recycled wood fiber and organic materials.
- ¹⁰ Included cables may vary by country.
- ¹¹ Lock sold separately.
- ¹² Host PC requires Windows 10 and above. HP Display Center is available on the Microsoft store.

Sign up for updates hp.com/go/getupdated

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.
January 2023

