# Poly Savi 8410 Office Monaural DECT 1920-1930 MHz Headset TAA (8L7E7AA)

## Overview



### Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].

### Be heard clearly

With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.

### Multi-device connectivity

Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

### Untether from your desk

Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].

# Features

### 3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

### Crystal-clear calls

Reduce background sounds with noise-canceling microphone and close conversation limiting.

### Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

### Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

### Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

### Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.[3]

---

*[1] Does not connect to the Savi 7200 headset.*

*[2] Line of sight from computer.*

*[3] Visit www.poly.com/savi-8400-office for more detail.*

## Specifications

| | |
|---|---|
| **Audio Features** | Hybrid Active noise cancellation (ANC); Microphone noise cancellation with close conversation limiting |
| **Weight (metric)** | 115 g |
| **Weight (imperial)** | 0.25 lb |
| **Package Dimensions (metric)** | 185 x 210 x 115 mm |
| **Package Weight (metric)** | 300 g |
| **Battery Life** | Up to 13 hours (talk time); Up to 50 hours (standby time) |
| **UPC Number** | 197497815139 |
| **Manufacturer Warranty** | Poly standard two-year limited warranty |
| **What Is In The Box** | Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC) |

## Additional specifications

| | |
|---|---|
| **Base Controls** | Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button; Configurable button |
| **Battery Description** | Rechargeable Li-ion polymer |
| **Bluetooth Version** | Bluetooth® Core 5.2 |
| **Button User Controls** | Power on/off; Call answer/end; Mute; Volume +/- |
| **Cartons Per Layer** | 10 |
| **Cartons Per Pallet** | 80 |
| **Certified Collaboration Software** | DECT Security certified |
| **Charge Time** | <3 hours |
| **Charging** | 3-way base |
| **Charging Type** | 3-way base |
| **Color** | Black |
| **Compatibility Statement** | Compatible with PCs via DECT™, USB Type-A, USB Type-C® or RJ-11 cable |
| **Compatible Operating Systems** | Windows 11; Windows 10; macOS; Android™; iOS |
| **Connection Type** | USB Type-C®/A |
| **Connection Type** | Wireless: DECT™, Bluetooth® (via office base); Wired: USB Type-A, USB Type-C®, RJ-11 |
| **Connectivity** | 3-way base |
| **ECCN** | 5A992 |
| **Ear Cushions** | Artificial leather (surface material) |
| **Ecolabels** | TCO Certified |
| **HTS Code** | 8517620090 |
| **Headphone Type** | On-ear (monaural) |
| **Impedance** | 32 ohms |
| **Layers Per Pallet** | 8 |
| **Management Software** | Poly Lens[1] |
| **Master Carton Dimension (imperial)** | 6.1 x 23.42 x 8.85 in |
| **Master Carton Dimension (metric)** | 15.5 x 59.5 x 22.5 cm |
| **Master Carton Weight (imperial)** | 10.03 lb |
| **Master Carton Weight (metric)** | 4.55 kg |
| **Microphone Bandwidth** | 100 Hz to 10 kHz |
| **Microphone Type** | Noise cancelling |
| **Multiple Order Quantity** | 1 |

| | |
|---|---|
| **Package Dimensions (imperial)** | 7.48 x 8.26 x 2.16 in |
| **Package Weight (imperial)** | 0.66 lb |
| **Pallet Dimensions (imperial)** | 40 x 48 x 58.66 in |
| **Pallet Dimensions (metric)** | 101.6 x 121.9 x 149 cm |
| **Pallet Weight (imperial)** | 787.05 lb |
| **Pallet Weight (metric)** | 357 kg |
| **Products Per Pallet** | 400 |
| **Products per Pallet Layer** | 50 |
| **Sensitivity (Microphone)** | 112 dB SPL |
| **Sensitivity (Speaker)** | 118 dB SPL |
| **Speaker Bandwidth** | 100 Hz to 6.8 kHZ (wideband mode); 20 Hz to 20 kHZ (multimedia mode) |
| **Speaker Size** | 32 mm |
| **Supported Bluetooth Profiles** | A2DP; HFP; HSP |
| **UC Compatibility** | Standard |
| **UNSPSC Code** | 43191638 |
| **Wearing Style** | Mono |
| **Wireless Range** | Up to 180 m in open area; Up to 55 m in typical office environment |
| **Wireless Range (imperial)** | Up to 590 ft in open area; Up to 180 ft in typical office environment |

---

*[1] Requires downloadable software on Poly.com/lens. Host PC requires Windows 10 or higher.*

---

# Hybrid Work Solutions

## Audio

★ : Recommended

### Audio Accessories

| | |
|---|---|
| Poly APA-24 (ALCATEL) Electronic Hookswitch TAA | 85Q52AA |
| Poly APC-43 Electronic Hookswitch TAA | 85Q55AA |
| Poly APD-80 Electronic Hookswitch TAA | 85Q58AA |
| Poly APN-91 Electronic Hookswitch TAA | 85Q59AA |
| Poly APP-51 Electronic Hookswitch TAA | 85Q60AA |
| Poly APS-11 Electronic Hookswitch TAA | 85Q78AA |
| Poly APU-76 Electronic Hookswitch TAA | 85R00AA |
| Poly APV-63 Electronic Hookswitch TAA | 85R01AA |
| Poly EHS 3.5mm to 3.5mm Cable | 85R17AA |
| Poly HL10 Handset Lifter | 784Q1AA |
| Poly HL10 Handset Lifter with Straight Plug TAA | 784Q2AA |
| Poly RD-1 Electronic Hookswitch | 85R71AA |
| Poly Savi 7410/7420 Office Charging Cradle | 8L556AA |
| Poly Savi 8200 5 Unit Charge Base | 85R34AA |
| Poly Savi 8200 Leatherette Ear Cushions (2 Pieces) | 85Q63AA |
| Poly Savi 8200 USB-A Headset Charging Cable | 85R35AA |
| Poly Savi 8210 Battery with Removal Tool | 85R37AA |
| Poly Savi 8220 Battery with Removal Tool | 85R39AA |
| Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base | 8L569AA |
| Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base | 8L571AA |
| Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base | 8L558AA |
| Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base | 8L562AA |
| Poly Savi 8410/8420 Office Charging Cradle | 8L573AA |
| Poly Savi D400 Microsoft Teams Certified DECT 1920-1930 MHz Dongle | 8L552AA |
| Poly Savi D400 UC DECT 1880-1900 MHz Dongle | 8J8V7AA |
| Poly Savi D400 UC DECT 1920-1930 MHz Dongle | 85T33AA |
| Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle | 8J8W1AA |
| Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle | 85T34AA |
| Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA | 8L5A2AA |

| | |
|---|---|
| Poly Savi Office S2 Telephone Cable | 85R55AA |
| Poly Savi Office Straight Plug Online Indicator | 85R52AA |
| Poly Savi Office Telephone Interface Cable | 85R57AA |
| Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA | 85R59AA |
| Poly Savi W8210/8220 Charging Cradle | 85R65AA |
| Poly USB-A to USB-C Adapter | 85Q48AA |
| Poly USB-C to USB-A Adapter | 85Q49AA |

---

## Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 10, 2026 7:26 PM UTC+0000