



Poly Savi 8420 Office Stereo Microsoft Teams Certified DECT 1920-1930 MHz Headset TAA (8L7F6AA)



Overview

Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].

Be heard clearly

With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.

Multi-device connectivity

Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

Untether from your desk

Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].

Features

3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Crystal-clear calls

Reduce background sounds for the person you are talking to with a noise-canceling microphone and close conversation limiting while you stay in the zone with active noise canceling.

Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

[1] Does not connect to the Savi 7200 headset.

[2] Line of sight from computer.

Specifications

Audio	Active noise cancellation (ANC); Noise cancellation with close conversation limiting
Weight	160 g
Weight	0.35 lb
Package dimensions (W x D x H)	185 x 210 x 115 mm
Package weight	300 g
Battery life	Up to 13 hours (talk time); Up to 50 hours (standby time)
Special features	Color display on office base for audio settings management
Minimum System Requirements	USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)
UPC number	197497833607
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC)

Additional specifications

Base controls	Microsoft Teams button; Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button
Battery type	Rechargeable Li-ion polymer
Bluetooth version	5.2
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Microsoft Teams
Charge time	3 hours
Color	Black
Compatible Operating Systems	macOS; Windows
Connection type	Bluetooth®; DECT™
Connects to	Desk phone; PC; Mobile
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	Artificial leather (surface material)
HTS code	8517620090
Impedance	32 ohms
Management Software	Poly Lens
Multiple order quantity	1
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	8
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	357 kg
Pallet weight	787.05 lb
Products per pallet	400
Products per pallet layer	50
Sensitivity (microphone)	112 dB SPL
Sensitivity (speaker)	118 dB SPL
Speaker size	32 mm
Supported bluetooth profiles	A2DP; HFP; HSP
UNSPSC code	43191638

Wireless range Up to 180 m in open area; Up to 55 m in typical office environment

Wireless range (imperial) Up to 590 ft in open area; Up to 180 ft in typical office environment

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly Busy Light (Angle Plug)	920Q4AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7410/7420 Office Charging Cradle	8L556AA
Poly Savi 8200 5 Unit Charge Base	85R34AA
Poly Savi 8200 Leatherette Ear Cushions (2 Pieces)	85Q63AA
Poly Savi 8200 USB-A Headset Charging Cable	85R35AA
Poly Savi 8210 Battery with Removal Tool	85R37AA
Poly Savi 8220 Battery with Removal Tool	85R39AA

Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Hard Case	85R51AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office USB-A PC Connection Cable	85R54AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA
Poly Savi W8210/8220 Charging Cradle	85R65AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.